




Copyright FCI.



Part Number & Date Code Printing

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	G±0.25	Plating: 0.75µ AU	Plating: Flash AU
09	30.81	24.99	16.96	16.21	5.90	D09S23B6G*00**	D09S23B4G*00**
15	39.14	33.32	25.18	24.54	5.90	D15S23B6G*00**	D15S23B4G*00**
25	53.03	47.04	39.12	38.25	5.70	D25S23B6G*00**	D25S23B4G*00**
37	69.32	63.50	55.68	54.71	5.70	D37S23B6G*00**	D37S23B4G*00**

REQUIREMENTS

Technical characteristics:

Shell: steel tin/Zinc Cr3 plated
Insulators: self-extinguishing black polyester, UL class 94V0
Contacts size 20: phosphor bronze, gold on mating end, bright tin on termination end over nickel on entire contact
Cycles : 500 for protection 6
: 200 for protection 4

Harpoons: phosphor bronze, tin plated

Metal plate for electrical continuity: brass, tin/Zinc Cr3 plated

Female screw: brass, tin/Zinc Cr3 plated torque: 0.5N/m

Electrical characteristics:



max. current rating: 5A
Test voltage: 1000V
Rated voltage: 300V
Contact resistance: ≤15mΩ
Shell resistance: ≤5mΩ
Insulation resistance: ≥5000MΩ

Climatic characteristics:

Operating temperature range: -55°C +125°C


Dimensions:

in accordance with MIL-C-24308




LF FOR LEAD FREE

Threaded ØT M3 = I
Threaded ØT 4.40 = V



PC card drilling dimensions (after plating)
(thickness 1.60±0.20mm)



FOR ROHS DETAILS REFER DWG. NO: C01-8646-0000

European Views

rev	ecn no	dr	date
B	105-0124	JS	2005/07/27
C	106-0074	SK	2006/06/08
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	JOHN SLEEBA	1999/05/17	ANGULAR 0.XX' ±1°	0.X	±0.1	Scale 1:1
Eng	GEORGE VJ	1999/05/17		0.XX	±0.1	
Chr	GEORGE VJ	2005/07/27		0.XXX	±0.1	
Appr	KVSD	2005/07/27	Product family			Spec ref -
			D-SUB			
			DELTA-D			
			CUSTOMER			
			sheet 1 of 1			

REV F - 2006-04-17

PDM: Rev:C

STATUS: Released

Printed: Jan 18, 2011