Sensitive Snap-Action Pushbutton Switches — Solder and P.C. Terminals (Momentary Action)

PS SERIES — 5 AMP. (S.P.) 1 AMP (D.P.) 0.4 VA

DIRECT PANEL MOUNT



ONE POLE



TWO POLE

Basic P/N	Terminal Type	Poles	Cap Size	Cap Color	Contact Material-Type
PS	1 - Solder lug 2 - Printed Circuit Terminals	1 - One ❶ 2 - Two ❶	0 - No Cap 1 - .200 Dia. 2 - .375 Dia. 3 - .450 Sq. 4 - .310 Dia. 5 - .780 Sq. ❸	0 - No Cap 1 - Black 2 - White 3 - Ted	B - Gold/Nickel/Brass ❷ G - Gold/Nickel/Silver ❶❷ Q - Coin Silver ❶

❶ Single pole circuit rated 5 amps, double pole circuit rated 1 amp.
❷ Ratings are 0.4 VA — 28 BAC or DC
❸ Supplied with .90" square black bezel as Standard

EXAMPLES:
PS1-100Q = One-pole, S.L., 5 amp., No Cap, Coin Silver Contacts
PS2-221B = Two-pole, PC, .4 VA, .375 Dia., Black Cap., Gold/Nickel/Brass Contacts



NEW .780" SQUARE CAP AND BEZEL

W-NU-29A

W-NU-30A

DECORATIVE FACE NUTS
(SEE NOTE UNDER MATERIALS)

SPECIFICATIONS

Contact Rating – Letter codes G and Q (1 Pole) 5 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 5 amp resistive @ 28 VDC. (2 pole) 1 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 1 amp resistive @ 28 VDC.
Letter codes B and G – (1 and 2 Poles) 0.4 Volt-amps (VA) maximum @ 28 V max. (AC or DC).
Contact Resistance – 50 milliohms maximum.
Insulation Resistance – 1,000 megohms minimum.
Dielectric Strength – 1,000 volts RMS minimum at sea level.
Electrical Life – 60,000 cycles minimum at full load-resistive.
Maximum Allowable Installation Force on Plunger – 10 pounds.
Multi-pole contacts do not make and break simultaneously.

MATERIALS

Case — Diallyl Phthalate.
Bushing — Brass, nickel plated.
Housing — Stainless steel.
Plunger — Thermoplastic.
Common Contact — Refer to contact material table above.
Center & End Contact — Refer to contact material table above.
Hardware — (2) Hex nuts W-NU-11, brass nickel plated. (1) Internal tooth lockwasher W-WA-16, steel chromium plated. (1) Locking Ring W-RI-16, C.R.S. nickel plated.
Decorative Face Nuts — Brass, bright chrome plated. See Page 16 for complete dimensions.













Description	P/N	Color
Small Cap .200	W-KN-16	Black
	W-KN-16A	White
	W-KN-16B	Red
Medium Cap .310	W-KN-32	Black
	W-KN-32A	White
	W-KN-32B	Red
Large Cap .375	W-KN-17	Black
	W-KN-17A	White
	W-KN-17B	Red
Square Cap .450	W-KN-18	Black
	W-KN-18A	White
	W-KN-18B	Red
.780 Square Cap	W-KN-52	Black
	W-KN-52A	White
	W-KN-52B	Red
.90 Square Bezel	Bezel W-BZ-21	Black

Solder Lug Terminal



Printed Circuit Terminal



PS SERIES 5 AMP. (S.P.) 0.4VA

Sensitive Snap-Action Pushbutton Switches — P.C. Terminals (Momentary Action)

RIGHT ANGLE MOUNT IN P.C. BOARDS (HORIZONTAL)







Mounting Information

Basic P/N	Terminal Type	Poles	Cap Size	Cap Color	Contact Material-Type
PS	5 - Rt. Angle P.C. Mount 6 - Rt. Angle P.C. Mount	1 - One	0 - No Cap 1 - .200 Dia. 2 - .375 Dia. 3 - .450 Sq. 4 - .310 Dia.	0 - No Cap 1 - Black 2 - White 3 - Red	B - Gold/Nickel/Brass ❷ G - Gold/Nickel/Silver ❶❷ Q - Coin Silver ❷

❶ Rating is 5 amps — 125 VAC or 28 VDC.
❷ Ratings are 0.4 VA — 28 VAC or DC.









Description	P/N	Color
Small Cap .200	W-KN-16	Black
	W-KN-16A	White
	W-KN-16B	Red
Medium Cap .310	W-KN-32	Black
	W-KN-32A	White
	W-KN-32B	Red
Large Cap .375	W-KN-17	Black
	W-KN-17A	White
	W-KN-17B	Red
Square Cap .450	W-KN-18	Black
	W-KN-18A	White
	W-KN-18B	Red

ORDERING EXAMPLES:

PS5-100G = (Rt. Angle P.C. mount 5 amp.) One-pole No Cap No Color Gold/Nickel/Silver Contacts

P	S	5	-	1	0	0	G

PS6-121Q = (Rt. Angle P.C. mount 5 amp.) One-pole .375 Dia. Black Cap Coin Silver Contacts

P	S	6	-	1	2	1	Q

SPECIFICATIONS

Contact Rating — Letter codes G and Q — 5 amp resistive @ 125 VAC or 28 VDC.
Letter codes B and G — 0.4 volts-amps (VA) maximum @ 28 VAC or DC.

Contact Resistance — 50 milliohms maximum.

Insulation Resistance — 1,000 megohms minimum.

Dielectric Strength — 1,000 volts RMS minimum at sea level.

Electrical Life — 60,000 cycles minimum at full load.

Maximum Allowable Installation Force on Plunger — 10 pounds.

MATERIALS

Case — Diallyl Phthalate.

Bushing — Brass, nickel plated.

Housing — Stainless steel.

Plunger — Thermoplastic.

Common Contact — Refer to contact material table above.

Center & End Contact — Refer to contact material table above.

Sensitive Snap-Action Pushbutton Switches — P.C. Terminals (Momentary Action)

PS SERIES — 5 AMP. (S.P.) 1 AMP. (D.P.) 0.4VA

RIGHT ANGLE P.C. MOUNT SWITCHES

Basic P/N	Terminal Type	Poles	Cap Size	Cap Color	Contact Material-Type
PS	9 - Horizontal Right Angle 10 - Vertical Right Angle (.100 Terminal Spacing) 11 - Vertical Right Angle 0.4 VA (.150 Terminal Spacing)	1 - One ❶ 2 - Two ❶	0 - No Cap 1 - .200 Dia. 2 - .375 Dia. 3 - .450 Sq. 4 - .310 Dia.	0 - No Cap 1 - Black 2 - White 3 - Red	B - Gold/Nickel/Brass ❷ G - Gold/Nickel/Silver ❶❷ Q - Coin Silver ❶

❶ Single pole circuit rated 5 amps, double pole circuit rated 1 amp.
❷ Ratings are 0.4 VA — 28 VAC or DC.

ORDERING EXAMPLES:

PS9-100B = (PC mounted 0.4 VA) — One-pole — No Cap — No Color — Gold/Nickel/Brass Contacts

P	S	9	-	1	0	0	B

PS10-221Q= (PC mounted 1 amp.) — Two-pole — .375 Dia. — Black Cap — Coin Silver Contacts

P	S	10	-	2	2	1	Q

SPECIFICATIONS

Contact Rating — Letter codes G and Q (1 Pole) 5 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 5 amp resistive @ 28 VDC. (2 pole) 1 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 1 amp resistive @ 28 VDC.
Letter codes B and G — (1 and 2 Poles) 0.4 Volt-amps (VA) maximum @ 28 V maximum (AC or DC).
Contact Resistance — 50 milliohms maximum.
Insulation Resistance — 1,000 megohms minimum.
Dielectric Strength — 1,000 volts RMS minimum at sea level.
Electrical Life — 60,000 cycles minimum at full load-resistive.
Maximum Allowable Installation Force on Plunger — 10 pounds.
Multi-pole contacts do not make and break simultaneously.

MATERIALS

Case — Diallyl Phthalate.
Bushing — Brass, nickel plated.
Housing — Stainless steel.
Plunger — Thermoplastic.
Common Contact — Refer to contact material table above.
Center & End Contact — Refer to contact material table above.



Description	P/N	Color
Small Cap .200	W-KN-16	Black
	W-KN-16A	White
	W-KN-16B	Red
Medium Cap .310	W-KN-32	Black
	W-KN-32A	White
	W-KN-32B	Red
Large Cap .375	W-KN-17	Black
	W-KN-17A	White
	W-KN-17B	Red
Square Cap .450	W-KN-18	Black
	W-KN-18A	White
	W-KN-18B	Red

Right Angle P.C. Terminal



Sensitive Snap-Action Pushbutton Switches — P.C. Terminals (Momentary Action)

PS SERIES | 5 AMP. (S.P.) 1 AMP. (D.P.) 0.4VA

RIGHT ANGLE P.C. MOUNT SWITCHES

PS 9









1 Pole P.C. Mounting

ONE POLE

EPOXY SEALED P.C. TERMINALS ARE SUPPLIED AS STANDARD FOR THESE OPTIONS.

PS 9









2 Pole P.C. Mounting

TWO POLE

EPOXY SEALED P.C. TERMINALS ARE SUPPLIED AS STANDARD FOR THESE OPTIONS.

PS 10









1 Pole P.C. Mounting

ONE POLE

EPOXY SEALED P.C. TERMINALS ARE SUPPLIED AS STANDARD FOR THESE OPTIONS.

PS 10









2 Pole P.C. Mounting

TWO POLE

EPOXY SEALED P.C. TERMINALS ARE SUPPLIED AS STANDARD FOR THESE OPTIONS.

PS 11









1 Pole P.C. Mounting

ONE POLE

EPOXY SEALED P.C. TERMINALS ARE SUPPLIED AS STANDARD FOR THESE OPTIONS.

PS 11









2 Pole P.C. Mounting

TWO POLE

EPOXY SEALED P.C. TERMINALS ARE SUPPLIED AS STANDARD FOR THESE OPTIONS.

Sensitive Snap-Action Pushbutton Switches — P.C. Terminals (Momentary Action)

PS SERIES — 5 AMP. (S.P.) 1 AMP. (D.P.) 0.4 VA

VERTICAL P.C. MOUNT (.460 x .620 BRACKET)

PS7 (LONG BUSHING)



SP



DP



PS8 (SHORT BUSHING)



SP



DP



Basic P/N	Terminal Type	Poles	Cap Size	Cap Color	Contact Material-Type
PS	7 - PC Mounted 8 - PC Mounted	1 - One ❶ 2 - Two ❶	0 - No Cap 1 - .200 Dia. 2 - .375 Dia. 3 - .450 Sq. 4 - .310 Dia.	0 - No Cap 1 - Black 2 - White	B - Gold/Nickel/Brass ❷ G - Gold/Nickel/Silver ❶❷ Q - Coin Silver ❶

❶ Single pole circuit rated 5 amps, double pole circuit rated 1 amp.
❷ Ratings are 0.4 VA — 28 VAC or DC.

ORDERING EXAMPLES:

PS7-100G = (PC mounted 5 amp.) | One-pole | No Cap | No Color | Gold/Nickel/Silver Contacts

P S 7 - 1 0 0 G

PS8-221B = (PC mounted 0.4 VA) | Two-pole | .375 Dia. | Black Cap | Gold/Nickel/Brass Contacts

P S 8 - 2 2 1 B



1 Pole P.C. Mounting



2 Pole P.C. Mounting









Description	P/N	Color
Small Cap .200	W-KN-16	Black
	W-KN-16A	White
	W-KN-16B	Red
Medium Cap .310	W-KN-32	Black
	W-KN-32A	White
	W-KN-32B	Red
Large Cap .375	W-KN-17	Black
	W-KN-17A	White
	W-KN-17B	Red
Square Cap .450	W-KN-18	Black
	W-KN-18A	White
	W-KN-18B	Red

Printed Circuit Terminal

SPECIFICATIONS

Contact Rating – Letter codes G and Q (1 Pole) 5 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 5 amp resistive @ 28 VDC. (2 pole) 1 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 1 amp resistive @ 28 VDC.
Letter codes B and G – (1 and 2 Poles) 0.4 Volt-amps (VA) maximum @ 28 V maximum (AC or DC).
Contact Resistance – 50 milliohms maximum.
Insulation Resistance – 1,000 megohms minimum.
Dielectric Strength – 1,000 volts RMS minimum at sea level.
Electrical Life – 60,000 cycles minimum at full load-resistive.
Maximum Allowable Installation Force on Plunger – 10 pounds.
Multi-pole contacts do not make and break simultaneously.

MATERIALS

Case — Diallyl Phthalate.
Bushing — Brass, nickel plated.
Housing — Stainless steel.
Plunger — Thermoplastic.
Common Contact — Refer to contact material table above.
Center & End Contact — Refer to contact material table above.

Sensitive Snap-Action Pushbutton Switches — P.C. Terminals (Momentary Action)

PS SERIES | 5 AMP. (S.P.) 1 AMP (D.P.) 0.4 VA

VERTICAL P.C. MOUNT (.630 x .620 BRACKET)

PS71 (LONG BUSHING)



SP



DP



PS81 (SHORT BUSHING)



SP



DP



Basic P/N	Terminal Type	Poles	Cap Size	Cap Color	Contact Material-Type
PS	71 - PC Mounted 81 - PC Mounted	1 - One ❶ 2 - Two ❶	0 - No Cap 1 - .200 Dia. 2 - .375 Dia. 3 - .450 Sq. 4 - .310 Dia.	0 - No Cap 1 - Black 2 - White 3 - Red	B - Gold/Nickel/Brass ❷ G - Gold/Nickel/Silver ❶❷ Q - Coin Silver ❶

❶ Single pole circuit rated 5 amps, double pole circuit rated 1 amp.
❷ Ratings are 0.4 VA — 28 VAC or DC.

ORDERING EXAMPLES:

PS71-100B= (PC mounted 0.4 VA) | One-pole | No Cap | No Color | Gold/Nickel/Brass Contacts

P S 71 - 1 0 0 B

PS81-221Q= (PC mounted 1 amp.) | Two-pole | .375 Dia. | Black Cap | Coin Silver Contacts

P S 81 - 2 2 1 Q

SPECIFICATIONS

Contact Rating – Letter codes G and Q (1 Pole) 5 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 5 amp resistive @ 28 VDC. (2 pole) 1 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 1 amp resistive @ 28 VDC.
Letter codes B and G – (1 and 2 Poles) 0.4 Volt-amps (VA) maximum @ 28 V maximum (AC or DC).
Contact Resistance – 50 milliohms maximum.
Insulation Resistance – 1,000 megohms minimum.
Dielectric Strength – 1,000 volts RMS minimum at sea level.
Electrical Life – 60,000 cycles minimum at full load-resistive.
Maximum Allowable Installation Force on Plunger – 10 pounds.
Multi-pole contacts do not make and break simultaneously.

MATERIALS

Case — Diallyl Phthalate.
Bushing — Brass, nickel plated.
Housing — Stainless steel.
Plunger — Thermoplastic.
Common Contact — Refer to contact material table above.
Center & End Contact — Refer to contact material table above.



1 Pole P.C. Mounting



2 Pole P.C. Mounting









Description	P/N	Color
Small Cap .200	W-KN-16	Black
	W-KN-16A	White
	W-KN-16B	Red
Medium Cap .310	W-KN-32	Black
	W-KN-32A	White
	W-KN-32B	Red
Large Cap .375	W-KN-17	Black
	W-KN-17A	White
	W-KN-17B	Red
Square Cap .450	W-KN-18	Black
	W-KN-18A	White
	W-KN-18B	Red

Printed Circuit Terminal

Sensitive Snap-Action Pushbutton Switches — P.C. Terminals (Momentary Action)

PS SERIES | 5 AMP. (S.P.) 1 AMP. (D.P.) 0.4 VA

VERTICAL P.C. MOUNT (.460 x .750 BRACKET)

PS72 (LONG BUSHING)



SP



DP



PS82 (SHORT BUSHING)





SP



DP



Basic P/N	Terminal Type	Poles	Cap Size	Cap Color	Contact Material-Type
PS	72 - PC Mounted 82 - PC Mounted	1 - One ❶ 2 - Two ❶	0 - No Cap 1 - .200 Dia. 2 - .375 Dia. 3 - .450 Sq. 4 - .310 Dia.	0 - No Cap 1 - Black 2 - White 3 - Red	B - Gold/Nickel/Brass ❷ G - Gold/Nickel/Silver ❶❷ Q - Coin Silver ❶

❶ Single pole circuit rated 5 amps, double pole circuit rated 1 amp.
❷ Ratings are 0.4 VA — 28 VAC or DC.

ORDERING EXAMPLES:

PS72-100Q= (PC mounted 5 amp.) One-pole No Cap No Color Coin Silver Contacts

P S 72 - 1 0 0 Q

PS82-221B= (PC mounted 0.4 VA) Two-pole .375 Dia. Black Cap Gold/Nickel/ Brass Contacts

P S 82 - 2 2 1 B



1 Pole P.C. Mounting



2 Pole P.C. Mounting









Description	P/N	Color
Small Cap .200	W-KN-16	Black
	W-KN-16A	White
	W-KN-16B	Red
Medium Cap .310	W-KN-32	Black
	W-KN-32A	White
	W-KN-32B	Red
Large Cap .375	W-KN-17	Black
	W-KN-17A	White
	W-KN-17B	Red
Square Cap .450	W-KN-18	Black
	W-KN-18A	White
	W-KN-18B	Red

Printed Circuit Terminal

SPECIFICATIONS

Contact Rating – Letter codes G and Q (1 Pole) 5 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 5 amp resistive @ 28 VDC. (2 pole) 1 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 1 amp resistive @ 28 VDC.
Letter codes B and G – (1 and 2 Poles) 0.4 Volt-amps (VA) maximum @ 28 V maximum (AC or DC).
Contact Resistance – 50 milliohms maximum.
Insulation Resistance – 1,000 megohms minimum.
Dielectric Strength – 1,000 volts RMS minimum at sea level.
Electrical Life – 60,000 cycles minimum at full load-resistive.
Maximum Allowable Installation Force on Plunger – 10 pounds.
Multi-pole contacts do not make and break simultaneously.

MATERIALS

Case — Diallyl Phthalate.
Bushing — Brass, nickel plated.
Housing — Stainless steel.
Plunger — Thermoplastic.
Common Contact — Refer to contact material table above.
Center & End Contact — Refer to contact material table above.

Sensitive Snap-Action Pushbutton Switches — P.C. Terminals (Momentary Action)

PS SERIES | 5 AMP. (S.P.) 1 AMP (D.P.) 0.4 VA

VERTICAL P.C. MOUNT (.630 x .750 BRACKET)

PS73 (LONG BUSHING)





PS83 (SHORT BUSHING)





Basic P/N	Terminal Type	Poles	Cap Size	Cap Color	Contact Material-Type
PS	73 - PC Mounted 83 - PC Mounted	1 - One 2 - Two	0 - No Cap 1 - .200 Dia. 2 - .375 Dia. 3 - .450 Sq. 4 - .310 Dia.	0 - No Cap 1 - Black 2 - White 3 - Red	B - Gold/Nickel/Brass ❷ G - Gold/Nickel/Silver ❶❷ Q - Coin Silver ❷

❶ Single pole circuit rated 5 amps, double pole circuit rated 1 amp.
❷ Ratings are 0.4 VA — 28 VAC or DC.

ORDERING EXAMPLES:

PS73-100G= (PC mounted 5 amp.) One-pole No Cap No Color Gold/Nickel/Silver Contacts

P S 73 - 1 0 0 G

PS83-221B= (PC mounted 0.4 VA) Two-pole .375 Dia. Black Cap Gold/Nickel/Brass Contacts

P S 83 - 2 2 1 B

SPECIFICATIONS

Contact Rating – Letter codes G and Q (1 Pole) 5 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 5 amp resistive @ 28 VDC. (2 pole) 1 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 1 amp resistive @ 28 VDC.
Letter codes B and G – (1 and 2 Poles) 0.4 Volt-amps (VA) maximum @ 28 V maximum (AC or DC).
Contact Resistance – 50 milliohms maximum.
Insulation Resistance – 1,000 megohms minimum.
Dielectric Strength – 1,000 volts RMS minimum at sea level.
Electrical Life – 60,000 cycles minimum at full load-resistive.
Maximum Allowable Installation Force on Plunger – 10 pounds.
Multi-pole contacts do not make and break simultaneously.

MATERIALS

Case — Diallyl Phthalate.
Bushing — Brass, nickel plated.
Housing — Stainless steel.
Plunger — Thermoplastic.
Common Contact — Refer to contact material table above.
Center & End Contact — Refer to contact material table above.



1 Pole P.C. Mounting



2 Pole P.C. Mounting









Description	P/N	Color
Small Cap .200	W-KN-16	Black
	W-KN-16A	White
	W-KN-16B	Red
Medium Cap .310	W-KN-32	Black
	W-KN-32A	White
	W-KN-32B	Red
Large Cap .375	W-KN-17	Black
	W-KN-17A	White
	W-KN-17B	Red
Square Cap .450	W-KN-18	Black
	W-KN-18A	White
	W-KN-18B	Red

Printed Circuit Terminal

EPOXY SEAL STD. FOR THIS SERIES

Sensitive Snap-Action Pushbutton Switches — Solder and P.C. Terminals (Momentary Action)

PS SERIES — 5 AMP. (S.P.) 1 AMP (D.P.) 0.4 VA

SNAP-IN MOUNT

PS14 SHOWN w/RAISED CAP



PS15 SHOWN w/FLUSH CAP



LED Not Included

Basic P/N	Cap Configuration Terminal-Rating	Poles	Cap Size	Cap Color	Optional Features: Bezel Color & Type	Optional Features: Contact Material-Type
PS	14 - Raised Cap Solder Lug 15 - Flush Cap ❸ Solder Lug 16 - Raised Cap PC Terminals 17 - Flush Cap ❸ PC Terminals	1 - One ❶ 2 - Two ❶	0 - No Cap 1 - .450 Sq.	0 - No Cap 1 - White 2 - Black 3 - Red	1 - White 2 - Black 3 - Red 4 - Black or LED	B - Gold/Nickel/Brass ❷ G - Gold/Nickel/Silver ❶❷ Q - Coin Silver ❶

❶ Single pole circuit rated 5 amps, double pole circuit rated 1 amp. ❷ Ratings are 0.4 VA — 28 BAC or DC. ❸ Flush cap is flush to bezel, not to mounting bracket.

EXAMPLES:
PS14-100Q = Raised Cap, Solder Lug Terminals, 5 Amp, Single Pole, No Cap, Coin Silver Contacts
PS14-1134B = Raised Cap, Solder Lug Terminals, 0.4 VA Rating, Single Pole, .450 Square Red Cap, Black Bezel for LED, Gold/Brass Contact Material

SPECIFICATIONS

Contact Rating – Letter codes G and Q (1 Pole) 5 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 5 amp resistive @ 28 VDC. (2 pole) 1 amp resistive @ 125 VAC (U.L. recognized, CSA certified) or 1 amp resistive @ 28 VDC.
Letter codes B and G – (1 and 2 Poles) 0.4 Volt-amps (VA) maximum @ 28 V maximum (AC or DC).
Contact Resistance – 50 milliohms maximum.
Insulation Resistance – 1,000 megohms minimum.
Dielectric Strength – 1,000 volts RMS minimum at sea level.
Electrical Life – 60,000 cycles minimum at full load-resistive.
Maximum Allowable Installation Force on Plunger – 10 pounds. Multi-pole contacts do not make and break simultaneously.

MATERIALS

Case — Diallyl Phthalate.
Bushing — Brass, nickel plated.
Housing — Stainless steel.
Plunger — Thermoplastic.
Pushbutton Cap — Molded nylon.
Bezel — Molded nylon.
Common Contact — Refer to contact material table above.
Center & End Contact — Refer to contact material table above.

Solder Lug Terminal



PC Terminal



APPROXIMATE DIMENSIONS (For Optional Bezel Types Shown on Page 12)

OPTIONAL BEZEL TYPE
1, 2, 3 (SEE TABLE)
PS14 Shown w/Raised Cap



Catalog No.	Color
W-BZ-12 W-BZ-12A W-BZ-12B	Black White Red

OPTIONAL BEZEL TYPE
1, 2, 3 (SEE TABLE)
PS15 Shown w/Flush Cap



Catalog No.	Color
W-BZ-12 W-BZ-12A W-BZ-12B	Black White Red

OPTIONAL BEZEL TYPE 4
FOR LED
PS14 Shown w/Raised Cap



SWITCHES SUPPLIED
WITHOUT LED LAMPS.

Catalog No.	Color
W-BZ-15	Black

OPTIONAL BEZEL TYPE 4
FOR LED
PS17 Shown w/Flush Cap



SWITCHES SUPPLIED
WITHOUT LED LAMPS.

Catalog No.	Color
W-BZ-15	Black

OPTIONAL MOUNTING CLIP (For Use With PS14 Thru PS17 Series Only)



- For thick plastic panel mount applications (.094" - .125" thick)
- For availability consult Electroswitch.