

**Part Number: 68126-3411**

2.54mm Pitch Header, Dual Row, Low Profile, Vertical, Shrouded, 34 Circuits, PBT Polyester 94V-0, Black, with Front Guide Slot

Image not available

Status:	OBsolete
Replacement:	Contact Molex
Series:	68126
Category:	PCB Headers

Series image - Reference only

Mates With Part(s):
[35811](#) IDT Receptacle**Product Environmental Compliance**EU RoHS: Compliance Status Not ReviewedChina RoHS:REACH SVHC: Not ReviewedLow-Halogen Status: Not Reviewed**Part Detail****General**

Status	Obsolete
Category	PCB Headers
Series	68126
Application	Signal, Wire-to-Board
Product Name	N/A

Physical

Breakaway	No
Circuits (Loaded)	34
Circuits (maximum)	34
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Plating Mating	Gold
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.20mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-55°C to +125°C
Termination Interface: Style	Through Hole

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Voltage - Maximum	125V

Agency Certification

CSA	LR19980
UL	E29179

Material Info

UPC	756054301647
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-35811-001
Sales Drawing	SD-68126-001

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)