



Main

Device short name	LUL
Range of product	TeSys U
Product or component type	Communication module
Product compatibility	LUCA LUCB LUCC LUCD LUCL LUCM

Complementary

Main function available	Communication module
Mounting mode	Plug-in
Mounting location	Front side
Physical interface	CAN
Bus type	Advantys STB
Cable connector type	Fire wire
Communication port protocol	CAN2.0A CAN2.B
Addressing	Self-addressing
Transmission rate	800 kbit/s
Current consumption	1.5 mA at 24 V DC 20...28 V
Input logic	Positive at 24 V DC - 7 mA
Response time	10 ms +/- 30 % change to state 0 10 ms +/- 30 % change to state 1
Input type	Resistive
Number of outputs	1 2 dedicated to starter-controller coil operation
Output supply	24 V DC network
Output current	<= 500 mA
Switching current capacity	0.5 mA at 24 V
Local signalling	3 LEDs front panel
Connection pitch	3.81 mm
Connections - terminals	Screw clamp terminals 1 cable 0.14...1 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable 0.14...1 mm ² - cable stiffness: rigid - without cable end Screw clamp terminals 1 cable 0.25...0.5 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable 0.25...1 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable 0.14...0.5 mm ² - cable stiffness: rigid - without cable end Screw clamp terminals 2 cable 0.14...0.75 mm ² - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable 0.25...0.34 mm ² - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable 0.5 mm ² - cable stiffness: flexible - with cable end
Associated cable type	AWG 26...AWG 16
Tightening torque	0.2...0.25 N.m - with screwdriver 2.5 mm

Environment

Ambient air temperature for operation

-25...55 °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LULC15](#)