


ALPHANUMERIC INDEX — CROSS-REFERENCE (Continued)

Industry Part Number	Motorola Direct Replacement	Motorola Similar Replacement	Page Number	Industry Part Number	Motorola Direct Replacement	Motorola Similar Replacement	Page Number
41506		2N8543	3-215	BD179-16	BD179-16		3-268
43104		2N5631	3-105	BD179-6	BD179-6		3-268
BD127		BD157	3-262	BD180	BD180		3-270
BD128		BD158	3-262	BD180-10	BD180-10		3-270
BD129		BD159	3-262	BD180-16	BD180-10		3-270
BD130		2N3055	3-6	BD180-6	BD180-6		3-270
BD131		BD785	3-304	BD185	BD185		3-272
BD132		BD786	3-304	BD186		BD778	3-302
BD133		BD787	3-304	BD187		BD787	3-304
BD135	BD135		3-258	BD188		BD788	3-304
BD135-10	BD135-10		3-258	BD189	BD189		3-272
BD135-16	BD135-16		3-258	BD190		BD788	3-304
BD135-6	BD135-6		3-258	BD195	MJE3055		3-904
BD136	BD136		3-260	BD196	MJE2955		3-904
BD136-10	BD136-10		3-260	BD197	MJE3055		3-904
BD136-16	BD136-16		3-260	BD198	MJE2955		3-904
BD136-6	BD136-6		3-260	BD199	MJE3055		3-904
BD137	BD137		3-258	BD200	MJE2955		3-904
BD137-10	BD137-10		3-258	BD201	BD795		3-312
BD137-16	BD137-16		3-258	BD202	BD796		3-314
BD137-6	BD137-6		3-258	BD203	BD797		3-312
BD138	BD138		3-260	BD204	BD798		3-314
BD138-10	BD138-10		3-260	BD206		MJE2955T	3-904
BD138-16	BD138-16		3-260	BD207		MJE3055T	3-904
BD138-6	BD138-6		3-260	BD208		MJE2955T	3-904
BD139	BD139		3-258	BD220		2N6123	3-154
BD139-10	BD139-10		3-258	BD221		2N6121	3-154
BD139-16	BD139-16		3-258	BD222		2N6122	3-154
BD139-6	BD139-6		3-258	BD223		2N6125	3-154
BD140	BD140		3-260	BD224		2N6124	3-154
BD140-10	BD140-10		3-260	BD225		2N6125	3-154
BD140-16	BD140-16		3-260	BD226	BD135		3-258
BD140-6	BD140-6		3-260	BD227	BD136		3-260
BD157	BD157		3-262	BD228	BD137		3-258
BD158	BD158		3-262	BD229	BD138		3-260
BD159	BD159		3-262	BD230	BD139		3-258
BD165	BD165		3-264	BD231	BD140		3-260
BD166	BD166		3-266	BD233	BD235		3-278
BD167	BD167		3-264	BD234	BD234		3-276
BD168	BD138		3-260	BD235	BD235		3-278
BD169	BD169		3-264	BD236	BD236		3-276
BD170	BD140		3-260	BD237	BD237		3-278
BD175	BD179		3-268	BD238		BD236	3-276
BD175-10	BD179-10		3-268	BD239	BD239		3-280
BD175-16	BD179-16		3-268	BD239A	BD239A		3-280
BD175-6	BD179-6		3-268	BD239B	BD239B		3-280
BD176	BD176		3-270	BD239C	BD239C		3-280
BD176-10	BD176-10		3-270	BD240	BD240		3-280
BD176-16	BD176-16		3-270	BD240A	BD240A		3-280
BD176-6	BD176-6		3-270	BD240B	BD240B		3-280
BD177	BD179		3-268	BD240C	BD240C		3-280
BD177-10	BD179-10		3-268	BD241	BD241		3-282
BD177-16	BD179-16		3-268	BD241A	BD241A		3-282
BD177-6	BD179-6		3-268	BD241B	BD241B		3-282
BD178	BD180		3-270	BD241C	BD241C		3-282
BD178-10	BD180-10		3-270	BD242	BD242		3-282
BD178-16	BD180-16		—	BD242A	BD242A		3-282
BD178-6	BD180-6		3-270	BD242B	BD242B		3-282
BD179	BD179		3-268	BD242C	BD242C		3-282
BD179-10	BD179-10		3-268	BD243	BD243		3-286

*Consult Motorola if a direct replacement is necessary.

TABLE 7 — PLASTIC TO-225 Type (Formerly TO-126 Type)

STYLE 1:
PIN 1. EMITTER
2. COLLECTOR
3. BASE



STYLE 3:
PIN 1. BASE
2. COLLECTOR
3. EMITTER

CASE 77-06

I _C Cont Amps Max	V _{CE(sus)} Volts Min	Device Type		h _{FE} Min/Max	@ I _C Amp	Resistive Switching			f _T MHz Min	P _D (Case) Watts @ 25°C
		NPN	PNP			t _s μs Max	t _f μs Max	@ I _C Amp		
0.3	250	MJE3440		40/160	0.02				15	15
	350	MJE3439		40/160	0.02				15	15
0.5	150	MJE341		25/200	0.05				15	20.8
	200	MJE344		30/300	0.05				15	20.8
	250	2N5655 BD157		30/250 30/240	0.1 0.05	3.5 typ	0.24 typ	0.1	10	20 20
	300	BD158 BD232 MJE340 2N5656	MJE350	30/240 20 min 30/240 30/250	0.05 0.15 0.05 0.1	3.5 typ	0.24 typ	0.1	10	20 20 20.8 20
	350	2N5657 BD159		30/250 30/240	0.1 0.05	3.5 typ	0.24 typ	0.1	10	20 20
1	40	2N4921	2N4918	20/100	0.5	0.6 typ	0.3 typ	0.5	3	30
	60	2N4922	2N4919	20/100	0.5	0.6 typ	0.3 typ	0.5	3	30
	80	2N4923	2N4920	20/100	0.5	0.6 typ	0.3 typ	0.5	3	30
1.5	45	BD165 BD135 BD135.6 BD135.10 BD135.16	BD166 BD136 BD136.6 BD136.10 BD136.16	15 min 40/250 40/100 63/160 100/250	0.5 0.15 0.15 0.15 0.15				6	20 12.5 12.5 12.5 12.5
	60	BD167 BD137 BD137.6 BD137.10 BD137.16	BD138 BD138.6 BD138.10 BD138.16	15 min 40/250 40/100 63/160 100/250	0.5 0.15 0.15 0.15 0.15				6	20 12.5 12.5 12.5 12.5
	80	BD169 BD139 BD139.6 BD139.10 BD139.16	BD140 BD140.6 BD140.10 BD140.16	15 min 40/250 40/100 63/160 100/250	0.5 0.15 0.15 0.15 0.15				6	20 12.5 12.5 12.5 12.5
	300	MJE13002•		5/25	1	4	0.7	1	5	40
	400	MJE13003•		5/25	1	4	0.7	1	5	40
2	45		BD234	25 min	1				3	25
	60	BD235	BD236	25 min	1				3	25
	80	BD237		25 min	1				3	25
	100	MJE270##	MJE271##	1.5k min	0.12				6	15
3	30	MJE520	MJE370	25 min	1					25
	40	MJE180	MJE170	50/250	0.1	0.6 typ	0.12 typ	0.1	50	12.5

• Case 77 (Style 3), # |h_{FE}| @ 1 MHz, ## Darlington

(continued)

MOTOROLA SEMICONDUCTOR TECHNICAL DATA

BD166

PLASTIC MEDIUM POWER SILICON PNP TRANSISTOR

... designed for use as audio amplifiers and drivers utilizing complementary or quasi complementary circuits.

- DC Current Gain — $h_{FE} = 40$ (Min) @ $I_C = 0.15$ Adc
- BD166 is complementary with BD165

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-Emitter Voltage	V_{CEO}	45	Vdc
Collector-Base Voltage	V_{CBO}	45	Vdc
Emitter-Base Voltage	V_{EBO}	5.0	Vdc
Collector Current	I_C	1.5	Adc
Base Current	I_B	0.5	Adc
Total Device Dissipation (θ : $T_A = 25^\circ\text{C}$ Derate above 25°C)	P_D	1.25 10	Watts mW/ $^\circ\text{C}$
Total Device Dissipation (θ : $T_C = 25^\circ\text{C}$ Derate above 25°C)	P_D	20 160	Watts mW/ $^\circ\text{C}$
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-65 to +150	$^\circ\text{C}$

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Case	θ_{JC}	6.25	$^\circ\text{C/W}$
Thermal Resistance, Junction to Ambient	θ_{JA}	100	$^\circ\text{C/W}$

ELECTRICAL CHARACTERISTICS ($T_C = 25^\circ\text{C}$ unless otherwise noted)



Characteristic	Symbol	Min	Max	Unit
Collector-Emitter Sustaining Voltage* ($I_C = 0.1$ Adc, $I_B = 0$)	$V_{(BR)CEO}$	45	—	Vdc
Collector Cutoff Current ($V_{CB} = 45$ Vdc, $I_E = 0$)	I_{CBO}	—	0.1	mA
Emitter Cutoff Current ($V_{BE} = 5.0$ Vdc, $I_C = 0$)	I_{EBO}	—	1.0	mA
DC Current Gain ($I_C = 0.15$ A, $V_{CE} = 2.0$ V) ($I_C = 0.5$ A, $V_{CE} = 2.0$ V)	h_{FE}	40 15	—	
Collector-Emitter Saturation Voltage* ($I_C = 0.5$ Adc, $I_B = 0.05$ Adc)	$V_{CE(sat)}$	—	0.5	Vdc
Base-Emitter On Voltage* ($I_C = 0.5$ Adc, $V_{CE} = 2.0$ Vdc)	$V_{BE(on)}$	—	0.95	Vdc
Current-Gain — Bandwidth Product ($I_C = 500$ mA, $V_{CE} = 2.0$ Vdc, $f = 1.0$ MHz)	f_T	6.0	—	MHz

*Pulse Test: Pulse Width ≤ 300 μs , Duty Cycle $\leq 2.0\%$.

1.5 AMPERE POWER TRANSISTOR

PNP SILICON

45 VOLTS
20 WATTS



- NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	10.80	11.94	0.425	0.435
B	7.50	7.74	0.295	0.305
C	2.42	2.66	0.095	0.105
D	0.51	0.66	0.020	0.026
E	2.93	3.17	0.115	0.125
F	2.39	2.54	0.094	0.100
G	1.27	2.41	0.050	0.095
H	0.39	0.63	0.015	0.025
J	14.61	16.53	0.575	0.650
K	3	—	—	—
L	3.76	4.01	0.148	0.158
M	1.15	1.29	0.045	0.055
N	0.64	0.68	0.025	0.025
O	3.69	3.93	0.145	0.155
P	1.02	—	0.040	—

CASE 77-06
TO-225AA TYPE

FIGURE 1 - P_D - T_C DERATING CURVE




FIGURE 2 - SAFE OPERATING AREA




FIGURE 3 - COLLECTOR SATURATION REGION




FIGURE 4 - CURRENT GAIN





FIGURE 5 - "ON" VOLTAGE



Note 1:

There are two limitations on the power handling ability of a transistor, average junction temperature and second breakdown. Safe operating area curves indicate $I_C \cdot V_{CE}$ limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 2 is based on $T_{J(pk)} = 150^\circ\text{C}$; T_C is variable depending on conditions. Second breakdown pulse limits are valid for duty cycles to 10% provided $T_{J(pk)} \leq 150^\circ\text{C}$. At high case temperatures, thermal limitations will reduce the power that can be handled to values less than the limitations imposed by second breakdown. (See AN-415)