

IF IN DOUBT - ASK




THIS IS A CAD DRAWING. ALL PRINTS ARE FOR REFERENCE ONLY. DO NOT AMMEND.
HARD COPIES. ALL CHANGES TO BE MADE TO ORIGINAL CAD DRAWING ONLY.

159-554 → 159-700
159-840 → 159-992

6VA-50VA 230V CHASSIS RANGE

159-554 to 159-700

159-840 to 159-992.



RATED VA	REG %	DIMENSIONS			FIXINGS		wt. KG
		LI/L2	W.#	H.	F	SIZE	
6	24	45/68	35.5	37.5	55	4BA	0.17
12	12	60/90	47	50	74	2BA	0.38
20	12	60/90	52	50	74	2BA	0.53
50	10	79/106	60	66	93.9	2BA	0.98

EXCLUDES TAGS

Third Angle Projection	DRAWING NAME	DRAWING No			
	OUTLINE DRAWINGS AND DATA	OLD-0003			
General Tolerance X = ± 0.4mm X.X = ± 0.2mm X.XX = ± 0.1mm	USED ON	ISSUE	DATE	ENG	ECN
	6VA-50VA 230V CHASSIS RANGE	1	02.07.88	GJS	
THIS DOCUMENT IS THE PROPERTY OF DAVALL ELECTRONICS LIMITED. WHICH MAKES THE COPYRIGHT IN THE DRAWING AND ALL THE RIGHTS RESERVED IN THE PRODUCT OR COMPONENTS HEREIN AND THEREON SHALL NOT BE LOANED, REPRODUCED OR IN ANY MANNER TO A THIRD PARTY WHO SHALL THE PRODUCT OR COMPONENTS REMAINED BE MADE, COPIED REPRODUCED OR IN ANY MANNER TO A THIRD PARTY WITHOUT THE PRIOR CONSENT IN WRITING OF DAVALL ELECTRONICS LIMITED.	FINISH	SCALE			
		N.T.S			