

Surface Mount Aluminum Electrolytic

CE Series




FEATURE


For General Purposes Series with 105°C 2000 Hours

Suitable for AV (TV, Video, Audio), Personal Computer, Home Appliance

MARKING



DIMENSIONS



() Reference Size

Unit : mm

SIZE CODE	DØ	L	A	H	I	W	P	K
B	4.0	5.4	4.3	5.5 Max.	1.8	0.65 ± 0.1	1.0	0.35 ^{+0.15} _{-0.20}
C	5.0	5.4	5.3	6.5 Max.	2.2	0.65 ± 0.1	1.5	0.35 ^{+0.15} _{-0.20}
D	6.3	5.4	6.6	7.8 Max.	2.6	0.65 ± 0.1	2.2	0.35 ^{+0.15} _{-0.20}
E	8.0	6.2	8.3	9.5 Max.	3.4	0.65 ± 0.1	2.2	0.35 ^{+0.15} _{-0.20}
F	8.0	10.2	8.3	10.0 Max.	3.4	0.90 ± 0.2	3.1	0.70 ± 0.20
G	10.0	10.2	10.3	12.0 Max.	3.5	0.90 ± 0.2	4.6	0.70 ± 0.20

SPECIFICATION

ITEM	CHARACTERISTIC								
Operation Temperature Range	-40 to +105°C								
Rated Working Voltage Range	4 to 50V. DC								
Capacitance Tolerance	± 20% (120Hz / +25°C)								
Leakage Current (25°C)	Polarized : I ≤ 0.01CV or 3 (μA)								
	Whichever is greater after 2 minutes application of DC rated working voltage at 25°C.								
	I : Leakage Current (μA)		C : Rated Capacitance (μF)		V : Working Voltage (V)				
Dissipation Factor (tanδ) (120Hz / +25°C)	Polarized () : D.F of Downsized								
	W V (V)		4	6.3	10	16	25	35	50
	D.F	Ø4 ~ Ø6.3	0.50	0.30 (0.35)	0.22 (0.26)	0.16 (0.20)	0.14 (0.18)	0.12 (0.14)	0.12
		Ø8 ~ Ø10	0.40	0.35	0.26	0.20	0.16	0.14	0.12
Low Temperature Stability	Impedance Ratio at 120Hz								
	W V (V)		4	6.3	10	16	25	35	50
	-25 / +20°C		7	4	3	2	2	2	2
	-40 / +20°C		15	8	6	4	4	3	3
Load Life	After 2000 hours application of W V at 105°C, the capacitor shall meet following limits.								
	Capacitance Change		≤ ± 20% of Initial Value						
	Dissipation Factor		≤ 200% of Initial Specified Value						
	Leakage Current		≤ Initial Specified Value						
Shelf Life	At +105°C no voltage application after 1000 hours and then through the aging treatment, the capacitor shall meet limits for load life characteristics.								

CASE SIZE & MAX RIPPLE CURRENT

Max. Ripple Current (mA) r.m.s. (120Hz / +105°C)

POLARIZED															
μF	CODE	V (CODE)													
		4 (004)		6.3 (006)		10 (010)		16 (016)		25 (025)		35 (035)		50 (050)	
0.1	0R10												4.0 x 5.4	1	
0.22	0R22												4.0 x 5.4	2	
0.33	0R33												4.0 x 5.4	3	
0.47	0R47												4.0 x 5.4	5	
1.0	1R00												4.0 x 5.4	10	
2.2	2R20												4.0 x 5.4	16	
3.3	3R30												4.0 x 5.4	16	
4.7	4R70									4.0 x 5.4	22		5.0 x 5.4	23	
6.8	0068									4.0 x 5.4	25		5.0 x 5.4	23	
10	0010							4.0 x 5.4	28	4.0 x 5.4	28	5.0 x 5.4	28	6.3 x 5.4	35
22	0022			4.0 x 5.4	26			5.0 x 5.4	39			6.3 x 5.4	55	8.0 x 6.2	70
33	0033			4.0 x 5.4	29	5.0 x 5.4	43			6.3 x 5.4	65	8.0 x 6.2	84	8.0 x 10.2	91
47	0047	4.0 x 5.4	34	5.0 x 5.4	46			6.3 x 5.4	70	6.3 x 5.4 8.0 x 6.2	80 91	8.0 x 10.2	98	10 x 10.2	100
100	0100	5.0 x 5.4	61	6.3 x 5.4	71	6.3 x 5.4 8.0 x 6.2	70 110	8.0 x 10.2	120	8.0 x 10.2	130	10 x 10.2	160		
150	0150	6.3 x 5.4	82												
220	0220	6.3 x 5.4	82	8.0 x 10.2	150	8.0 x 10.2	160	10 x 10.2	210	10 x 10.2	190				
330	0330			8.0 x 10.2	230			10 x 10.2	230						
470	0470					10 x 10.2	270							Size	R.C

PARTS NUMBER SYSTEM

Example : 10μF, 16V

CE	016	M	0010	R	E	B	-	0405
Series Name	Voltage Code	Tolerance	Capacitance Code	Package Code	Life Code	Size Code		Case Code

CAPACITANCE TOLERANCE		LIFE CODE		SIZE CODE							
M	±20%	E	2000 Hours	Size Code	A	B	C	D	E	F	G
K	±10%	S	1000 Hours	DØ (mm)	3.0 x 5.4	4.0 x 5.4	5.0 x 5.4	6.3 x 5.4	8.0 x 6.2	8.0 x 10.2	10.0 x 10.2
W	-5% ~ +20%	R	Special								

CAPACITANCE CODE																		
Capacitance	0.1	0.22	0.33	0.47	1.0	2.2	3.3	4.7	6.8	10	22	33	47	100	220	330	470	1000
Code	0R10	0R22	0R33	0R47	1R00	2R20	3R30	4R70	6R80	0010	0022	0033	0047	0100	0220	0330	0470	1000

VOLTAGE CODE									
Voltage	4	6.3	10	16	25	35	50	63	100
Code	004	006	010	016	025	035	050	063	100


PACKAGE CODE		CASE CODE								Unit : mm
R	Embossed Plastic Tape Reel	0305	3.0 x 5.4	0405	4.0 x 5.4	05.5	5.0 x 5.4	0605	6.3 x 5.4	
		0806	8.0 x 6.2	0810	8.0 x 10.2	1010	10.0 x 10.2			

STANDARD PRODUCTS


W V (VD.C)	CAP. (μ F)	SIZE (mm)		PART NO.	D.F Max. 120 Hz	LEAKAGE CURRENT (μ A/2 Min.) Max.	RIPPLE CURRENT (mA) r.m.s. 120 Hz / 85°C
		D Ø	L				
4	47	4	5.4	CE004M0047REB-0405	0.50	34	34
	100	5	5.4	CE004M0100REC-0505	0.50	4.0	61
	150	6.3	5.4	CE004M0150RED-0605	0.50	6.0	82
	220	6.3	5.4	CE004M0220RED-0605	0.50	8.8	82
6	22	4	5.4	CE006M0022REB-0405	0.30	3.0	26
	33	4	5.4	CE006M0033REB-0405	0.30	3.0	29
	47	5	5.4	CE006M0047REC-0505	0.30	3.0	46
	100	6.3	5.4	CE006M0100RED-0605	0.35	6.3	71
	220	8	10.2	CE006M0220REF-0810	0.35	13.8	150
	330	8	10.2	CE006M0330REF-0810	0.35	20.8	230
10	33	5	5.4	CE010M0033REC-0505	0.22	3.3	43
	100	6.3	5.4	CE010M0100RED-0605	0.26	10.0	70
	100	8	6.2	CE010M0100REE-0806	0.22	10.0	110
	220	8	10.2	CE010M0220REF-0810	0.26	22.0	160
	470	10	10.2	CE010M0470REG-1010	0.26	47.0	270
16	10	4	5.4	CE016M0010REB-0405	0.16	3.0	28
	22	5	5.4	CE016M0022REC-0505	0.16	3.5	39
	47	6.3	5.4	CE016M0047RED-0605	0.16	7.5	70
	100	6.3	5.4	CE016M0100RED-0605	0.20	16.0	120
	220	10	10.2	CE016M0220REG-1010	0.20	35.2	210
	330	10	10.2	CE016M0330REG-1010	0.20	52.8	230
25	4.7	4	5.4	CE025M4R70REB-0405	0.14	3.0	22
	6.8	4	5.4	CE025M6R80REB-0405	0.14	3.0	25
	10	4	5.4	CE025M0010REB-0405	0.14	3.0	28
	33	6.3	5.4	CE025M0033RED-0605	0.14	8.2	65
	47	6.3	5.4	CE025M0047RED-0605	0.18	11.7	80
	47	8	6.2	CE025M0047REE-0806	0.16	11.7	91
	100	8	10.2	CE025M0100REF-0810	0.16	25.0	130
	220	10	10.2	CE025M0220REG-1010	0.16	55.0	190
35	10	5	5.4	CE035M0010REC-0505	0.12	3.5	28
	22	6.3	5.4	CE035M0022RED-0605	0.12	7.7	55
	33	8	6.2	CE035M0033REE-0806	0.14	11.6	84
	47	8	10.2	CE035M0047REF-0810	0.14	16.5	98
	100	10	10.2	CE035M0100REG-1010	0.14	35.0	160
50	0.1	4	5.4	CE050M0R10REB-0405	0.12	3.0	1
	0.22	4	5.4	CE050M0R22REB-0405	0.12	3.0	2
	0.33	4	5.4	CE050M0R33REB-0405	0.12	3.0	3
	0.47	4	5.4	CE050M0R47REB-0405	0.12	3.0	5
	1	4	5.4	CE050M1R00REB-0405	0.12	3.0	10
	2.2	4	5.4	CE050M2R20REB-0405	0.12	3.0	16
	3.3	4	5.4	CE050M3R30REB-0405	0.12	3.0	16
	4.7	5	5.4	CE050M4R70REC-0505	0.12	3.0	23
	6.8	5	5.4	CE050M6R80REC-0505	0.12	3.4	23
	10	6.3	5.4	CE050M0010RED-0605	0.12	5.0	35
	22	8	6.2	CE050M0022REE-0806	0.12	11.0	70
	33	8	10.2	CE050M0033REF-0810	0.12	16.5	91
	47	10	10.2	CE050M0047REG-1010	0.12	23.5	100

Note : Extended capacitance and voltage values as well as miniaturized products are available on request.


TEMPERATURE CHARACTERISTICS DATA




LOAD LIFE DATA



FREQUENCY CHARACTERISTICS DATA




1μF/50V 4.0 x 5.4
 10μF/16V 4.0 x 5.4
 22μF/6.3V 4.0 x 5.4




10μF/50V 6.3 x 5.4
 22μF/35V 6.3 x 5.4
 47μF/16V 6.3 x 5.4

TEMPERATURE CHARACTERISTICS DATA



1μF/50V 4.0 x 5.4
 10μF/16V 4.0 x 5.4
 22μF/6.3V 4.0 x 5.4



10μF/50V 6.3 x 5.4
 22μF/35V 6.3 x 5.4
 33μF/25V 6.3 x 5.4