

*** 2421 V SERIES ***

RoHS COMPLIANT

Ordering information:

2421P ** V * 0 *
1 2 3

Material:

* Insulator : UL 94V-0 NYLON 66
* Contact : Brass





1.No.of circuits

2.Plating:

0= Tin plated 120u" min. over 30u"min. nickel overall
U= Gold flash over 30u"min. nickel overall

3.Base color:

0=white 1=black 3=red 7=blue 9=gray







2421P15V*0*	15	35.0(1.378)	39.94±0.30(1.572±.012)
2421P14V*0*	14	32.5(1.280)	37.44±0.30(1.474±.012)
2421P13V*0*	13	30.0(1.181)	34.94±0.30(1.376±.012)
2421P12V*0*	12	27.50(1.083)	32.44(1.277)
2421P11V*0*	11	25.00(.984)	29.94(1.179)
2421P10V*0*	10	22.50(.886)	27.44(1.080)
2421P09V*0*	9	20.00(.787)	24.94(.982)
2421P08V*0*	8	17.50(.689)	22.44(.883)
2421P07V*0*	7	15.00(.591)	19.94(.785)
2421P06V*0*	6	12.50(.492)	17.44(.687)
2421P05V*0*	5	10.000(.394)	14.94(.588)
2421P04V*0*	4	7.500(.295)	12.44(.490)
2421P03V*0*	3	5.000(.197)	9.94(.391)
2421P02V*0*	2	2.500(.098)	7.44(.293)
PART NO.	CIRCUITS	DIM. A	DIM. B

H	ES110343			LEOCO CORPORATION GENERAL TOLERANCES: (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>inch</td></tr><tr><td>1 PLACE</td><td>± 0.30</td><td>± --</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± .012</td></tr><tr><td>3 PLACES</td><td>± 0.10</td><td>± .008</td></tr><tr><td>4 PLACES</td><td>± --</td><td>± .004</td></tr></table> ANGULAR ± (1°)		mm	inch	1 PLACE	± 0.30	± --	2 PLACES	± 0.20	± .012	3 PLACES	± 0.10	± .008	4 PLACES	± --	± .004	APPROVED: CHARD		PART NO.: 2421P**V*0*			
	mm	inch																							
1 PLACE	± 0.30	± --																							
2 PLACES	± 0.20	± .012																							
3 PLACES	± 0.10	± .008																							
4 PLACES	± --	± .004																							
G	ES110315				DATE:		TITLE: HEADER																		
F	ES101254				CHECKED: SMILE		DRAWING NO.: 242106S																		
E	ES070924				DATE:		UNITS		SCALE	SIZE	SHEET	REV.													
D	ES061018			DRAWN: ANGEL		mm inch		3:1	A4	1/1	H														
REV.	ECO. NO.	CHG.	APP.	DATE:																					

RoHS COMPLIANT

CUSTOMER DRAWING

REV.	ECO. NO.	DESCRIPTION	DATE
A	DWG. REL.	APPROVED	2018.08.01



Note:

Material:

Insulator: Glass Filled Nylon66 , UL94 V-0

Contact: Brass, With Kink

Plating : Matte Tin plated 80μ " min over 30μ " min. Nickel underplating overall.

General Part Number:

2421P**V0G*

1 2

1. No.of circuits(02~15)

2. Color: 0=Natural 1=Black 3=Red 7=Blue

$A = 2.50(.098") \times \text{No. of spaces}$

$B = A + 4.94(.194")$

TOLERANCE UNLESS OTHERWISE SPECIFIED			 LEOCO CORPORATION http://www.leoco.com.tw			
mm [inch]	mm	inch	APPROVED BY: Chard	DATE: 2018.08.01	TITLE: 2.50mm Pitch Wafer	
1 PLACE	± 0.30	$\pm \text{---}$	CHECKED BY: Angel	DATE: 2018.08.01		
2 PLACES	± 0.20	$\pm .012$	DRAWN BY: Dylan	DATE: 2018.08.01	PART NO.: 2421P**V0G*	
3 PLACES	± 0.10	$\pm .008$	SIZE: A3	SCALE: 1:1	DRAWING NO.: 242124S	REV.: A
4 PLACES	$\pm \text{---}$	$\pm .004$			SHEET: 1 OF 1	
ANGULAR $\pm 1^\circ$						