



	1	2	3	4	5	6	7																																																																																																																																									
A						<table><tr><th>Contact</th><th>DIM A</th><th>DIM B</th><th>Contact</th><th>DIM A</th><th>DIM B</th><th>Contact</th><th>DIM A</th><th>DIM B</th></tr><tr><td>01</td><td>2.54</td><td>—</td><td>15</td><td>38.10</td><td>35.56</td><td>29</td><td>73.66</td><td>71.12</td></tr><tr><td>02</td><td>5.08</td><td>2.54</td><td>16</td><td>40.64</td><td>38.10</td><td>30</td><td>76.20</td><td>73.66</td></tr><tr><td>03</td><td>7.62</td><td>5.08</td><td>17</td><td>43.18</td><td>40.64</td><td>31</td><td>78.74</td><td>76.20</td></tr><tr><td>04</td><td>10.16</td><td>7.62</td><td>18</td><td>45.72</td><td>43.18</td><td>32</td><td>81.28</td><td>78.74</td></tr><tr><td>05</td><td>12.70</td><td>10.16</td><td>19</td><td>48.26</td><td>45.72</td><td>33</td><td>83.82</td><td>81.28</td></tr><tr><td>06</td><td>15.24</td><td>12.70</td><td>20</td><td>50.80</td><td>48.26</td><td>34</td><td>86.36</td><td>83.82</td></tr><tr><td>07</td><td>17.78</td><td>15.24</td><td>21</td><td>53.34</td><td>50.80</td><td>35</td><td>88.90</td><td>86.36</td></tr><tr><td>08</td><td>20.32</td><td>17.78</td><td>22</td><td>55.88</td><td>53.34</td><td>36</td><td>91.44</td><td>88.90</td></tr><tr><td>09</td><td>22.86</td><td>20.32</td><td>23</td><td>58.42</td><td>55.88</td><td>37</td><td>93.98</td><td>91.44</td></tr><tr><td>10</td><td>25.40</td><td>22.86</td><td>24</td><td>60.96</td><td>58.42</td><td>38</td><td>96.52</td><td>93.98</td></tr><tr><td>11</td><td>27.94</td><td>25.40</td><td>25</td><td>63.50</td><td>60.96</td><td>39</td><td>99.06</td><td>96.52</td></tr><tr><td>12</td><td>30.48</td><td>27.94</td><td>26</td><td>66.04</td><td>63.50</td><td>40</td><td>101.16</td><td>99.06</td></tr><tr><td>13</td><td>33.02</td><td>30.48</td><td>27</td><td>68.58</td><td>66.04</td><td></td><td></td><td></td></tr><tr><td>14</td><td>35.56</td><td>33.02</td><td>28</td><td>71.12</td><td>68.58</td><td></td><td></td><td></td></tr></table>			Contact	DIM A	DIM B	Contact	DIM A	DIM B	Contact	DIM A	DIM B	01	2.54	—	15	38.10	35.56	29	73.66	71.12	02	5.08	2.54	16	40.64	38.10	30	76.20	73.66	03	7.62	5.08	17	43.18	40.64	31	78.74	76.20	04	10.16	7.62	18	45.72	43.18	32	81.28	78.74	05	12.70	10.16	19	48.26	45.72	33	83.82	81.28	06	15.24	12.70	20	50.80	48.26	34	86.36	83.82	07	17.78	15.24	21	53.34	50.80	35	88.90	86.36	08	20.32	17.78	22	55.88	53.34	36	91.44	88.90	09	22.86	20.32	23	58.42	55.88	37	93.98	91.44	10	25.40	22.86	24	60.96	58.42	38	96.52	93.98	11	27.94	25.40	25	63.50	60.96	39	99.06	96.52	12	30.48	27.94	26	66.04	63.50	40	101.16	99.06	13	33.02	30.48	27	68.58	66.04				14	35.56	33.02	28	71.12	68.58				A
Contact	DIM A	DIM B	Contact	DIM A	DIM B	Contact	DIM A	DIM B																																																																																																																																								
01	2.54	—	15	38.10	35.56	29	73.66	71.12																																																																																																																																								
02	5.08	2.54	16	40.64	38.10	30	76.20	73.66																																																																																																																																								
03	7.62	5.08	17	43.18	40.64	31	78.74	76.20																																																																																																																																								
04	10.16	7.62	18	45.72	43.18	32	81.28	78.74																																																																																																																																								
05	12.70	10.16	19	48.26	45.72	33	83.82	81.28																																																																																																																																								
06	15.24	12.70	20	50.80	48.26	34	86.36	83.82																																																																																																																																								
07	17.78	15.24	21	53.34	50.80	35	88.90	86.36																																																																																																																																								
08	20.32	17.78	22	55.88	53.34	36	91.44	88.90																																																																																																																																								
09	22.86	20.32	23	58.42	55.88	37	93.98	91.44																																																																																																																																								
10	25.40	22.86	24	60.96	58.42	38	96.52	93.98																																																																																																																																								
11	27.94	25.40	25	63.50	60.96	39	99.06	96.52																																																																																																																																								
12	30.48	27.94	26	66.04	63.50	40	101.16	99.06																																																																																																																																								
13	33.02	30.48	27	68.58	66.04																																																																																																																																											
14	35.56	33.02	28	71.12	68.58																																																																																																																																											
B									B																																																																																																																																							
C									C																																																																																																																																							
D						PIN: Brass, Machined, CuZn38Pb2 Clip: Beryllium Copper, Heat Treated Plating Pin: TIN Gold Plated: 2um/80u” Nickel, Full Gold Plating Inner Contact: 2um/80u” Nickel Insulator: Polyamide, Glass Filled, UL94V-0 Current Rating: 3A/Contact max. Contact Resistance: <4mOhm/Contact Insulation Resistance: >1000Mohm at V=100V Operating: 60Vac/DC Operating Temperature: -55°C to +125°C Soldering Temperature: 260°C 10’s max.			D																																																																																																																																							
E									E																																																																																																																																							
F									F																																																																																																																																							
G	RoHS Complaint <table><tr><th>Scale</th><th>1:1</th></tr><tr><td>TOLERANCE</td><td></td></tr><tr><td>X.X</td><td>±0.40</td></tr><tr><td>X.XX</td><td>±0.25</td></tr><tr><td>X.XXX</td><td>±0.15</td></tr><tr><td>Angle</td><td>±3°</td></tr></table>					Scale	1:1	TOLERANCE		X.X	±0.40	X.XX	±0.25	X.XXX	±0.15	Angle	±3°	<table><tr><th colspan="3">Name</th><th>Item No.</th></tr><tr><td>Drawn</td><td>11.08.11</td><td>Chappell</td><td rowspan="2">AW127-xx/G-T-R</td></tr><tr><td>Approved</td><td></td><td></td></tr><tr><td colspan="3"></td><td>Title Socket, Machined Contacts, 1 Row, Gold Plating</td></tr><tr><td colspan="3"></td><td>Drawing No.</td></tr><tr><td colspan="3"></td><td>rev00</td></tr><tr><td colspan="3"></td><td>Replace</td></tr><tr><td colspan="3"></td><td>Sheet</td></tr></table>			Name			Item No.	Drawn	11.08.11	Chappell	AW127-xx/G-T-R	Approved						Title Socket, Machined Contacts, 1 Row, Gold Plating				Drawing No.				rev00				Replace				Sheet	G																																																																																												
Scale	1:1																																																																																																																																															
TOLERANCE																																																																																																																																																
X.X	±0.40																																																																																																																																															
X.XX	±0.25																																																																																																																																															
X.XXX	±0.15																																																																																																																																															
Angle	±3°																																																																																																																																															
Name			Item No.																																																																																																																																													
Drawn	11.08.11	Chappell	AW127-xx/G-T-R																																																																																																																																													
Approved																																																																																																																																																
			Title Socket, Machined Contacts, 1 Row, Gold Plating																																																																																																																																													
			Drawing No.																																																																																																																																													
			rev00																																																																																																																																													
			Replace																																																																																																																																													
			Sheet																																																																																																																																													
H	RoHS Complaint <table><tr><th>Scale</th><th>1:1</th></tr><tr><td>TOLERANCE</td><td></td></tr><tr><td>X.X</td><td>±0.40</td></tr><tr><td>X.XX</td><td>±0.25</td></tr><tr><td>X.XXX</td><td>±0.15</td></tr><tr><td>Angle</td><td>±3°</td></tr></table>					Scale	1:1	TOLERANCE		X.X	±0.40	X.XX	±0.25	X.XXX	±0.15	Angle	±3°	ASSMANN components			H																																																																																																																											
Scale	1:1																																																																																																																																															
TOLERANCE																																																																																																																																																
X.X	±0.40																																																																																																																																															
X.XX	±0.25																																																																																																																																															
X.XXX	±0.15																																																																																																																																															
Angle	±3°																																																																																																																																															
	1	2	3	4	5	6	7																																																																																																																																									