

## Housing - - 1407626

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON EVO sleeve housing, plastic, with bayonet flange for EVO screw connection, B10, for single locking latch, height: 60.6 mm, without EVO screw connection

### Product Features

- Flexible cable outlet direction, lateral or straight
- Lower costs than metal version
- Labeling option using 9 x 20 mm marking label
- Low weight
- Lower risk of condensation
- Both contact insert PE sheets are connected by means of a metal frame integrated in the sleeve housing
- Metal inlays ensure leading PE contact with angled plugs
- Completely corrosion-resistant
- Halogen-free plastic
- Impact test according to IK 08



### Key commercial data

|                      |   |
|----------------------|---|
| Packing unit         | 1   |
| GTIN                 | <br>4 046356 776882 |
| Custom tariff number | 85389099  |

### Technical data

#### General data

|        |  |
|--------|--|
| Note   | For contact inserts HC-B10, BB18, DD42, M, K8/24 |
| Design | B10  |
| Height | 60.5 mm  |
| Width  | 44 mm  |

# Housing - - 1407626

## Technical data

### General data

|   |  |
|---|--|
| Length                                  | 73 mm  |
| Housing type                            | Sleeve housings  |
| Color                                   | black  |
| Locking type                            | for single locking latch   |
| No. of cable exits                      | 1  |
| Cable exit                              | Straight   |
| Cable exit                              | Lateral  |
| Protective cover                        | No   |
| Degree of protection for housing        | IP65   |
| Ambient temperature (operation)         | -40 °C ... 125 °C  |
| Housing material                        | Polyamide  |
| Inflammability class according to UL 94 | V0   |
| Connection                              | The sleeve base housing must be supplemented with the EVO screw connection. The EVO screw connection is available in four sizes. It facilitates the creation of a straight or a side cable outlet. The EVO screw connection is mounted with the aid of, for example, a pipe wrench |

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 11     | 31261502 |
| UNSPSC 12.01  | 31261502 |
| UNSPSC 13.2   | 31261502 |
| UNSPSC 6.01   | 31261502 |
| UNSPSC 7.0901 | 31261502 |

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |

## Housing - - 1407626

### Accessories

#### Accessories

#### Marking

Snap-in markers - US-EMP (20X9) - 0829439



Snap-in markers, Card, white, Unlabeled, Can be labeled with: Thermomark C+, Thermomark C, Mounting type: Snapped into marker carrier, Lettering field: 20 x 9 mm

---

Cable gland - HC-B-G-M20-PLRBK - 1407669



EVO plastic cable gland with bayonet locking; size M20

---

Cable gland - HC-B-G-M25-PLRBK - 1407670



EVO plastic cable gland with bayonet locking; size M25

---

Cable gland - HC-B-G-M32-PLRBK - 1407671



EVO plastic cable gland with bayonet locking; size M32

---

Cable gland - HC-B-G-M40-PLRBK - 1407672



EVO plastic cable gland with bayonet locking; size M40

## Housing - - 1407626


### Accessories

---

### Drawings

## Housing - - 1407626

Dimensioned drawing



---

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>