





MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC []


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



MOUNTING HARDWARE




LOCK WASHER



HEX NUT

NOTES:

1. TUSONIX STANDARD PART NUMBER: 4400-098.
TUSONIX RoHS COMPLIANT PART NUMBER: 4400-098 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. MATERIAL: BUSHING; SILVER PLATED. LEAD; SILVER PLATED.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS. STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. OPERATING TEMP. RANGE: -55°C TO +125°C.
5. MAX. RECOMMENDED SOLDERING TEMPERATURE : 260° C.
6. SUPPLIED WITH SILVER PLATED INTERNAL TOOTH LOCK WASHER.
7. MAX. RECOMMENDED MOUNTING TORQUE : 2.0 Lb. in. [.226 Nm.]

CAP.(pf)		TOLERANCE	DC WORKING VOLTAGE		DC CURRENT (AMPS)	I.R. MIN. @ 100 (VDC)	DWV (VDC)	MIN. NO LOAD INSERTION LOSS (db) @ 25°C PER MIL-STD-220				
			85°C	125 °C				1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
27,000		GMV	70	50	10	40 G Ω	150	10	28	42	65	65
REVISION RECORD Original Release C.O. 19981028-4-01 REVISED NOTES & ADDED NUT/WASHER. S.M. 01-14-00 20000104-1-08 ORIENTATION SYMBOL ADDED DWV(VDC) 500 DELETED 1 MHz 10 WAS 1MHz ---- L.E. 04-14-00 20000410-2-07 ADDED IR & DWV. REVISED & ADDED NOTES. S.M. 12-01-05 20051128-1-18			--TOLERANCES-- Unless Otherwise Specified		Title BUSHING STYLE EMI FILTER							
			DECIMAL ± NOTED									
			ANGLES ± 		Drawn S.M. 10-29-98					Scale 5 X		
			TUSONIX TUCSON, ARIZONA		Approved J.Mc. 10-29-98							
A	4400-098											