


Precision Thin Film Chip Resistor Array Superior Moisture Resistivity



ACAS 0606 AT and ACAS 0612 AT precision automotive grade thin film chip resistor arrays with convex terminations combine the proven reliability of discrete chip resistors with the advantages of chip resistor arrays. Defined tolerance matching and TCR tracking make this product perfectly suited for applications with outstanding requirements towards stable fixed resistor ratios. Four equal resistor values or two pairs are available for the ACAS 0612 AT, whereas the ACAS 0606 AT is available either with two equal or two different resistor values. Find out more about Vishay's automotive grade product requirements at:

www.vishay.com/applications

FEATURES

- Superior moisture resistivity, $|\Delta R/R| < 0.5 \%$ (85 °C; 85 % RH; 1000 h)
- Rated dissipation P_{70} up to 125 mW per resistor
- ESD capability 1000 V, human body model
- TCR tracking down to 10 ppm/K (± 5 ppm/K) and tolerance matching down to 0.1 % ($\pm 0.05 \%$)
- AEC-Q200 qualified
- Compliant to RoHS directive 2002/95/EC

AUTOMOTIVE
GRADE



RoHS
COMPLIANT

APPLICATIONS

- Precision analogue circuits
- Voltage divider
- Feedback circuits
- Signal conditioning

TECHNICAL SPECIFICATIONS

DESCRIPTION	ACAS 0606 AT	ACAS 0612 AT
EIA size	0606	0612
Metric size	RR 1616MM	RR 1632M
Configuration, isolated	2 x 0603	4 x 0603
Design:		
All equal values (AE)	AE	AE
Two pairs of values (TP)		TP
Different values (DF)	DF	
Resistance values	47 Ω to 150 k Ω ⁽¹⁾	
Absolute tolerance	$\pm 0.5 \%$; $\pm 0.25 \%$	
Tolerance matching ⁽²⁾	0.5 % (equivalent to $\pm 0.25 \%$) 0.25 % (equivalent to $\pm 0.125 \%$) 0.1 % (equivalent to $\pm 0.05 \%$)	
Absolute temperature coefficient	± 50 ppm/K; ± 25 ppm/K	
Temperature coefficient tracking ⁽²⁾	50 ppm/K (equivalent to ± 25 ppm/K) 25 ppm/K (equivalent to ± 12.5 ppm/K) 15 ppm/K (equivalent to ± 7.5 ppm/K) 10 ppm/K (equivalent to ± 5 ppm/K)	
Max. resistance ratio R_{min}/R_{max}	1:20	
Rated dissipation: P_{70} ⁽³⁾		
Element	0.125 W	0.125 W
Package	0.2 W	0.4 W
Operating voltage, U_{max} AC/DC	75 V	
Permissible film temperature	155 °C	
Insulation voltage (U_{ins}) against ambient and between integrated resistors, continuous	75 V	

Notes

⁽¹⁾ Resistance values to be selected from E24 and E96.

⁽²⁾ In applications with defined resistance ratios like voltage dividers or feedback circuits, an array with a defined tracking of e.g. 10 ppm/K is required to replace discrete resistors with a temperature coefficient of resistance of ± 5 ppm/K. Furthermore, in order to achieve the same tolerance of $\pm 0.05 \%$ of individual resistors, an array requires a matching of 0.1 %.

⁽³⁾ Please refer to APPLICATION INFORMATION, see below.

APPLICATION INFORMATION

The power dissipation on the resistor generates a temperature rise against the local ambient, depending on the heat flow support of the printed-circuit board (thermal resistance). The rated dissipation applies only if the permitted film temperature is not exceeded. These resistors do not feature a limited lifetime when operated within the permissible limits.

MAXIMUM RESISTANCE CHANGE AT RATED POWER ⁽¹⁾				
DESCRIPTION	ACAS 0606 AT		ACAS 0612 AT	
Configuration, isolated	2 x 0603		4 x 0603	
Operation mode	Standard	Power	Standard	Power
Rated power per element, P_{70}	0.1 W	0.125 W	0.1 W	0.125 W
Rated power per package, P_{70}	0.15 W	0.2 W	0.3 W	0.4 W
Film temperature	125 °C	155 °C	125 °C	155 °C
Max. resistance change at P_{70}				
$\Delta R/R$ max., after:				
1000 h	$\pm 0.1 \%$	$\pm 0.25 \%$	$\pm 0.1 \%$	$\pm 0.25 \%$
8000 h	$\pm 0.25 \%$	$\pm 0.5 \%$	$\pm 0.25 \%$	$\pm 0.5 \%$
Max. relative resistance change (relative drift) at P_{70}				
$\Delta R/R$ max., after:				
1000 h	0.1 % ⁽²⁾	0.25 % ⁽³⁾	0.1 % ⁽²⁾	0.25 % ⁽³⁾
8000 h	0.25 % ⁽³⁾	0.5 % ⁽⁴⁾	0.25 % ⁽³⁾	0.5 % ⁽⁴⁾

Notes


⁽¹⁾ Figures are given for arrays with equal values, design type AE

⁽²⁾ Equivalent to $\pm 0.05 \%$


⁽³⁾ Equivalent to $\pm 0.125 \%$

⁽⁴⁾ Equivalent to $\pm 0.25 \%$

SKETCHES



ACAS 0606 AT



ACAS 0612 AT

Marking on ACAS 0606 AT: For types with different resistor values pin 1 is marked.

DESIGN		
TYPE	ACAS 0606 AT	ACAS 0612 AT
AE	$R_1 = R_2$	$R_1 = R_2 = R_3 = R_4$
TP		$R_1 = R_4 < R_2 = R_3$
DF	$R_1 < R_2$	

ACAS 0606 AT, ACAS 0612 AT - Precision

Vishay Beyschlag

Precision Thin Film Chip Resistor Array
Superior Moisture Resistivity



PART NUMBER AND PRODUCT DESCRIPTION (1)

PART NUMBER: ACASA1100A2200P5AT

A	C	A	S	A	1	1	0	0	A	2	2	0	0	P	5	A	T
MODEL	TERMINAL	SIZE	RESISTANCE VALUE (2)		ACCURACY GRADE (3)		RESISTANCE VALUE (2)		PACKAGING (4)		SPECIAL						
ACA	S = Convex square	N = 0606 A = 0612	3 digit resistance value R_1, R_4 1 digit multiplier		TCR, Tracking, Tolerance and Matching A, B, E, F J, K, N or P		3 digit resistance value R_2, R_3 1 digit multiplier		P1 P5		AT = Automotive						
			MULTIPLIER				MULTIPLIER										
			9 = $\times 10^{-1}$				9 = $\times 10^{-1}$										
			0 = $\times 10^0$				0 = $\times 10^0$										
			1 = $\times 10^1$				1 = $\times 10^1$										
			2 = $\times 10^2$				2 = $\times 10^2$										
			3 = $\times 10^3$				3 = $\times 10^3$										

PRODUCT DESCRIPTION: ACAS 0612 110R A 220R AT P5

ACA	S	0612	110R	A	220R	AT	P5
MODEL	TERMINAL	SIZE	RESISTANCE VALUE R_1, R_4 (2)	ACCURACY GRADE (3)	RESISTANCE VALUE R_2, R_3 (2)	SPECIAL	PACKAGING (4)
ACA = Chip Array	S = Convex square	0606 0612	110R = 110 Ω 1K1 = 1.1 k Ω 22K1 = 22.1 k Ω	TCR, Tracking, Tolerance and Matching A, B, E, F J, K, N or P	220R = 220 Ω 1K1 = 1.1 k Ω 22K1 = 22.1 k Ω	AT = Automotive	P1 P5

Notes

(1) Products can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION

(2) $R_1 = R_4 \leq R_2 = R_3$

(3) Please refer to table TEMPERATURE COEFFICIENT AND RESISTANCE RANGE, see below

(4) Please refer to table PACKAGING, see below

TEMPERATURE COEFFICIENT AND RESISTANCE RANGE

DESCRIPTION					RESISTANCE VALUE
ACCURACY GRADE	ABSOLUTE TCR	TCR TRACKING (5)	ABSOLUTE TOLERANCE	TOLERANCE MATCHING (5)	ACAS 0606 AT ACAS 0612 AT
A	± 25 ppm/K	10 ppm/K	± 0.25 %	0.1 %	47 Ω to 150 k Ω
B	± 25 ppm/K	10 ppm/K	± 0.5 %	0.25 %	47 Ω to 150 k Ω
E	± 25 ppm/K	15 ppm/K	± 0.25 %	0.1 %	47 Ω to 150 k Ω
F	± 25 ppm/K	15 ppm/K	± 0.5 %	0.25 %	47 Ω to 150 k Ω
J	± 25 ppm/K	25 ppm/K	± 0.25 %	0.1 %	47 Ω to 150 k Ω
K	± 25 ppm/K	25 ppm/K	± 0.5 %	0.25 %	47 Ω to 150 k Ω
N	± 50 ppm/K	25 ppm/K	± 0.5 %	0.5 %	47 Ω to 150 k Ω
P	± 50 ppm/K	50 ppm/K	± 0.5 %	0.5 %	47 Ω to 150 k Ω

Note

(5) Please refer to TECHNICAL SPECIFICATIONS, Note (2), see above



ACAS 0606 AT, ACAS 0612 AT - Precision

Precision Thin Film Chip Resistor Array
Superior Moisture Resistivity


Vishay Beyschlag

PACKAGING


MODEL	TAPE WIDTH	DIAMETER	PIECES	PITCH	PACKAGING CODE
					PAPER TAPE
ACAS 0606 AT	8 mm	180 mm/7"	1000	4 mm	P1
ACAS 0612 AT	8 mm	180 mm/7"	5000	4 mm	P5

DIMENSIONS

ACAS 0606 AT





ACAS 0612 AT



DIMENSIONS - chip resistor array, mass and relevant physical dimensions

TYPE	L (mm)	W (mm)	H (mm)	P (mm)	A ₁ (mm)	A (mm)	T ₁ (mm)	T ₂ (mm)	MASS (mg)
ACAS 0606 AT	1.5 ± 0.15	1.6 ± 0.15	0.45 ± 0.1	-	0.6 ± 0.1	0.4 ± 0.1	0.3 ± 0.15	0.4 ± 0.15	3.6
ACAS 0612 AT	1.5 ± 0.15	3.2 ± 0.15	0.45 ± 0.1	0.8 ± 0.1	0.6 ± 0.1	0.4 ± 0.1	0.3 ± 0.15	0.4 ± 0.15	6.8

PATTERN STYLES FOR CHIP RESISTOR ARRAYS



Dimensions in mm

RECOMMENDED SOLDER PAD DIMENSIONS FOR CHIP RESISTOR ARRAYS

TYPE	G (mm)	Y (mm)	X (mm)	U (mm)	Z (mm)	I (mm)	P (mm)
ACAS 0606 AT	0.7	0.7	0.64	-	2.1	0.3	0.8
ACAS 0612 AT	0.7	0.7	0.64	0.5	2.1	0.3	0.8

DESCRIPTION

The production of the components is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of metal alloy is deposited on a high grade (96 % Al_2O_3) ceramic substrate using a mask to separate the adjacent resistors and conditioned to achieve the desired temperature coefficient. Specially designed inner contacts are realized on both sides. A special laser is used to achieve the target value by smoothly cutting a meander groove in the resistive layer without damaging the ceramics.

The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure and optical inspection performed on 100 % of the individual chip resistors. Only accepted products are laid directly into the paper tape in accordance with **IEC 60286-3** ⁽³⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using reflow or vapour phase as shown in **IEC 61760-1** ⁽³⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions.

The suitability of conformal coatings, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system. The resistors are RoHS compliant; the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. The permitted storage time is 20 years, whereas the solderability is specified for 2 years after production or requalification. The immunity of the plating against tin whisker growth has been proven under extensive testing.

All products comply with the **GADSL** ⁽¹⁾ and the **CEPIC-EECA-EICTA** ⁽²⁾ list of legal restrictions on hazardous substances. This includes full compliance with the following directives:

- 2000/53/EC End of Vehicle life Directive (ELV) and Annex II (ELV II)
- 2002/95/EC Restriction of the use of Hazardous Substances directive (RoHS)
- 2002/96/EC Waste Electrical and Electronic Equipment Directive (WEEE)

APPROVALS

The chip resistor array is **AEC-Q200** qualified.

Where applicable, the resistors are tested in accordance with **EN 140401-801** which refers to **EN 60115-1** and **EN 140400**.


Notes

⁽¹⁾ Global Automotive Declarable Substance List, see www.gadsl.org

⁽²⁾ CEPIC (European Chemical Industry Council), EECA (European Electronic Component Manufacturers Association), EICTA (European trade organisation representing the information and communications technology and consumer electronics), see www.eicta.org → policy → environmental policy group → chemicals → jig → Joint Industry Guide (JIG-101 Ed 2.0)

⁽³⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents

FUNCTIONAL PERFORMANCE



For permissible resistance change please refer to table MAXIMUM RESISTANCE CHANGE AT RATED POWER, above

Derating



TESTS AND REQUIREMENTS

Essentially all tests are carried out in accordance with the following specifications:

EN 60115-1, Generic specification

EN 140400, Sectional specification

EN 140401-801, Detail specification

The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5202.

The tests are carried out under standard atmospheric conditions according to **IEC 60068-1** ⁽¹⁾, 5.3. Climatic category LCT/UCT/56 (rated temperature range: Lower Category Temperature, Upper Category Temperature; damp heat, long term, 56 days) is valid (LCT = - 55 °C/UCT = 125 °C).

Unless otherwise specified the following values apply:

Temperature: 15 °C to 35 °C

Relative humidity: 45 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar)

The requirements stated in the "Test Procedures and Requirements" table are based on the required tests and permitted limits of EN 140401-801 where applicable.

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 ⁽¹⁾ TEST METHOD	TEST	PROCEDURE	REQUIREMENTS ⁽²⁾ PERMISSIBLE CHANGE (ΔR)
			Stability for product types: ACAS 0606 AT ACAS 0612 AT	47 Ω to 150 k Ω 47 Ω to 150 k Ω
4.5	-	Resistance	-	$\pm 0.5 \% R$; $\pm 0.25 \% R$
4.8.4.2	-	Temperature coefficient	At (20/- 55/ 20) °C and (20/125/20) °C	± 50 ppm/K; ± 25 ppm/K
4.25.1	-	Endurance at 70 °C: Standard operation mode	$U = \sqrt{P_{70} \times R}$ or $U = U_{max.}$; 1.5 h on; 0.5 h off; 1000 h: Absolute Relative ⁽³⁾ 8000 h: Absolute Relative ⁽³⁾	$\pm (0.1 \% R + 0.05 \Omega)$ $0.1 \% R + 0.05 \Omega$ $\pm (0.25 \% R + 0.05 \Omega)$ $0.25 \% R + 0.05 \Omega$
		Endurance at 70 °C: Power operation mode	$U = \sqrt{P_{70} \times R}$ or $U = U_{max.}$; 1.5 h on; 0.5 h off; 1000 h: Absolute Relative ⁽³⁾ 8000 h: Absolute Relative ⁽³⁾	$\pm (0.25 \% R + 0.05 \Omega)$ $0.25 \% R + 0.05 \Omega$ $\pm (0.5 \% R + 0.05 \Omega)$ $0.5 \% R + 0.05 \Omega$
4.25.3	-	Endurance at upper category temperature	125 °C; 1000 h: Absolute Relative ⁽³⁾ 125 °C; 8000 h: Absolute Relative ⁽³⁾ 155 °C; 1000 h: Absolute Relative ⁽³⁾	$\pm (0.25 \% R + 0.05 \Omega)$ $0.25 \% R + 0.05 \Omega$ $\pm (0.5 \% R + 0.05 \Omega)$ $0.5 \% R + 0.05 \Omega$ $\pm (0.4 \% R + 0.05 \Omega)$ $0.4 \% R + 0.05 \Omega$

TEST PROCEDURES AND REQUIREMENTS

EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS (2) PERMISSIBLE CHANGE (ΔR)
			Stability for product types: ACAS 0606 AT ACAS 0612 AT	47 Ω to 150 k Ω 47 Ω to 150 k Ω
4.24	78 (Cab)	Damp heat, steady state	(40 $\pm$ 2) $^{\circ}$ C; 56 days; (93 $\pm$ 3) % RH	$\pm$ (0.25 % R + 0.05 Ω)
4.39	67 (Cy)	Damp heat, steady state, accelerated	(85 $\pm$ 2) $^{\circ}$ C (85 $\pm$ 5) % RH $U = 0.1 \times \sqrt{P_{70}} \times R$ ≤ 100 V; 1000 h	$\pm$ (0.5 % R + 0.05 Ω)
4.13	-	Short time overload (4)	$U = 2.5 \times \sqrt{P_{70}} \times R$ or $U = 2 \times U_{max.}$; 5 s	$\pm$ (0.1 % R + 0.01 Ω) no visible damage
4.40	-	Electrostatic discharge (Human body model) (4)	IEC 61340-3-1; 3 pos. + 3 neg. (equivalent to MIL-STD-883, Method 3015); 1000 V	$\pm$ (0.5 % R + 0.05 Ω)
4.19	14 (Na)	Rapid change of temperature	30 min at - 55 $^{\circ}$ C and 30 min at 125 $^{\circ}$ C; 1000 cycles	$\pm$ (0.25 % R + 0.05 Ω) no visible damage
4.18.2	58 (Td)	Resistance to soldering heat	Reflow method 2 (IR/forced gas convention); (260 $\pm$ 5) $^{\circ}$ C; (10 $\pm$ 1) s	$\pm$ (0.1 % R + 0.01 Ω) no visible damage
4.17.2	58 (Td)	Solderability	Solder bath method; SnPb; non-activated flux accelerated aging 4 h/155 $^{\circ}$ C (215 $\pm$ 3) $^{\circ}$ C; (3 $\pm$ 0.3) s	Good tinning ($\geq$ 95 % covered); no visible damage
			Solder bath method; SnAgCu; non-activated flux accelerated aging 4 h/155 $^{\circ}$ C (235 $\pm$ 3) $^{\circ}$ C; (2 $\pm$ 0.2) s	
4.32	21 (Ue ₃)	Shear (adhesion)	45 N	No visible damage
4.33	21 (Ue ₁)	Substrate bending	Depth 2 mm, 3 times	$\pm$ (0.1 % R + 0.01 Ω) no visible damage; no open circuit in bent position
4.35	-	Flammability	IEC 60695-11-5, needle flame test; 10 s	No burning after 30 s
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 to 2000 Hz; no resonance; amplitude $\leq$ 1.5 mm or $\leq$ 200 m/s ² ; 6 h	$\pm$ (0.1 % R + 0.01 Ω); no visible damage
4.7	-	Voltage proof	$U_{rms} = U_{ins}$ 60 $\pm$ 5 s; against ambient, between adjacent resistors	No flashover or breakdown

Notes

(1) The quoted IEC standards are also released as EN standards with the same number and identical contents

(2) Figures are given for arrays with equal values, design type AE

(3) Relative values are equivalent to the half of its value with $\pm$ symbol, i.e. 0.1 % is equivalent to $\pm$ 0.05 %

(4) For a single element



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk and agree to fully indemnify and hold Vishay and its distributors harmless from and against any and all claims, liabilities, expenses and damages arising or resulting in connection with such use or sale, including attorneys fees, even if such claim alleges that Vishay or its distributor was negligent regarding the design or manufacture of the part. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.