





LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			A	REVISED PER ECO-12-018102	17OCT2012	MGM	CT	
			B	ECO-13-004759	01APR2013	KG	DH	



- 1 MATERIAL:
CONTACT AND SHIELD: COPPER ALLOY
HOUSING AND CHICKLET: LCP, COLOR: BLACK
- 2 FINISH:
CONTACT: MATING AREA: 1.27µm MIN GOLD OVER
1.27µm MIN NICKEL
SHIELD: 1.27µm MIN NICKEL
- 3 FINISH:
COMPLIANT PIN AREA: 0.5µm MIN BRIGHT TIN LEAD OVER
1.27µm MIN NICKEL
- 4 FINISH:
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER
1.27µm MIN NICKEL
- 5 DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- 6 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- 7 REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 8 RECOMMENDED DIFFERENTIAL PAIR CONFIGURATION SHOWN.
THE CONNECTOR UTILIZES AN OPEN PIN FIELD AND
CAN BE LAID OUT IN A SINGLE-ENDED CONFIGURATION.



2	4	2102088-2
2	3	2102088-1
FINISH		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN D. BELACK 24NOV2010 CHK A. TSANG APVD W. McALONIS		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±0.13 1 PLC ±0.13 2 PLC ±0.05 3 PLC ±0.13 4 PLC ±0.05 ANGLES ±0.2°		Fortis Zd. 2-PAIR, 10-COLUMN, R/A RIGHT MODULE ASSEMBLY	
		PRODUCT SPEC 108-2409 APPLICATION SPEC 114-13267 WEIGHT ~6.98 g		SIZE CAGE CODE DRAWING NO	
MATERIAL		FINISH		RESTRICTED TO	
		-		A100779C-2102088	
Customer Drawing		SCALE 6:1		SHEET 1 OF 1 REV B	