


D


C

B

A




SEE SHEET 2 FOR HOLE PATTERN




SECTION L-L
SCALE 8:1

- 1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC. COLOR: BROWN.
- 2 CONTACT: PHOSPHOR BRONZE.
- 3 CONTACT FINISH: .000050 MIN NICKEL ALL OVER. .000030 MIN GOLD OVER NICKEL IN CONTACT AREA. .000100 MIN TIN-LEAD OVER NICKEL ON SOLDER TAILS.
- 4 METAL HOLD DOWN: BRASS
- 5 METAL HOLD DOWN FINISH: .000050 MIN NICKEL ALL OVER, .000150 MIN TIN-LEAD ALL OVER
- 6 DISTANCE FROM CONTACT POINT TO BOTTOM OF CARD SLOT.
- 7 AMP PART NUMBER, DATE CODE AND CSA LOGO MARKED IN APPROXIMATE AREA SHOWN.
- 8 DISTANCE FROM CONTACT POINT TO BOTTOM OF CARD SLOT.
- 9 PIN ONE IDENTIFIER NOTCH ONLY ON PART NUMBERS INDICATED.
- 10 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI


	.125	YES	B	2.350	2.310	3.14	.610	10	44	56	145020-8
	.140	YES	A	2.550	2.510	4.89	2.160	41	48	91	145020-7
OBSOLETE	.125	YES	A	2.550	2.510	4.89	2.160	41	48	91	145020-6
SUPERSEDED	.125	NO	D	1.800	1.760	2.59	.610	10	33	45	145020-5
OBSOLETE	.140	NO	C	2.200	2.160	4.34	1.960	37	41	80	145020-4
OBSOLETE	.100	NO	D	1.800	1.760	2.59	.610	10	33	45	145020-3
OBSOLETE	.100	YES	B	2.350	2.310	3.14	.610	10	44	56	145020-2
OBSOLETE	.100	YES	A	2.550	2.510	4.89	2.160	41	48	91	145020-1
	W	PIN ONE IDENTIFIER	HOLE PATTERN	V	U	T	S	Y	X	NO OF DUAL POSN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R. BROWN	4-20-93	tyco Electronics					
				CHK J. DIORAZO	4-28-93	Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. THUMMA		NAME		CONNECTOR ASSEMBLY DUAL POSITION .050 SERIES, STANDARD EDGE			
		0 PLC ± .0005 1 PLC ± .001 2 PLC ± .001 3 PLC ± .001 4 PLC ± .001		PRODUCT SPEC		108-14034					
		ANGLES ± .2°		APPLICATION SPEC		114-26012					
MATERIAL		FINISH		WEIGHT		A1 00779		145020			
						CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 2 REV N1			




RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN A
(CONNECTOR SIDE SHOWN)




RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN B
(CONNECTOR SIDE SHOWN)



RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN C
(CONNECTOR SIDE SHOWN)



RECOMMENDED CONNECTOR MOUNTING HOLE PATTERN D
(CONNECTOR SIDE SHOWN)



RECOMMENDED MATING BOARD EDGE CONFIGURATION