

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

CE

-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	BI	ECR-10-006880	11OCT2012	KG	DW

1. PACKAGED LOOSE PIECE.

2. DIMENSIONS ARE FOR REFERENCE ONLY.

3

FINISH: HARD ANODIZE.

4

FINISH: OLIVE DRAB ZINC.

5

FINISH: BLACK ZINC-NICKEL.

CRIMP SLEEVE

MAT'L: NICKEL-SILVER ALLOY

CRIMP SUPPORT

MAT'L: NICKEL-SILVER ALLOY

WASHER

MAT'L: STAINLESS STEEL

SEAL

MAT'L: EPDM RUBBER

EXTENSION

MAT'L: SEE TABLE

BOOT

MAT'L: EPDM RUBBER

ALUMINUM	7.5mm	3-1918932-2
	6.7mm	3-1918932-1
	6.0mm	3-1918932-0
	5.5mm	2-1918932-9
	5.0mm	2-1918932-8
	4.2mm	2-1918932-7
	3.6mm	2-1918932-6
	3.2mm	2-1918932-5
ALUMINUM	7.5mm	2-1918932-4
	6.7mm	2-1918932-3
	6.0mm	2-1918932-2
	5.5mm	2-1918932-1
	5.0mm	2-1918932-0
	4.2mm	1-1918932-9
	3.6mm	1-1918932-8
	3.2mm	1-1918932-7
NICKEL ALUMINUM BRONZE	7.5mm	1-1918932-6
	6.7mm	1-1918932-5
	6.0mm	1-1918932-4
	5.5mm	1-1918932-3
	5.0mm	1-1918932-2
	4.2mm	1-1918932-1
	3.6mm	1-1918932-0
	3.2mm	1918932-9
ALUMINUM	7.5mm	1918932-8
	6.7mm	1918932-7
	6.0mm	1918932-6
	5.5mm	1918932-5
	5.0mm	1918932-4
	4.2mm	1918932-3
	3.6mm	1918932-2
	3.2mm	1918932-1
EXTENSION MATERIAL	MAXIMUM CABLE DIAMETER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC

±

1 PLC

±

2 PLC

±

3 PLC

±

4 PLC

±

ANGLES

±

FINISH

3

4

DWN

27OCT2006

K. GLATFELTER

CHK

02JUN2008

D. WERTMAN

APVD

02JUN2008

D. WERTMAN

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

Customer Drawing

TE Connectivity

NAME

CABLE ADAPTER KIT, SEALED BLKHD, PRO BEAM JR.

SIZE

A2

CAGE CODE

00779

DRAWING NO

C-1918932

RESTRICTED TO

-

SCALE

2:1

SHEET

1

OF

1

REV

BI

1471-9 (3/11)