




- High-volume Vertical Display Mounting Applications
- Useful for Connection of Board-to-Board Jumpers and DIP Switches, as well as LED Devices



- **Optional Rail & Plating**
 - WR = Without Rails
 - TL = Sn/Pb
 - WRTL = Without Rails, Sn/Pb
- **Economy Version**
- **Display Angle**
- **Series**
- **Pin Count**
(See Table)

Technical drawing of a 15-pin connector assembly. The drawing includes a side view of the connector housing and a detailed view of the contact pins.

Dimensions (Inches [Millimeters]):

- "A" (Overall Length): .390 [9.91]
- "B" (Pin Pitch): .003 ± .08
- PIN #1 I.D. (Pin 1 Inner Diameter): .020 X .025 [.51 X .64]
- SEATING PLANE (Seating Plane)
- RAILS (Rails)
- Pin Diameter: .300 ± .003 [7.62 ± .08]
- Pin Length: .260 [6.60]
- Pin Angle: 90° ± 2° [3.81 ± .25]
- Pin Spacing: .150 ± .010
- Pin Diameter: .025 ± .002 [.64 ± .05]
- Pin Length: .100 ± .010 [2.54 ± .25]
- Pin Diameter: .280 [7.11]
- Pin Diameter: .006 ± .002 [.15 ± .05]
- Pin Diameter: .200 ± .003 [5.08 ± .08]
- Pin Diameter: .125 [3.18]
- Pin Diameter: .065 [1.65]
- Pin Diameter: .160 [4.06]

Formulas:

- "W" NO. OF PINS PER ROW x 0.100 [2.54]
- "X" (NO. OF PINS PER ROW - 1) x 0.100 [2.54]

CONTACT DETAIL

SEATING PLANE

TOL. NON-CUM

Body Style	Dim. "Y"	Dim. "Z"	Pin Count
A	0.450 [11.43]	0.300 [7.62]	8, 10
B	0.750 [19.05]	0.600 [15.24]	8, 10, 12, 14, 16
B	0.850 [21.59]	0.700 [17.78]	8, 10
B	0.950 [24.13]	0.800 [20.32]	8, 10, 12, 14, 16

13003
Rev. 6.1
1 of 1