

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT 2011APR

By - Tyco Electronics Japan G.K.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

C

REVISED

25APR11

MM

NY

CIRCUIT NO

DATE CODE

RETENTION REG

CONTACT TAIL

ROUND DIA3MIN 2PLACES

DIA2±0.05 2PLACES

OUTLINE OF HEADER HOUSING

ROW ID

20-∅0.8±0.05
DIA0.8±0.05 20PLACES


RECOMENDED PC BOARD HOLE PATTERN(TOL:±0.05)

PC BOARD THICKNESS:1.6±0.3

(CONNECTOR MOUNT SIDE)

SERIES MARK

LOGO MARK

1318127-2
9-1318127-2
(KEYING Y)
SCALE:2-1

NOTES

1. MATERIAL:HOUSING:GLASS FILLED THERMO PLASTIC
,POLYESTER(94V-0),
COLOR:1318127-1/-2 : BLACK
9-1318127-2 : NATURAL

TAB CONTACT:COPPER ALLOY

RETENTION LEG:BRASS

2. FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING
OVER Ni PLATING

3. FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL

Y	NATURAL	9-1318127-2
Y	BLACK	1318127-2
X	BLACK	1318127-1
KEY	COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN K.IKEDA 07DEC98

CHK N.MATSUBARA 07DEC98

APVD I.HASEGAWA 07DEC98

PRODUCT SPEC

108-5619

APPLICATION SPEC

114-5218

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME

DOUBLE ROW HEADER ASS'Y 20P ("V" TYPE)
<DYNAMIC D-2100D>

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-1318127

SCALE 1:1

SHEET 1 OF 1

REV C

10.7

13.2

1318127-1
(KEYING X)