




REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
F2	REVISED	PER ECR-15-006702	28JUL2015	NK PQ

- 1

MATERIAL:
HOUSING- NYLON UL94V-2 (BLUE).
CONTACTS- 0.30 [.012] THK COPPER ALLOY
DUAL PLATING : GOLD PLATE AREA, 0.00076 [.000030] GOLD OR 0.00008 [.000003] MIN GOLD FLASH OVER 0.00068 [.000027] PALLADIUM NICKEL, PER TE CONNECTIVITY'S DISCRETION, ALL SIDES, OVER NICKEL UNDERPLATE, .00127 [.000050] MIN, ALL SIDES AND ENTIRE LENGTH OF POST.
ONPOST, BRIGHT TIN-LEAD 0.00203[.000080] MIN THK 647010-2 THRU 1-647010-9 OR MATTE TIN 0.00203[.000080] MIN THK. FOR 3-647016-2 THRU 4-647010-9 ON WIRE SLOT, WITH NICKEL UNDERPLATE .00127[.000050] MIN THK ALL OVER.
- 2

CONTACTS ACCEPT 26 AWG (0.12 – 0.15 mm mm²) TIN PLATED SOLID,CONCENTRIC FUSED STRANDED, OR CONCENTRIC STRANDED (7 STRANDS) WIRE WITH 1.52 [.060] MAX INSULATION DIAMETER.
- 3

MATES WITH STANDARD MTA-100 CONNECTORS:
OF THE SAME CIRCUIT SIZES
WITH SIMILARLY PLATED CONTACTS
WITH POLARIZING TABS-CIRCUIT SIZES 4-19 ONLY
WITHOUT POLARIZING TABS-CIRCUIT SIZES 2 & 3.

DOES NOT MATE WITH MTA-100 CONNECTORS:
WITH POLARIZING TABS-CIRCUIT SIZES 2 & 3 ONLY.
(SEE DETAIL A)
WITH BLOCKED CIRCUITS -ALL CIRCUIT SIZES.
NOT RECOMMENDED FOR MATING WITH MTA-100 CONNECTOR WITHOUT POLARIZING TABS.
CIRCUIT SIZES 4-19.
- 4

ACCESSORIES:
REPLACEMENT IDC CONTACTS: 647030-2.
COVERS: SEE TABLE
- 5

QUANTITY OF CENTRALLY POSITIONED RAILS VARIES WITH CIRCUIT SIZE. (SEE TABLE)
LOCATION MAY DIFFER FROM EXAMPLE SHOWN.
- 6

DIMENSIONS IN BRACKETS ARE IN INCHES.
- 7


SIMILAR SIZED LOCK AND SINGLE TAB USED OR CIRCUITS 4 & 5.
- 8

QUANTITY OF GUSSET RIBS VARIES WITH CIRCUIT SIZE (SEE TABLE).
LOCATION MAY DIFFER FROM EXAMPLE SHOWN.
- 9

INNER END RAIL PAIR NOT PRESENT FOR CIRCUIT SIZES 2 OR 3.
- 10

CIRCUIT ID MAY APPEAR FULLY NUMBERED OR SHOWING LOCATION 1 ONLY DEPENDING ON CIRCUIT SIZE.
- 11

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 30-- -98	 TE Connectivity	
		CHK R. SWING 30-- -98		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J. FLIJS 30-- -98	NAME	MTA-100 POSTED CONNECTOR ASSEMBLY, CLOSED END, 26 AWG
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.007] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC	APPLICATION SPEC	
MATERIAL	FINISH	WEIGHT	SIZE A1	CAGE CODE 00779
		CUSTOMER DRAWING	DRAWING NO 647010	RESTRICTED TO
		SCALE 5:1	SHEET 1	OF 2
		REV F2		

REVISIONS					
P	LTR	DESCRIPTION	DATE	OWN	APVD
—	—	SEE SHEET 1	—	—	—

1-640642-9	1-643077-9	4	2	45.72	1.800	48.95	1.927	50.80	2.000	19	4-647010-9
1-640642-8	1-643077-8	4	2	43.18	1.700	46.41	1.827	48.26	1.900	18	4-647010-8
1-640642-7	1-643077-7	4	2	40.64	1.600	43.86	1.727	45.72	1.800	17	4-647010-7
1-640642-6	1-643077-6	4	2	38.10	1.500	41.32	1.627	43.18	1.700	16	4-647010-6
1-640642-5	1-643077-5	4	2	35.56	1.400	38.78	1.527	40.64	1.600	15	4-647010-5
1-640642-4	1-643077-4	4	2	33.02	1.300	36.24	1.427	38.10	1.500	14	4-647010-4
1-640642-3	1-643077-3	4	2	30.48	1.200	33.70	1.327	35.56	1.400	13	4-647010-3
1-640642-2	1-643077-2	2	1	27.94	1.100	31.16	1.227	33.02	1.300	12	4-647010-2
1-640642-1	1-643077-1	2	1	25.40	1.000	28.62	1.127	30.48	1.200	11	4-647010-1
1-640642-0	1-643077-0	2	1	22.86	.900	26.08	1.027	27.94	1.100	10	4-647010-0
640642-9	643077-9	2	1	20.32	.800	23.54	.927	25.40	1.000	9	3-647010-9
640642-8	643077-8	2	0	17.78	.700	21.00	.827	22.86	.900	8	3-647010-8
640642-7	643077-7	0	0	15.24	.600	18.46	.727	20.32	.800	7	3-647010-7
640642-6	643077-6	0	0	12.70	.500	15.92	.627	17.78	.700	6	3-647010-6
640642-5	643077-5	0	0	10.16	.400	13.38	.527	15.24	.600	5	3-647010-5
640642-4	643077-4	0	0	7.62	.300	10.84	.427	12.70	.500	4	3-647010-4
640642-3	643077-3	0	0	5.08	.200	8.30	.327	10.16	.400	3	3-647010-3
—	643077-2	0	0	2.54	.100	5.76	.227	7.62	.300	2	3-647010-2
1-640642-9	1-643077-9	4	2	45.72	1.800	48.95	1.927	50.80	2.000	19	1-647010-9
1-640642-8	1-643077-8	4	2	43.18	1.700	46.41	1.827	48.26	1.900	18	1-647010-8
1-640642-7	1-643077-7	4	2	40.64	1.600	43.86	1.727	45.72	1.800	17	1-647010-7
1-640642-6	1-643077-6	4	2	38.10	1.500	41.32	1.627	43.18	1.700	16	1-647010-6
1-640642-5	1-643077-5	4	2	35.56	1.400	38.78	1.527	40.64	1.600	15	1-647010-5
1-640642-4	1-643077-4	4	2	33.02	1.300	36.24	1.427	38.10	1.500	14	1-647010-4
1-640642-3	1-643077-3	4	2	30.48	1.200	33.70	1.327	35.56	1.400	13	1-647010-3
1-640642-2	1-643077-2	2	1	27.94	1.100	31.16	1.227	33.02	1.300	12	1-647010-2
1-640642-1	1-643077-1	2	1	25.40	1.000	28.62	1.127	30.48	1.200	11	1-647010-1
1-640642-0	1-643077-0	2	1	22.86	.900	26.08	1.027	27.94	1.100	10	1-647010-0
640642-9	643077-9	2	1	20.32	.800	23.54	.927	25.40	1.000	9	647010-9
640642-8	643077-8	2	0	17.78	.700	21.00	.827	22.86	.900	8	647010-8
640642-7	643077-7	0	0	15.24	.600	18.46	.727	20.32	.800	7	647010-7
640642-6	643077-6	0	0	12.70	.500	15.92	.627	17.78	.700	6	647010-6
640642-5	643077-5	0	0	10.16	.400	13.38	.527	15.24	.600	5	647010-5
640642-4	643077-4	0	0	7.62	.300	10.84	.427	12.70	.500	4	647010-4
640642-3	643077-3	0	0	5.08	.200	8.30	.327	10.16	.400	3	647010-3
—	643077-2	0	0	2.54	.100	5.76	.227	7.62	.300	2	647010-2
DUST COVER	STRAIN RELIEF COVERS	QTY OF GUSSET RIBS	QTY OF CENTRAL RAILS	MM	IN	MM	IN	MM	IN	NO. OF CIRCUITS	PART NO
4	ACCESSORIES	8	5	C		B		A			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC

± -
± -
± -
± -
± -

ANGLES
FINISH

± -
± -

DWN
B. LEWIS
30-- -98

CHK
R. SWING
30-- -98

APVD
J. ELIUS
30-- -98

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

NAME

MTA-100 POSTED CONNECTOR ASSEMBLY, CLOSED END, 26 AWG

SIZE
A1

CAGE CODE
00779

DRAWING NO
647010

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE
1:1

SHEET
2

OF
2

REV
F2

TE Connectivity

4805 (1/15)