


NPN General Purpose Transistor

MMBTA13/MMBTA14

FEATURES

- Epitaxial planar die construction.
- Complementary PNP type available (MMBTA63/MMBTA64).
- High current gain.



APPLICATIONS

- Ideal for medium power amplification and switching

ORDERING INFORMATION

Type No.	Marking	Package Code
MMBTA13	K2D	SOT-23
MMBTA14	K3D	SOT-23

MAXIMUM RATING @ Ta=25°C unless otherwise specified

Symbol	Parameter	Value	UNIT
V_{CBO}	collector-base voltage	MMBTA13	V
		MMBTA14	
V_{CEO}	collector-emitter voltage	MMBTA13	V
		MMBTA14	
V_{EBO}	emitter-base voltage	10	V
I_C	collector current (DC)	0.3	A
P_C	Collector dissipation	0.35	W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	357	°C/W
T_j, T_{stg}	junction and storage temperature	-55-150	°C

NPN General Purpose Transistor

MMBTA13/MMBTA14

ELECTRICAL CHARACTERISTICS @ Ta=25°C unless otherwise specified

Symbol	Parameter	Test conditions	MIN.	MAX.	UNIT
$V_{(BR)CBO}$	Collector-base breakdown voltage MMBTA13 MMBTA14	$I_C=100\mu A, I_E=0$	30 30	-	V
$V_{(BR)CEO}$	Collector-emitter breakdown voltage MMBTA13 MMBTA14	$I_C=0.1mA, I_B=0$	30 30	-	V
$V_{(BR)EBO}$	Emitter-base breakdown voltage	$I_E=100\mu A, I_C=0$	10	-	V
I_{CBO}	collector cut-off current	$I_E = 0; V_{CB} = 30V$	-	0.1	μA
I_{CEO}	collector cut-off current	$I_E = 0; V_{CE} = 10V$	-	0.1	μA
h_{FE}	DC current gain MMBTA13 MMBTA14 MMBTA13 MMBTA14	$V_{CE} = 5V; I_C = 10mA$ $V_{CE} = 5V; I_C = 10mA$ $V_{CE} = 5V; I_C = 100mA$ $V_{CE} = 5V; I_C = 100mA$	5000 10000 10000 20000	-	
$V_{CE(sat)}$	collector-emitter saturation voltage	$I_C = 100mA; I_B = 0.1mA$	-	1.5	V
f_T	transition frequency	$I_C = 10mA; V_{CE} = 5.0V;$ $f = 100MHz$	125	-	MHz

PACKAGE OUTLINE


Plastic surface mounted package

SOT-23

SOT-23		
Dim	Min	Max
A	2.85	2.95
B	1.25	1.35
C	1.0Typical	
D	0.37	0.43
E	0.35	0.48
G	1.85	1.95
H	0.02	0.1
J	0.1Typical	
K	2.35	2.45
All Dimensions in mm		

NPN General Purpose Transistor

MMBTA13/MMBTA14

SOLDERING FOOTPRINT

Unit : mm

PACKAGE INFORMATION

Device	Package	Shipping
MMBTA13/MMBTA14	SOT-23	3000/Tape&Reel