



General ordering data

Order No.	0443720000
Part designation	SAK 10/35 KRG
Version	Feed-through terminal, 10 mm ² , Screw connection, KrG, Medium yellow, TS 35
EAN	4008190183899
Qty.	100 pc(s).

Product notes

Note, ordering data	A higher torque of 2 to 2.4 Nm is necessary when using H07V-R16 and AWG 6 conductors.
Note, technical data	When used with twin ferrules ZH 0.5 - ZH 4, the rated voltage is 690 V.

PT OKIECEEx/ATEX rating data

EU-type examination certificate	KEMA97ATEX1798U
Download, German	KEMA97ATEX1798U_d.pdf
Download English	KEMA97ATEX1798U_e.pdf
IECEEx Certificate of Conformity	IECEXKEM06.0014U
ATEX voltage	550 V
ATEX current	50 A
ATEX conductor cross-section	10 mm ²
IECEEx voltage	550 V
IECEEx current	50 A
IECEEx conductor cross-section	10 mm ²
Voltage when using cross-connections	CrossConnectionGuide.pdf
Operating temperature range	Einsatztemperaturbereich siehe EG-Baumusterprüfbescheinigung/IECEEx-Certificate of Conformity
Marking EN 60079-7	Ex e II
Marking ATEX Directive 94/9/EC	Ex II 2 G D

Additional technical data

Colour of insulating material	Medium yellow
Connection direction	on side
End plate required	Yes
Explosion-tested version "Ex e"	No
Installation advice	TS 35
Insulating material	KrG
Levels cross-connected internally	No
No. of identical terminals	1

Additional technical data

No. of levels	1
No. of terminal strips per level	2
Open sides	right
Operating temperature range	- 60 °C, + 130 °C
Type of connection	Screwed
Type of mounting	Snap-on
UL 94 flammability rating of insulation material	5VA
Version	Feed-through terminal

CSA rating data

Voltage (CSA)	600 V
CSA current	65 A
Min. cross-section (CSA)	AWG 16
Max. cross-section (CSA)	AWG 6

Conductors for clamping (additional connection)

Flexible with ferrule, min. (DIN 46228 pt 1)	1.5 mm ²
Flexible with ferrule, max. (DIN 46228 pt 1)	10 mm ²

Conductors for clamping (rated connection)

Clamping range, min.	1.5 mm ²
Clamping range, max.	16 mm ²
Type of connection	Screw connection
2nd type of connection	screwed
Connection direction	on side
No. of connections	2
Stripping length	12 mm
Clamping screw	M 4
Blade size	1.0 x 5.5 mm
Tightening torque range	2.0...4.0 Nm
Torque level with DMS electric screwdriver	4
Gauge to IEC 60947-1	B6
Solid, min.	1.5 mm ²
Solid, max.	10 mm ²
Stranded, min.	1.5 mm ²
Stranded, max.	16 mm ²
Flexible, min.	1.5 mm ²
Flexible, max.	16 mm ²
Flexible with ferrule, min. (DIN 46228/1)	1.5 mm ²
Flexible with ferrule, max. (DIN 46228/1)	10 mm ²
Flexible, min., ferrule with plastic collar (DIN 46228 pt 4)	1.5 mm ²
Flexible, max., ferrule with plastic collar (DIN 46228 pt 4)	10 mm ²
Twin wire-end ferrule, min.	0.75 mm ²
Twin wire end ferrule, max.	6 mm ²
AWG conductor size, min.	AWG 14
AWG conductor size, max.	13.3 mm ²

Dimensions

Width	10 mm
Height of lowest version	51.5 mm
Length	45 mm
TS 35 offset	22 mm

Disconnect terminals

Torque level with DMS electric screwdriver	4
--	---

Rating data

Rated cross-section	10 mm ²
Rated voltage	800 V
Rated impulse voltage	8 kV
Rated current	57 A
Standards	IEC 60947-7-1
Current with max. conductor	76 A
Pollution severity	3

UL rating data

Voltage (UL)	600 V
Current (UL)	60 A
Min. cross-section (UL)	AWG 14
Max. cross-section (UL)	AWG 6

Approvals

Approvals institutes



Downloads

STEP	0443720000_06061_SAK_10-35_KRG_STP.stp
------	--

Classifications

ETIM 2.0	EC000897
ETIM 3.0	EC000897
eClass 4.1	27-14-11-20
eClass 5.0	27-14-11-20
eClass 5.1	27-14-11-20

Similar products

Order No.	Part designation	Version
0443770000	SAK 10/35 KRG/BL	Feed-through terminal, 10 mm ² , Screw connection, KrG, blue, TS 35