



(1,27 mm) .050"

CLP-107-02-F-D-P

CLP-115-02-L-D

CLP-130-02-L-D

CLP-116-02-F-DH

CLP SERIES

# LOW PROFILE DUAL WIPE SOCKET

## SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?CLP](http://www.samtec.com?CLP)

### Insulator Material:

Black Liquid Crystal Polymer

### Contact Material:

Phosphor Bronze

### Plating:

Sn or Au over

50µ" (1,27 µm) Ni

### Current Rating (CLP/FTSH):

3.3 A per pin

(1 pin powered per row)

### Voltage Rating:

240 VAC/340 VDC

### Operating Temp Range:

-55°C to +125°C

### Contact Resistance:

10 mΩ

### Insertion Depth:

Top Entry = (1,40 mm) .055"

minimum, Bottom Entry =

(2,41 mm) .095" minimum

plus board thickness

DH Entry = (2,31 mm) .091"

to (2,67 mm) .105"

### Insertion Force:

(Single contact only)

3.8 oz (1,05 N) average

### Normal Force:

60 grams (0,59 N) average

### Withdrawal Force:

(Single contact only)

2 oz (0,56 N) average

### Max Cycles:

100 with 10µ" (0,25 µm) Au

### RoHS Compliant:

Yes

### Processing:

Lead-Free Solderable:

Yes

### SMT Lead Coplanarity:

(0,10 mm) .004" max (02-35)

(0,15 mm) .006" max (36-50)

Mates with:  
FTSH, FTS, FW

## APPLICATIONS

CLP FTSH

HORIZONTAL

PASS-THRU


High reliability  
Tiger Claw™  
contacts

(1,27 mm x 1,27 mm)  
.050" x .050"  
micro pitch

Low Profile  
(2,21 mm)  
.087"

Surface  
Mount

Suitable for pass-through  
applications



## RECOGNITIONS

For complete scope of recognitions see [www.samtec.com/quality](http://www.samtec.com/quality)



FILE NO. E111594

## ALSO AVAILABLE (MOQ Required)

- Single row
  - Other platings
- Contact Samtec.

**Note:** Some sizes, styles and options are non-standard, non-returnable.