

- 1

ZINC.
- 2

STAINLESS STEEL.
- 3




TO ASSEMBLE JACKSCREW REFER TO INSTRUCTION SHEET #1189.
- 4

HOLE CENTRALLY LOCATED WITHIN ± 0.07 [.003] OF THE 5.54 [.218] DIA AND THE 2.77/2.84 [.109/.112] DIA CENTER LINES.
- 5


CHROMATE CONVERSION, CLEAR.
- 7

NON-HEXAVALENT CHROMATE COATING ON JACKSCREW BODY.
- 8

SPECIAL PACKAGING - ONE UNASSEMBLED UNIT PER BAG



OBSOLETE	87	-201414-5-
	7	201414-4
	7	201414-1
NOTES		PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.FOLTZ 10/18/94	 TE Connectivity				
		CHK R.STONE 11/07/94					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME JACKSCREW KIT, UNASSEMBLED, FEMALE, M SERIES			
		APVD					
		PRODUCT SPEC					
		APPLICATION SPEC					
MATERIAL JACKSCREW BODY:  JACKSCREW TIP:  PIN: 		FINISH JACKSCREW BODY:  PIN: PASSIVATED		SIZE A1	CAGE CODE 00779	DRAWING NO 201414	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1	REV M	