



LOC
IRDIST
-

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
J		FIRST ISSUE	02MAY2007	HY	GT
J1		ADDED WIRE & INSULATION RANGE 02MAY07 HY		GT	
J2		REVISED PER ECO-09-026346	25NOV09	KK	AEG
J3		INSULATION BARREL WIDTH CORRECTED	20MAR12	PKS	RRP
J4		REVISED PER ECR-15-016344	09NOV15	L.P	T.D

SEC: A-A

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI

1 OBSOLETE	6-160555-0	TIN LEAD	PHOSPH. BRONZE	5-160556-5	0
	5-160555-4	PLAIN	PHOSPH. BRONZE	5-160556-4	0
1 OBSOLETE	5-160555-3	SILVER PLATED	BRASS	5-160556-3	0
	5-160555-2	TIN PLATED	BRASS	5-160556-2	0
	5-160555-1	PLAIN	BRASS	5-160556-1	0
1 OBSOLETE	0-160484-8	TIN LEAD	BRASS	0-160539-7	-
	0-160484-7	PRE-TIN PLATED	PHOSPH. BRONZE	0-160539-6	-
	0-160484-6	TIN PLATED	PHOSPH. BRONZE	0-160539-5	-
	0-160484-3	SILVER PLATED	BRASS	0-160539-3	J
OBSOLETE	0-160484-4	TIN PLATED	BRASS	0-160539-2	J
	0-160484-1	PLAIN	BRASS	0-160539-1	J
	STRIP FORM	FINISH	MATERIAL	P/N	REV

WIRE RANGE 0,5-1,0 mm².
INSULATION RANGE 2,0-2,5 mm.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN H. Yeali CHK - APVD G. Turco PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING	02MAY2007	STE TE Connectivity	
DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.3 2 PLC ±0.3 3 PLC ±0.3 4 PLC ±0.3 ANGLES ±1° FINISH -		NAME FASTON Connector, 2.8 mm series RECEPTACLE CONTACT LOOSE PIECE VERSION		RESTRICTED TO	
MATERIAL SEE TABLE		SIZE A300779		CAGE CODE C=160539	DRAWING NO - REV J4