

LOC		DIST		REVISIONS				
AJ		00		REV	PER	ECO	DATE	APVD
				Y	REV	PER	ECO	08-009474

- 1

POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:NATURAL
- 2

POLYESTER PBT PER MIL-M-24519, TYPE GPT-15F, UL94V-O RATED, COLOR:BLACK
- 3

POLYMETHYLPENTENE, GENERAL PURPOSE.
- 4

ZINC PER QQ-Z-363.
- 5

PHOSPHOR BRONZE PER QQ-B-750.
- 6

BRASS PER ASTM-B-453.
- 7

NICKEL PLATE PER QQ-N-290, 3.81 μ m [.000150] MINIMUM THICK.
- 8





TIN PLATE PER ASTM-B-545. 3.81 μ m [.000150] MINIMUM THICK.
- 9

GOLD PLATE PER MIL-G-45204, 0.76 μ m [.000030] MINIMUM THICK.
- 10


SILVER PLATE PER QQ-S-365, 2.54 μ m [.000100] MINIMUM THICK.
- 11

TIN PLATE PER ASTM-B-545, 3.81 μ m [.000150] MINIMUM THICK.
12.

SEE INSTRUCTION SHEET 2769.



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

OBSOLETE	1	1	1	1	9-226993-0
	8	8	9	2	226993-6
SUPERSEDED BY 226993-3	8	8	10	1	226993-5
SUPERSEDED BY 226993-6	8	8	10	2	226993-4
OBSOLETE	8	8	9	1	226993-3
OBSOLETE	8	8	8	1	226993-2
	8	8	8	1	226993-1
GROUND POST PLATING	CONTACT POST PLATING	CONTACT PLATING	HOUSING MATERIAL	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. SCOTT 6-11-91	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK J. LIPPERT 8-07-91	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. LIPPERT	PRODUCT SPEC	
0 PLC ± -			108-12078	
1 PLC ± -			APPLICATION SPEC	
2 PLC ± 0.20 [.008]			SIZE	
3 PLC ± -			CAGE CODE	
4 PLC ± -			DRAWING NO	
ANGLES ± -			RESTRICTED TO	
MATERIAL		WEIGHT	A1 00779 226993	
FINISH			CUSTOMER DRAWING	