



UBP600-3-1

0.6 m | 2.0 ft Flat Panel Directional Antenna for Unlicensed Band, single-polarized, 3.300–3.800 GHz, Type N Female, gray antenna, plastic gray radome without flash, standard pack—one-piece reflector (pack of 1)

General Specifications

Packing	Standard pack
Radome Color	Gray
Radome Material	UV Protected Plastic
Reflector Construction	One-piece reflector
Antenna Input	N Female
Antenna Color	Gray
Antenna Type	UB - Directional Antenna for Unlicensed Band, single-polarized
Diameter, nominal	0.6 m 2 ft
Flash Included	No
Includes	Mounting kit
Package Quantity	1
Polarization	Single

Electrical Specifications

Beamwidth, Horizontal	8.0 °
Beamwidth, Vertical	8.0 °
Cross Polarization Discrimination (XPD)	25 dB
Electrical Compliance	CE ETSI 302 085 V1.1.2 (2001-02) Class TS 1
Front-to-Back Ratio	35 dB
Gain, Low Band	23.5 dBi
Gain, Mid Band	24.0 dBi
Gain, Top Band	24.5 dBi
Operating Frequency Band	3.300 – 3.800 GHz
Return Loss	10.2 dB
VSWR	1.90

Mechanical Specifications

Fine Elevation Adjustment	±10°
Mounting Pipe Diameter	25 mm–76 mm 1 in–3 in
Net Weight, per unit with mounting kit	7 kg 16 lb
Side Struts, Included	0
Side Struts, Optional	0
Wind Velocity Operational	160 km/h 99 mph
Wind Velocity Survival Rating	220 km/h 137 mph

Product Specifications

COMMSCOPE®

UBP600-3-1


POWERED BY

 ANDREW®

Wind Forces At Wind Velocity Survival Rating

Angle α for MT Max	4 °
Axial Force (FA)	1039 N 234 lbf
Side Force (FS)	88 N 20 lbf
Twisting Moment (MT)	146 N•m
Weight with 1/2 in (12 mm) Radial Ice	16 kg 35 lb
Zcg with 1/2 in (12 mm) Radial Ice	140 mm 6 in
Zcg without Ice	134 mm 5 in


Wind Forces At Wind Velocity Survival Rating Image



Packed Dimensions

Gross Weight, Packed Antenna	10.0 kg 22.0 lb
Height	160.0 mm 6.3 in
Length	830.0 mm 32.7 in
Volume	96.3 m³
Width	725.0 mm 28.5 in

Antenna Dimensions And Mounting Information

**Dimensions in Inches (mm)**

Antenna Size, ft(m)	A	B	C
2 (0.6)	23.6 (600)	5 (126.8)	4.9 (125)

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2008

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



* Footnotes

Axial Force (FA)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Cross Polarization Discrimination (XPD)

The difference between the peak of the co-polarized main beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.

Front-to-Back Ratio

Denotes highest radiation relative to the main beam, at $180^\circ \pm 40^\circ$, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.

Gain, Mid Band

For a given frequency band, gain is primarily a function of antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the measured antenna patterns.

Operating Frequency Band

Bands correspond with CCIR recommendations or common allocations used throughout the world. Other ranges can be accommodated on special order.

Packing

Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wire-bound crates (dependent on

Product Specifications

COMMSCOPE®

UBP600-31

POWERED BY



Return Loss

product). For your convenience, Andrew offers heavy duty export packing options.

Side Force (FS)

The figure that indicates the proportion of radio waves incident upon the antenna that are rejected as a ratio of those that are accepted.

Twisting Moment (MT)

Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

VSWR

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Wind Velocity Operational

Maximum; is the guaranteed Peak Voltage-Standing-Wave-Ratio within the operating band.

The wind speed where the antenna deflection is equal to or less than 0.1 degrees. In the case of ValuLine antennas, it is defined as a maximum deflection of 0.3 x the 3 dB beam width of the antenna.

Wind Velocity Survival Rating

The maximum wind speed the antenna, including mounts and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified amount of radial ice.