

## Housing - HC-B 32-TFQ-80/O1PG21S - 1675078

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Sleeve housing, for double locking latch, height 80 mm, without screw connection, 1x Pg21, lateral cable entry



### Key commercial data

|                                      |           |
|--------------------------------------|-----------|
| Packing unit                         | 1 PCE     |
| Weight per Piece (excluding packing) | 502.2 GRM |
| Custom tariff number                 | 85389099  |
| Country of origin                    | Germany   |

### Technical data

#### Dimensions

|        |       |
|--------|-------|
| Height | 80 mm |
| Width  | 79 mm |
| Length | 94 mm |

#### Ambient conditions

|                                      |                   |
|--------------------------------------|-------------------|
| Degree of protection of housing (IP) | IP65              |
| Ambient temperature (operation)      | -40 °C ... 125 °C |

#### General

|                              |                                      |
|------------------------------|--------------------------------------|
| Note                         | For contact inserts HC-B32, DD144, M |
| Design                       | B32                                  |
| Housing type                 | Sleeve housings                      |
| Locking type                 | For double locking latch             |
| No. of cable exits           | 1                                    |
| Cable exit                   | Lateral                              |
| Screw connection             | None                                 |
| Type of the screw connection | 1x Pg21                              |

## Housing - HC-B 32-TFQ-80/O1PG21S - 1675078

### Technical data

#### General

|                          |                     |
|--------------------------|---------------------|
| Housing material         | Aluminum die-cast   |
| Housing surface material | Powder-coated, gray |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000437 |
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11     | 31261502 |
| UNSPSC 12.01  | 31261502 |
| UNSPSC 13.2   | 31261502 |

### Approvals

#### Approvals

---

Approvals

GOST

---

Ex Approvals

---

Approvals submitted

## Housing - HC-B 32-TFQ-80/O1PG21S - 1675078

### Approvals

---

#### Approval details



### Drawings

Dimensioned drawing

