


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT INVENTORY NUMBERING SYSTEM



PANDUIT PART NUMBER	Min. Exp. I.D In. (mm)	Max. Rec. I.D In. (mm)	NOMINAL REC WALL THICKNESS In. (mm)
HST0.4 - - - - (Y)	0.400 (10.2)	0.160 (4.1)	0.08 (2.0)
HST0.8 - - - - (Y)	0.750 (19.1)	0.220 (5.6)	0.09 (2.3)
HST1.1 - - - - (Y)	1.100 (27.9)	0.375 (9.5)	0.12 (3.0)
HST1.5 - - - - (Y)	1.500 (38.1)	0.500 (12.7)	0.16 (4.1)
HST2.0 - - - - (Y)	2.000 (50.8)	0.666 (16.9)	0.16 (4.1)
HST2.7 - - - - (Y)	2.700 (68.6)	.870 (22.1)	0.16 (4.1)
HST3.0 - - - - -	3.000 (76.2)	1.000 (25.4)	0.16 (4.1)
HST3.5 - - - - (Y)	3.500 (88.9)	1.200 (30.5)	0.16 (4.1)

(D) (D) (D) (D) (D) (C) (F) (C)

EXPANDED INSIDE DIAMETER TUBING
THICK WALL, ADHESIVE LINED HEAT SHRINK TUBING.

NOTES:

- 1. APPROXIMATE SHRINK RATIO: 3:1 (EXPANDED: RECOVERED 1D)
- 2. SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO TABLE 1 FOR THE EXACT MINIMUM EXPANDED AND MAXIMUM RECOVERED I.D.'S.
- 3. MATERIAL: CROSSLINKED POLYOLEFIN
- 4. COLOR: BLACK AND RED
- 5. "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE.)"
- 6. ALL PARTS ARE ROHS COMPLIANT

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
--	----	--	--	1 ADDED NOTE #6 H CHANGED Y:1 (ROHS COMPLIANT) TO INTERNAL CODE F PUT HST3.0 BACK ON DRAWING				
3	2/25/11	LEF		ADDED Y:ROHS ADDED LINES HST2.7 & 3.5 DIM. CHANGES REMOVED HST 3.0 LINE	GB0239KM	3	RAMI	
--	----	--	--					
2	10/12/10	LEF			GB0239KM	2	RAMI	

DIMENSIONS IN BRACKETS ARE METRIC (mm)

CAD FILENAME/LAYERS

G03597HN_DC_GB0239KM/03

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

HST THICK WALL ADHESIVE LINED HEAT SHRINK

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

DATE

10/12/10

CHK'D

JVL

MAT'L:

SEE NOTES

DRAWING NO.

GB0239KM

DWG

A

SIZE