



Power Cord, C13 to C14, 2.5m

Part Number: AP9870



Output

Maximum Total Current Draw per Phase

10A

Output Connections

(1) IEC 320 C13



Overload Protection

No

Input

Input Frequency

50/60 Hz

Input Connections

IEC-320 C14

Cord Length

2.5 meters

Number of Power Cords

1

Acceptable Input Voltage

90-250 VAC

Maximum Line Current per phase

10A

Maximum Input Current per phase

10A

Physical

Net Weight

0.23 KG

Maximum Height

38.00 mm

Maximum Width

76.00 mm

Maximum Depth

203.00 mm

Shipping Weight

0.30 KG

Shipping Height

51.00 mm

Shipping Width

102.00 mm

Shipping Depth

203.00 mm

Color

Black

Units per Pallet

600.00

Environmental

Operating Environment

0 - 45 °C

Operating Relative Humidity

0 - 95%

Operating Elevation

0-3000 meters
Storage Temperature
-25 - 65 °C
Storage Relative Humidity
0 - 95%
Storage Elevation
0-15000 meters

Conformance

Regulatory Approvals
CSA,UL Listed,VDE
Standard Warranty
2 years repair or replace
Environmental Compliance
RoHS

*Except where noted, all prices are Estimated Resale Price (ERP) - Without Tax/VAT. Pricing in other locations and sites may vary.

[Copyright](#) © American Power Conversion Corp., all rights reserved

[About APC](#)[About Schneider Electric](#)[Investors](#)[Job Seekers](#)[Press](#)[Feedback](#)[Contact](#)[Privacy Policy](#)