

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F004 * Effective: 12/21/98 * DCP No: 680						
DCP #	REV	DESCRIPTION			DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	A	Redrawn in Autocad			JAP	12/6/01				
1199	B	Redrawn and Renamed			JWM	11/9/01	JC	11/26/01	JC	11/26/01


NOTES:

MATERIAL:


1. ELECTRO-TIN PLATED COPPER WITH NYLON 6/6 FULL SLEEVE.
2. FLAMMABILITY: UL94V-2
3. VOLTAGE RATING: 600 V
4. OPERATING TEMP: -40°F(40°C) TO 167°F(75°C)




OSHA
Acceptable






Style 1



Style 2



Style 3



PART NUMBER	WIRE RANGE (AWG)	MATES WITH MALE TAB WIDTH (W) X THICKNESS	L	E	B	T	M	U	COLOR	Style
CFS-DY-1025	12 - 10	.250 x .032	.96	.32	.25	.165	.250	.020	YELLOW	1
CFS-DY-1412 †	16 - 14	.110 x .020	.80	.25	.19	.115	.145	.012	BLUE	3
CFS-DY-1418	16 - 14	.187 x .020	.77	.25	.25	.085	.170	.016	BLUE	1
CFS-DY-1425	16 - 14	.250 x .032	.86	.30	.25	.080	.170	.020	BLUE	2
CFS-DY-1818	22 - 18	.187 x .020	.77	.25	.25	.085	.145	.016	RED	1
CFS-DY-1825	22 - 18	.250 x .032	.86	.30	.25	.080	.145	.020	RED	2

SPC-F004.DWG

† NOT UL LISTED OR CSA CERTIFIED

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

Tolerances: Unless
Otherwise Specified:
.X = ±.015
.XX = ±.010
.XXX = ±.005

DRAWN BY:	DATE:
JC	3/8/91
CHECKED BY:	DATE:
JOHN COLE	12/10/91
APPROVED BY:	DATE:
John Liska	12/10/91

DRAWING TITLE:
Nylon Insulated Female Disconnects

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-445	TA-445.dwg	B
SCALE: NTS		U.O.M.: INCHES [mm]	SHEET: 1 OF 1