



PNP Medium Power Transistor



Features:

- Low Voltage
- High Current

Applications:

- Low voltage,high current LF applications
- Complement to BC868

Pin Configuration:

1. Base
2. Emitter
3. Collector

Maximum Ratings

Parameter	Symbol	Value	Unit
Collector - Base Voltage	V_{CBO}	-32	V
Collector - Emitter Voltage	V_{CEO}	-20	
Emitter - Base Voltage	V_{ebo}	-5	
DC Collector Current	I_C	-1	A
Collector Current - Peak	I_{CM}	-2	
Peak Base Current	I_{BM}	-200	mA
Total Power Dissipation ($T_{AMB} < 25^{\circ}C$)	P_{TOT}	1.35	W
Junction and Storage Temperature	T_j, T_{stg}	-65 to +150	$^{\circ}C$


PNP Medium Power Transistor

Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Unit
Collector Cut-Off Current	I_{CBO}	$V_{CB} = -25\text{V}, I_E = 0$ $V_{CB} = -25\text{V}, I_E = 0, T_j = 150^\circ\text{C}$			-100 -10	nA μA
Emitter Cut-Off Current	I_{EBO}	$V_{EB} = -5\text{V}, I_C = 0$			-10	nA
DC Current Gain	h_{FE}	$V_{CE} = -10\text{V}, I_C = -5\text{mA}$ $V_{CE} = -1\text{V}, I_C = -500\text{mA}$ $V_{CE} = -1\text{V}, I_C = -1\text{A}$	50 100 60		375	
Collector - Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = -1\text{A}, I_B = -100\text{mA}$			-0.5	V
Base Emitter Voltage	V_{BE}	$I_C = -1\text{A}, V_{CE} = -1\text{V}$			-1	
Transition Frequency	f_T	$V_{CE} = -5\text{V}, I_C = -10\text{mA},$ $f = 100\text{MHz}$	40			MHz

Typical Characteristics: $T_a = 25^\circ\text{C}$ unless otherwise specified

Ratings & Characteristic Curves




$V_{CE} = -1\text{V}$.

DC current gain; typical values

PNP Medium Power Transistor

Package Outline


Plastic surface mounted package



Dimensions	Min.	Max.
A	4.5	4.7
B	2.3	2.7
C	1.5 Typical	
D	0.35	0.55
E	1.4	1.6
F	0.4	0.6
H	1.55	1.75
J	0.4 Typical	
K	4.15	4.25

Dimensions : Millimetres

Soldering Footprint



Dimensions : Millimetres

Part Number Table

Description	Part Number
Transistor, PNP, 1A, 20V, SOT-89	BC869

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.