


6 mm Square Thin Type Double-action SMD Light Touch Switches

Type: **EVQPR/EVQQ0/EVQ3PR**




■ Features

- External dimensions : 6.0 mm×6.0 mm,
Height : 0.9 mm (Without push plate)
0.95 mm (With push plate)
- Wide selection of double action operating variations
With push plate : 1st 0.7 N, 2nd 2.6 N
Without push plate : 1st 1.0 N, 2nd 2.6 N
- Wide selection of double action operating variations

■ Recommended Applications

- Camera function
(Digital still cameras, Camcorders, Mobile phones, etc.)
- Operating switches for menu scrolling and confirmation for portable equipment.

■ Explanation of Part Numbers







■ Specifications

Type		Snap action/Push-on type SPDT	
Push Plate type		With Push Plate	Without Push Plate
Electrical	Rating	10 μ A 2 Vdc to 20 mA 15 Vdc (Resistive load)	
	Contact Resistance	100 m Ω max.	
	Insulation Resistance	50 M Ω min.	
	Dielectric Withstanding Voltage	100 Vac for 1 minute	
	Bouncing	3 ms max. (ON) 20 ms max. (OFF)	
Mechanical	Operating Force	1st : 0.7 N	1st : 1.0 N
		2nd : 2.6 N	2nd : 2.6 N
	Travel	1st: 0.4 mm	2nd: 0.6 mm
Endurance	Operating Life	30000 cycles min.	
Operating Temperature		-20 °C to +70 °C	
Storage Temperature		-40 °C to +85 °C (Bulk)	
		-20 °C to +60 °C (Taping)	
Minimum Quantity/Packing Unit		5000 pcs. Embossed Taping (Reel Pack)	
Quantity/Carton		25000 pcs.	


Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Dimensions in mm (not to scale)


No. 1 With Push Plate EVQQ0 EVQPR (Mounting base with Boss) (With ground terminal) 	 Either ⑤ or ⑥ type will be used because of variety of molding dies.																									
Part Numbers EVQQ04A10 EVQPR7A10 EVQPR5A10 EVQPR9A10	<table> <tr> <th>Ground Terminal</th><th>Boss</th><th>Operating Force</th><th>Height</th><th>Operating Life</th></tr> <tr> <td>Without</td><td>Without</td><td>1st/0.7 N, 2nd/2.6 N</td><td>0.95 mm</td><td>30000 cycles</td></tr> <tr> <td>Without</td><td>With</td><td>1st/0.7 N, 2nd/2.6 N</td><td>0.95 mm</td><td>30000 cycles</td></tr> <tr> <td>With</td><td>Without</td><td>1st/0.7 N, 2nd/2.6 N</td><td>0.95 mm</td><td>30000 cycles</td></tr> <tr> <td>With</td><td>With</td><td>1st/0.7 N, 2nd/2.6 N</td><td>0.95 mm</td><td>30000 cycles</td></tr> </table>	Ground Terminal	Boss	Operating Force	Height	Operating Life	Without	Without	1st/0.7 N, 2nd/2.6 N	0.95 mm	30000 cycles	Without	With	1st/0.7 N, 2nd/2.6 N	0.95 mm	30000 cycles	With	Without	1st/0.7 N, 2nd/2.6 N	0.95 mm	30000 cycles	With	With	1st/0.7 N, 2nd/2.6 N	0.95 mm	30000 cycles
Ground Terminal	Boss	Operating Force	Height	Operating Life																						
Without	Without	1st/0.7 N, 2nd/2.6 N	0.95 mm	30000 cycles																						
Without	With	1st/0.7 N, 2nd/2.6 N	0.95 mm	30000 cycles																						
With	Without	1st/0.7 N, 2nd/2.6 N	0.95 mm	30000 cycles																						
With	With	1st/0.7 N, 2nd/2.6 N	0.95 mm	30000 cycles																						
No. 2 Without Push Plate EVQPR EVQ3PR (Mounting base with Boss) (With ground terminal) 	 Either ⑤ or ⑥ type will be used because of variety of molding dies.																									
Part Numbers EVQPRBA09 EVQ3PRA09 EVQPRDA09 EVQPRHA09	<table> <tr> <th>Ground Terminal</th><th>Boss</th><th>Operating Force</th><th>Height</th><th>Operating Life</th></tr> <tr> <td>Without</td><td>Without</td><td>1st/1.0 N, 2nd/2.6 N</td><td>0.9 mm</td><td>30000 cycles</td></tr> <tr> <td>Without</td><td>With</td><td>1st/1.0 N, 2nd/2.6 N</td><td>0.9 mm</td><td>30000 cycles</td></tr> <tr> <td>With</td><td>Without</td><td>1st/1.0 N, 2nd/2.6 N</td><td>0.9 mm</td><td>30000 cycles</td></tr> <tr> <td>With</td><td>With</td><td>1st/1.0 N, 2nd/2.6 N</td><td>0.9 mm</td><td>30000 cycles</td></tr> </table>	Ground Terminal	Boss	Operating Force	Height	Operating Life	Without	Without	1st/1.0 N, 2nd/2.6 N	0.9 mm	30000 cycles	Without	With	1st/1.0 N, 2nd/2.6 N	0.9 mm	30000 cycles	With	Without	1st/1.0 N, 2nd/2.6 N	0.9 mm	30000 cycles	With	With	1st/1.0 N, 2nd/2.6 N	0.9 mm	30000 cycles
Ground Terminal	Boss	Operating Force	Height	Operating Life																						
Without	Without	1st/1.0 N, 2nd/2.6 N	0.9 mm	30000 cycles																						
Without	With	1st/1.0 N, 2nd/2.6 N	0.9 mm	30000 cycles																						
With	Without	1st/1.0 N, 2nd/2.6 N	0.9 mm	30000 cycles																						
With	With	1st/1.0 N, 2nd/2.6 N	0.9 mm	30000 cycles																						

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Recommended Reflow Soldering Conditions




● Embossed Carrier Taping



Unit: mm


Part No.	Height	A	B	W	F	E	P_1	P_2	P_0	D_0 Dia.	t_1	t_2
EVQPR/Q0/3PR	0.9, 0.95	6.3 ± 0.3	6.3 ± 0.3	12.0 ± 0.3	5.50 ± 0.15	1.75 ± 0.15	8.00 ± 0.15	2.00 ± 0.15	4.00 ± 0.15	$1.5^{+0.1}_{-0.1}$	0.30 ± 0.05	$1.7^{+0.2}_{-0.1}$

● Standard Reel Dimensions in mm (not to scale)



Item	A	B	C	D	E
Rate (mm)	$\phi 380.0 \pm 2.0$	$\phi 80.0 \pm 1.0$	$\phi 13.0 \pm 0.2$	$\phi 21.0 \pm 0.8$	2.0 ± 0.5
Item	W	T	t	r	
Rate (mm)	13.5 ± 1.0	17.5 ± 1.0	1.0 to 3.0	1.0 ± 0.5	

■ Recommended Shape of Test Pole



■ Recommended Operating Conditions

