


Designed to be wave soldered along with other Printed Circuit Board Components and withstand associated cleaning processes.

Following the table from left to right, the designer is able to specify the options wanted. The options are described and illustrated on The following pages.

To determine a part number select the options desired and fill in the boxes in the selection guides illustrated below.

WashableToggle Switch Selection Guide



Series		Poles and Throw		Circuits ⑥				Lever Options and Finishes				Bushing Options		Terminal Options		Contact Material	
Type	Code	No.	Code				Code	Type	Code	Finish	Code	Type	Code	Type	Code	Type	Code
Toggle	WT	SPDT	1			POS. "C"		.940 BAT.	L0	Bright Chrome	1	.250 Smooth	D1	Right Angle PC	A	Gold/Brass	B
			DPDT	2	ON	OFF	ON	21	.740 BAT.	L1	Black ③	3	.280 Smooth	D9 ②	Vertical PC .150 Spacing	AV2	Gold/Silver
		ON		NONE	ON	23	.650 BAT.	L2	Black Nylon ④	4	.350 ⑤	Y ⑦	PC Terminals	C	Coin/Silver	Q	
		ON		NONE	ON*	26	Long Mod Cap	L3	Red Nylon ④	5	Threaded		PC & Support	V30	⑧	K	
		ON*		OFF	ON*	27	Short Mod Cap	L4	White Nylon ④	6	.350 ⑤		.750 Wire Wrap	W	⑧	L	
		ON		OFF	ON*	31	.510 BAT.	S			.964 Wire Wrap		W1	⑧	M		
		ON		ON	ON	32 ①	.300 BAT.	M			.425 Wire Wrap	W3					
		ON		ON	ON*	33 ①					1.062 Wire Wrap	W4					
		ON*		ON	ON*	35 ①					Solder Lug	Z					
										Quick Connect	Z3						

④ Available only with L3 and L4 lever options only.

⑧ Same as B, G and Q respectively except terminals brass with tin nickel alloy over nickel plate. Consult plant for availability.

WT123M1D9AB = SPDT toggle switch with an ON-NONE-ON circuit, .270" long lever (see note 2 above) with a bright chrome finish, .280" smooth bushing right angle P.C. terminals with gold/brass contacts.

WT232S1D1V30G = DPDT toggle switch with an ON-ON-ON circuit, .510" long lever with a bright chrome finish, .250" smooth bushing, P.C. terminals with support bracket and gold/silver contacts.

Letter codes B and G – 0.5 volt amp (VA) maximum @ 28 V maximum (AC or DC).

Life Under Load — 60,000 make-and-break cycles — resistive load only.

Initial Contact Resistance — 10 milliohms maximum 3 VDC, 100 ma for both silver and gold plated contacts.

Insulation Resistance — 1,000 megohms, min.

Dielectric Strength — 1,000 volts rms at sea level.

Operating Temperature — -30 degrees C to 85 degrees C.

Base & Bushing—Thermoplastic high temperature (UL 94V-O).

Lever (toggle) — Brass, chrome plated.

Support brackets — Brass or steel tin plated.


Letter Code Q — Coin silver

Letter Code Q — Silver plated brass.


Hardware — See pages 55-57.

Washable Toggle Switches — Base Dimensions and Lever Options

APPROXIMATE BASE DIMENSIONS



TOGGLE LEVER OPTIONS



BUSHING OPTIONS

D1 Standard (.250") Smooth	D9 (.280") Smooth
Y (.350") Threaded	Y9 (.350") Smooth

TERMINATION OPTIONS

C Printed Circuit	W Wire-Wrap	W1 Wire-Wrap	W3 Wire-Wrap	W4 Wire-Wrap	Z Standard	Z3 Quick Connect Mating Receptacle from AMP SPECIAL IND., P.O. Box 984, Paoli, Pa. 19301 Amp P/N single piece 61454 series, strip from 60900
---------------------------------	---------------------------	----------------------------	----------------------------	----------------------------	--------------------------	---

NOTE: Wire-Wrap is a registered trademark of the Gardner-Denver Company.


TERMINATION & MOUNTING OPTIONS

A			P.C. MOUNTING
A			P.C. MOUNTING

TERMINATION & MOUNTING OPTIONS — Contd.


AV2

ONE POLE




AV2

TWO POLE



V30

ONE POLE



V30

TWO POLE

