






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
J			O	RELEASED FJB0-0871-04		24AUG04	C.W I.E
			01	REVISED PER ECO-09-024927		09NOV09	KK AEG




- 1 MATERIAL & FINISH
PLUG HOUSING:THERMOPLASTIC(UL94V-0)
COLOR: BLACK.
REC CONTACT:COPPER ALLOY.
FINISH:OVER NICKEL,MATING END:
0.0002 OR 0.00076 MIN.GOLD,
TERMINATION END:TIN. AND SEALING TREATMENT
ALL OVER.
- 2 P.W.B. LAYOUT AND P.W.B. TREATMENT(REF.)
P.W.B. SURFACE ARE TREATED WITH SOLDER RESIST.
BOARD THICKNESS:1.6mm.
- 3 ON KINK POINT(4 PLACES).
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

(NON-CUMULATIVE TOLERANCE)



30,50 POS.
CONNECTOR MOUNTING

(NON-CUMULATIVE TOLERANCE)



20,40,60 POS.
CONNECTOR MOUNTING

D/D.SINISI	4 OBSOLETE	Au PL. 0.00076 MIN.	20	11	11.43	15.60	19.20	9	20	6—	—5
			60	31	36.83	41.00	44.60	29	60	6—	—4
			50	26	30.48	34.65	38.26	24	50	6—	—3
			40	21	24.13	28.30	31.90	19	40	6—	—2
			30	16	17.78	21.95	25.55	14	30	6—	—1
	4 OBSOLETE	Au PL. 0.0002 MIN.	20	11	11.43	15.60	19.20	9	20		—5
			60	31	36.83	41.00	44.60	29	60		—4
			50	26	30.48	34.65	38.26	24	50		—3
			40	21	24.13	28.30	31.90	19	40		—2
			30	16	17.78	21.95	25.55	14	30		5175710—1
REMARK		N	M	A		B		C	n	POS.	PART NO.
		CIRCUIT NO.		DIMENSION							

LEAD FREE

GENERAL TOLERANCE

10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	24AUG04		 Tyco Electronics Tycu Electronics AMP K.K. Kawasaki,Japan				
		CHK	24AUG04						
		STEVEN YAO							
		APVD	24AUG04		NAME				
		I.ENOMOTO							
		PRODUCT SPEC		PLUG ASSY V WITH KINK AMPLIMITE .050 SERIES I B-TO-B CONN. —					
		108-60036							
		APPLICATION SPEC							
		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
				A3	00779	C-5175710	—		
CUSTOMER DRAWING				SCALE	NTS	SHEET	1 OF 1	REV	01