


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER		STUD SIZE	DIMENSIONS in.				
PREFIX	PK		A $\pm .03$ (.8)	C $\pm .015$ (.4)	H $\pm .01$ (.3)	M $\pm .03$ (.8)	W $\pm .01$ (.3)
PV18-6FB	-3K	#6	.78 (19.8)	.20 (5.1)	.15 (3.8)	.64 (16.3)	.30 (7.6)
PV18-6FNB	-3K	#6	.78 (19.8)	.20 (5.1)	.15 (3.8)	.64 (16.3)	.25 (6.4)
PV18-8FB	-3K	#8	.84 (21.3)	.23 (5.8)	.17 (4.3)	.68 (17.2)	.32 (8.1)
PV18-10FB	-3K	#10	.86 (21.8)	.25 (6.4)	.20 (5.1)	.70 (17.7)	.35 (8.9)
PV18-10FNB	-3K	#10	.86 (21.8)	.25 (6.4)	.20 (5.1)	.70 (17.7)	.31 (7.9)
PV18-14FB	-3K	1/4"	1.03 (26.2)	.33 (8.4)	.27 (6.9)	.78 (19.9)	.44 (11.2)

NOTES:

- USED FOR:
A. 600V MAX VOLTAGE RATING
B. 221°F (105°C) MAX TEMP RATING
C. 22-18 AWG (.5-1.5 mm²) SOLID OR STRANDED COPPER WIRE
- INSTALLATION TOOLS:
A. PRESSES : CP-851, CP-860, CP-861
B. APPLICATOR : CA-800
C. DIE INSERTS : CD-800-1
- WIRE STRIP LENGTH: 1/4 $\pm 1/32$ (6.4 $\pm .8$)
- MAX WIRE INSULATION DIA: .150 (3.81)
- MATERIAL USED:
A. TERMINAL STAMPING: .03 (.8) THICK TIN PLATED COPPER
B. HOUSING : RED VINYL
- PACKAGING: 3K = 3000 PCS (CONTINUOUSLY MOLDED ON REEL)
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS OR mm²



LISTED
587H
E52164



CERTIFIED
LR31212

A41081_03

03	12/00	ED		FILESPEC WAS: N41081AA_PCD_02	08925			PANDUIT CORP. TINLEY PARK, ILLINOIS REELSMART™ TERMO 2PC. CONTINUOUSLY MOLDED VINYL INSULATED, #22-18 BARREL, FORKS			
02	5/93	BK		UPDATED DRAWING FORMAT	01564						
1	12-87	DSM		REDRAWN ON CAD		KS	LA	DRAWN BY DSM CUST'D FS SCALE NONE DRAWING NO. A41081			
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PV18-8FB-3K](#)