



REVISED PER 0720-0230-93		NAME	AND
DATE	DESCRIPTION	DATE	AND

METRIC
DIMENSIONS LISTED IN mm [INCHES]



WIRE RANGE	E13288 Listed
12-10 AWG STRANDED	12-10 AWG STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP 12-10* APPROX AS SHOWN



AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS
FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS
FOR APPLICATION
TOOLING INFORMATION
FOR ORDER ENTRY

MAX RECOMMENDED OPERATING
TEMPERATURE: 170°C MAX
VOLTAGE RATING:
NOT APPLICABLE
WIRE CROSS SECTIONAL AREA RANGE:
2.62-6.64mm² [5.180-13.100] CIR MILS
STRANDED
THIS DRAWING IS A CONTROLLED DOCUMENT. FOR
REVISIONS, CONTACT THE DRAWING ENGINEER.
THIS DOCUMENT IS NOT TO BE REPRODUCED OR
TRANSMITTED IN ANY FORM OR BY ANY MEANS
ELECTRONIC OR MECHANICAL, INCLUDING
PHOTOCOPYING, RECORDING, OR BY ANY
INFORMATION STORAGE AND RETRIEVAL
SYSTEM.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm - FINISHES -
TOLERANCES ON:
2 PLG DEC ± .1
3 PLG DEC ± .1
ANGLES
MATERIAL
COPPER PER
ASTM B-152
ANNEALED
FINISH
TIN PLATE
0.00254 [0.000100] MIN
THK PER MIL-T-10727

DR 1-28-93 TA BRIKMAN	NAME	AMP Incorporated Harrisburg, PA 17105-3508
CHK 1-28-93 DA PATTERSON	PRODUCT SPEC	TERMINAL, RECTANGULAR TONGUE, BUDGET
APPD 1-28-93 DE MILLER	APPLICATION SPEC	SIZE CAGE CODE DRAWING NO
APPD 1-28-93 JL HECKLEY	WEIGHT	SCALE 8:1
APPD 1-28-93 JL HECKLEY	SCALE 8:1	SHEET 1 OF 1