


## Thick Film, Rectangular Chip Resistors



### FEATURES

- Metal glaze on high quality ceramic
- Protective overglaze
- Lead bearing (90 % Sn/10 % Pb) solder contacts
- Excellent stability ( $\Delta R/R \leq \pm 0.5\%$  for 1000 h at 70 °C) in different environmental conditions
- High volume product suitable for commercial and special applications

### STANDARD ELECTRICAL SPECIFICATIONS

| MODEL                                                                         | SIZE |        | POWER RATING $P_{70\text{ °C}}$<br>W | LIMITING<br>ELEMENT<br>VOLTAGE<br>MAX $V_{\Sigma}$ | TEMPERATURE<br>COEFFICIENT<br>ppm/K       | TOLERANCE<br>%                | RESISTANCE<br>RANGE<br>$\Omega$      | E-SERIES                 |
|-------------------------------------------------------------------------------|------|--------|--------------------------------------|----------------------------------------------------|-------------------------------------------|-------------------------------|--------------------------------------|--------------------------|
|                                                                               | INCH | METRIC | CECC 40401-802/EIA-575               |                                                    |                                           |                               |                                      |                          |
| D10<br>— — —<br>CRCW0402                                                      | 0402 | 1005   | 0.063                                | 50                                                 | $\pm 200^{(1)}$<br>$\pm 100$<br>$\pm 200$ | $\pm 1$<br>$\pm 1$<br>$\pm 5$ | 1R0 - 9R76<br>10R - 10M<br>1R0 - 10M | 24 + 96<br>24 + 96<br>24 |
| Zero-Ohm-Resistor: $R_{\max} = 20\text{ m}\Omega$ , $I_{\max} = 1\text{ A}$   |      |        |                                      |                                                    |                                           |                               |                                      |                          |
| D11<br>— — —<br>CRCW0603                                                      | 0603 | 1608   | 0.10                                 | 75                                                 | $\pm 200^{(1)}$<br>$\pm 100$<br>$\pm 200$ | $\pm 1$<br>$\pm 1$<br>$\pm 5$ | 1R0 - 9R76<br>10R - 10M<br>1R0 - 10M | 24 + 96<br>24 + 96<br>24 |
| Zero-Ohm-Resistor: $R_{\max} = 20\text{ m}\Omega$ , $I_{\max} = 1.5\text{ A}$ |      |        |                                      |                                                    |                                           |                               |                                      |                          |
| D12<br>— — —<br>CRCW0805                                                      | 0805 | 2012   | 0.125                                | 150                                                | $\pm 200^{(1)}$<br>$\pm 100$<br>$\pm 200$ | $\pm 1$<br>$\pm 1$<br>$\pm 5$ | 1R0 - 9R76<br>10R - 10M<br>1R0 - 10M | 24 + 96<br>24 + 96<br>24 |
| Zero-Ohm-Resistor: $R_{\max} = 20\text{ m}\Omega$ , $I_{\max} = 2\text{ A}$   |      |        |                                      |                                                    |                                           |                               |                                      |                          |
| D25<br>— — —<br>CRCW1206                                                      | 1206 | 3216   | 0.25                                 | 200                                                | $\pm 200^{(1)}$<br>$\pm 100$<br>$\pm 200$ | $\pm 1$<br>$\pm 1$<br>$\pm 5$ | 1R0 - 9R76<br>10R - 10M<br>1R0 - 10M | 24 + 96<br>24 + 96<br>24 |
| Zero-Ohm-Resistor: $R_{\max} = 20\text{ m}\Omega$ , $I_{\max} = 2.5\text{ A}$ |      |        |                                      |                                                    |                                           |                               |                                      |                          |
| CRCW1210                                                                      | 1210 | 3225   | 0.33                                 | 200                                                | $\pm 200^{(1)}$<br>$\pm 100$<br>$\pm 200$ | $\pm 1$<br>$\pm 1$<br>$\pm 5$ | 1R0 - 9R76<br>10R - 10M<br>1R0 - 10M | 24 + 96<br>24 + 96<br>24 |
| Zero-Ohm-Resistor: $R_{\max} = 20\text{ m}\Omega$ , $I_{\max} = 2.5\text{ A}$ |      |        |                                      |                                                    |                                           |                               |                                      |                          |
| CRCW1218                                                                      | 1218 | 3246   | 1.0                                  | 200                                                | $\pm 200^{(1)}$<br>$\pm 100$<br>$\pm 200$ | $\pm 1$<br>$\pm 1$<br>$\pm 5$ | 1R0 - 9R76<br>10R - 2M2<br>1R0 - 2M2 | 24 + 96<br>24 + 96<br>24 |
| Zero-Ohm-Resistor: $R_{\max} = 20\text{ m}\Omega$ , $I_{\max} = 4\text{ A}$   |      |        |                                      |                                                    |                                           |                               |                                      |                          |
| CRCW2010                                                                      | 2010 | 5025   | 0.5                                  | 400                                                | $\pm 200^{(1)}$<br>$\pm 100$<br>$\pm 200$ | $\pm 1$<br>$\pm 1$<br>$\pm 5$ | 1R0 - 9R76<br>10R - 10M<br>1R0 - 10M | 24 + 96<br>24 + 96<br>24 |
| Zero-Ohm-Resistor: $R_{\max} = 20\text{ m}\Omega$ , $I_{\max} = 3\text{ A}$   |      |        |                                      |                                                    |                                           |                               |                                      |                          |
| CRCW2512                                                                      | 2512 | 6332   | 1.0                                  | 500                                                | $\pm 200^{(1)}$<br>$\pm 100$<br>$\pm 200$ | $\pm 1$<br>$\pm 1$<br>$\pm 5$ | 1R0 - 9R76<br>10R - 10M<br>1R0 - 10M | 24 + 96<br>24 + 96<br>24 |
| Zero-Ohm-Resistor: $R_{\max} = 20\text{ m}\Omega$ , $I_{\max} = 4\text{ A}$   |      |        |                                      |                                                    |                                           |                               |                                      |                          |

#### Notes

1. 100 ppm/K on request
- Ask about further value ranges
- For low values see Thick Film rectangular low value resistors
- For high values see Thick Film rectangular high values
- Marking and packaging: see appropriate catalog or web pages

- For precision Thick Film CRCW see Thick Film rectangular Precision Resistors
- Power rating depends on the max. temperature at the solder point, the component placement density and the substrate material
- AgPd or Pd terminations for conductive adhesive attachment on request

### TECHNICAL SPECIFICATIONS


| PARAMETER                                            | UNIT              | D10<br>CRCW0402      | D11<br>CRCW0603  | D12<br>CRCW0805  | D25<br>CRCW1206  | CRCW1210         | CRCW1218        | CRCW2010        | CRCW2512        |
|------------------------------------------------------|-------------------|----------------------|------------------|------------------|------------------|------------------|-----------------|-----------------|-----------------|
| Rated Dissipation at 70 °C<br>(CECC 40401   EIA 575) | W                 | 0.063                | 0.10             | 0.125            | 0.25             | 0.33             | 1.0             | 0.5             | 1.0             |
| Limiting Element Voltage <sup>(2)</sup>              | $V_{\Sigma}$      | 50                   | 75               | 150              | 200              | 200              | 200             | 400             | 500             |
| Insulation Voltage (1 min)                           | $V_{\text{peak}}$ | > 75                 | > 100            | > 200            | > 300            | > 300            | > 300           | > 300           | > 300           |
| Thermal Resistance                                   | K/W               | $\leq 870^{(1)}$     | $\leq 550^{(1)}$ | $\leq 440^{(1)}$ | $\leq 220^{(1)}$ | $\leq 140^{(3)}$ | $\leq 65^{(3)}$ | $\leq 88^{(3)}$ | $\leq 65^{(3)}$ |
| Insulation Resistance                                | $\Omega$          | $> 10^9$             |                  |                  |                  |                  |                 |                 |                 |
| Category Temperature                                 | °C                | - 55/+ 125 (+ 155)   |                  |                  |                  |                  |                 |                 |                 |
| Failure Rate                                         | $\text{h}^{-1}$   | $0.3 \times 10^{-9}$ |                  |                  |                  |                  |                 |                 |                 |
| Weight/1000 pcs                                      | g                 | 0.65                 | 2                | 5.5              | 10               | 16               | 29.5            | 25.5            | 40.5            |

#### Notes

1. Measuring conditions in acc. to CECC 4040
2. Rated voltage:  $\sqrt{P \times R}$
3. Depending on solder pad dimensions



## DIMENSIONS



| SIZE |        | DIMENSIONS [in millimeters]            |             |             |                                       |           |
|------|--------|----------------------------------------|-------------|-------------|---------------------------------------|-----------|
| INCH | METRIC | L                                      | W           | H           | T1                                    | T2        |
| 0402 | 1005   | 1.0 ± 0.05                             | 0.5 ± 0.05  | 0.35 ± 0.05 | 0.25 ± 0.05                           | 0.2 ± 0.1 |
| 0603 | 1608   | 1.55 <sup>+0.10</sup> <sub>-0.05</sub> | 0.85 ± 0.1  | 0.45 ± 0.05 | 0.3 ± 0.2                             | 0.3 ± 0.2 |
| 0805 | 2012   | 2.0 <sup>+0.20</sup> <sub>-0.10</sub>  | 1.25 ± 0.15 | 0.45 ± 0.05 | 0.3 <sup>+0.20</sup> <sub>-0.10</sub> | 0.3 ± 0.2 |
| 1206 | 3216   | 3.2 <sup>+0.10</sup> <sub>-0.20</sub>  | 1.6 ± 0.15  | 0.55 ± 0.05 | 0.45 ± 0.2                            | 0.4 ± 0.2 |
| 1210 | 3225   | 3.2 ± 0.2                              | 2.5 ± 0.2   | 0.55 ± 0.05 | 0.45 ± 0.2                            | 0.4 ± 0.2 |
| 1218 | 3246   | 3.2 <sup>+0.10</sup> <sub>-0.20</sub>  | 4.6 ± 0.15  | 0.55 ± 0.05 | 0.45 ± 0.2                            | 0.4 ± 0.2 |
| 2010 | 5025   | 5.0 ± 0.15                             | 2.5 ± 0.15  | 0.6 ± 0.1   | 0.6 ± 0.2                             | 0.6 ± 0.2 |
| 2512 | 6332   | 6.3 ± 0.2                              | 3.15 ± 0.15 | 0.6 ± 0.1   | 0.6 ± 0.2                             | 0.6 ± 0.2 |

| SIZE |        | SOLDER PAD DIMENSIONS [in millimeters] |     |     |                |     |     |
|------|--------|----------------------------------------|-----|-----|----------------|-----|-----|
| INCH | METRIC | REFLOW SOLDERING                       |     |     | WAVE SOLDERING |     |     |
|      |        | a                                      | b   | l   | a              | b   | l   |
| 0402 | 1005   | 0.4                                    | 0.6 | 0.5 |                |     |     |
| 0603 | 1608   | 0.5                                    | 0.9 | 1.0 | 0.9            | 0.9 | 1.0 |
| 0805 | 2012   | 0.7                                    | 1.3 | 1.2 | 0.9            | 1.3 | 1.3 |
| 1206 | 3216   | 0.9                                    | 1.7 | 2.0 | 1.1            | 1.7 | 2.3 |
| 1210 | 3225   | 0.9                                    | 2.5 | 2.0 | 1.1            | 2.5 | 2.2 |
| 1218 | 3246   | 1.05                                   | 4.9 | 1.9 | 1.25           | 4.8 | 1.9 |
| 2010 | 5025   | 1.0                                    | 2.5 | 3.9 | 1.2            | 2.5 | 3.9 |
| 2512 | 6332   | 1.0                                    | 3.2 | 5.2 | 1.2            | 3.2 | 5.2 |

PART NUMBER AND PRODUCT DESCRIPTION<sup>1)</sup>

PART NUMBER: D1208050B5620FP0

|                                          |   |                   |   |                                                  |   |                                                                                                                                                                                                                                                                                                            |   |                        |   |                                        |   |                |   |   |   |  |  |
|------------------------------------------|---|-------------------|---|--------------------------------------------------|---|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---|------------------------|---|----------------------------------------|---|----------------|---|---|---|--|--|
| D                                        | 1 | 2                 | 0 | 8                                                | 0 | 5                                                                                                                                                                                                                                                                                                          | 0 | B                      | 5 | 6                                      | 2 | 0              | F | P | 0 |  |  |
| MODEL/SIZE                               |   | SPECIAL CHARACTER |   | TCR                                              |   | VALUE                                                                                                                                                                                                                                                                                                      |   | TOLERANCE              |   | PACKAGING <sup>2)</sup>                |   | SPECIAL        |   |   |   |  |  |
| D100402<br>D110603<br>D120805<br>D251206 |   | 0 = neutral       |   | B = ± 100 ppm/K<br>A = ± 200 ppm/K<br>0 = Jumper |   | 3 digit value<br>1 digit multiplier<br><br>MULTIPLIER<br>7 = *10 <sup>-3</sup> 2 = *10 <sup>2</sup><br>8 = *10 <sup>-2</sup> 3 = *10 <sup>3</sup><br>9 = *10 <sup>-1</sup> 4 = *10 <sup>4</sup><br>0 = *10 <sup>0</sup> 5 = *10 <sup>5</sup><br>1 = *10 <sup>1</sup> 6 = *10 <sup>6</sup><br>0000 = Jumper |   | F = ± 1 %<br>J = ± 5 % |   | P0 M0<br>P5 PZ<br>PN B5<br>MZ BN<br>MU |   | up to 2 digits |   |   |   |  |  |

PRODUCT DESCRIPTION: D12 100 562R 1% P5

PRODUCT DESCRIPTION: D12 100 562R 1% P5

|                          |                            |                                               |                |                                        |
|--------------------------|----------------------------|-----------------------------------------------|----------------|----------------------------------------|
| D12                      | 100                        | 562R                                          | 1 %            | P5                                     |
| MODEL                    | TCR                        | RESISTANCE VALUE                              | TOLERANCE      | PACKAGING <sup>2)</sup>                |
| D10<br>D11<br>D12<br>D25 | ± 100 ppm/K<br>± 200 ppm/K | 49K9 = 49.9 kΩ<br>5R1 = 5.1 Ω<br>0R0 = Jumper | ± 1 %<br>± 5 % | P0 M0<br>P5 PZ<br>PN B5<br>MZ BN<br>MU |

PART NUMBER: CRCW0805562RFKTA

|                                                                                              |   |                                                             |   |                                               |   |                                                             |   |                                                                                                          |   |                                           |   |   |   |   |   |  |  |
|----------------------------------------------------------------------------------------------|---|-------------------------------------------------------------|---|-----------------------------------------------|---|-------------------------------------------------------------|---|----------------------------------------------------------------------------------------------------------|---|-------------------------------------------|---|---|---|---|---|--|--|
| C                                                                                            | R | C                                                           | W | 0                                             | 8 | 0                                                           | 5 | 5                                                                                                        | 6 | 2                                         | R | F | K | T | A |  |  |
| MODEL/SIZE                                                                                   |   | VALUE                                                       |   | TOLERANCE                                     |   | TCR                                                         |   | PACKAGING <sup>2)</sup>                                                                                  |   | SPECIAL                                   |   |   |   |   |   |  |  |
| CRCW0402<br>CRCW0603<br>CRCW0805<br>CRCW1206<br>CRCW1210<br>CRCW1218<br>CRCW2010<br>CRCW2512 |   | R = Decimal<br>K = Thousand<br>M = Million<br>0000 = Jumper |   | F = ± 1 %<br>J = ± 5 %<br>Z = Zero Ohm Jumper |   | K = ± 100 ppm/K<br>N = ± 200 ppm/K<br>S = Jumper or Special |   | TA = RT1<br>TB = RT5<br>TC = RT6<br>TD = RT7<br>TF = R02<br>TG = R67<br>TH = R82<br>TK = RT9<br>BA = B27 |   | up to 2 digits<br>TR = Customer Trimmable |   |   |   |   |   |  |  |





PRODUCT DESCRIPTION: CRCW 0805 5620 F 100 RT1

|       |                                                  |                              |                                               |                            |                                                 |
|-------|--------------------------------------------------|------------------------------|-----------------------------------------------|----------------------------|-------------------------------------------------|
| CRCW  | 0805                                             | 5620                         | F                                             | 100                        | RT1                                             |
| MODEL | SIZE                                             | RESISTANCE VALUE             | TOLERANCE                                     | TCR                        | PACKAGING <sup>2)</sup>                         |
| CRCW  | 0402 1201<br>0603 1218<br>0805 2010<br>1206 2512 | 685 = 6.8 MΩ<br>224 = 220 kΩ | F = ± 1 %<br>J = ± 5 %<br>Z = Zero Ohm Jumper | ± 100 ppm/K<br>± 200 ppm/K | RT1 R67<br>RT5 R82<br>RT6 RT9<br>RT7 B27<br>R02 |

± 1 % = 3 sig.digits, plus multiplier  
± 5 % = 2 sig.digits, plus multiplier

## Notes

1. Preferred way for ordering products is by use of the PART NUMBER. 2. Please refer to table PACKAGING, page 116.







| PACKAGING       |            |            |             |       |                     |                       |                       |                    |
|-----------------|------------|------------|-------------|-------|---------------------|-----------------------|-----------------------|--------------------|
| MODEL           | REEL       |            |             |       | BULK                |                       |                       |                    |
|                 | TAPE WIDTH | DIAMETER   | PIECES/REEL | PITCH | PACKAGING CODE      |                       | BULK FEEDING MAGAZINE |                    |
|                 |            |            |             |       | PAPER <sup>1)</sup> | BLISTER <sup>2)</sup> | PIECES <sup>1)</sup>  | CODE <sup>2)</sup> |
| D10<br>CRCW0402 | 8 mm       | 180 mm/7"  | 10 000      | 2 mm  | P0/TD               |                       | 50 000                | MZ/BA              |
|                 |            | 330 mm/13" | 50 000      | 2 mm  | PZ/TE               |                       |                       |                    |
| D11<br>CRCW0603 | 8 mm       | 180 mm/7"  | 5000        | 4 mm  | P5/TA               | B5/na                 | 25 000                | MU/BA              |
|                 |            | 255 mm/10" | 10 000      | 4 mm  | P0/TB               |                       |                       |                    |
|                 |            | 330 mm/13" | 20 000      | 4 mm  | PN/TC               | BN/na                 |                       |                    |
| D12<br>CRCW0805 | 8 mm       | 180 mm/7"  | 5000        | 4 mm  | P5/TA               | B5/na                 | 10 000                | MO/BA              |
|                 |            | 255 mm/10" | 10 000      | 4 mm  | P0/TB               |                       |                       |                    |
|                 |            | 330 mm/13" | 20 000      | 4 mm  | PN/TC               | BN/na                 |                       |                    |
| D25<br>CRCW1206 | 8 mm       | 180 mm/7"  | 5000        | 4 mm  | P5/TA               | B5/na                 |                       |                    |
|                 |            | 255 mm/10" | 10 000      | 4 mm  | P0/TB               |                       |                       |                    |
|                 |            | 330 mm/13" | 20 000      | 4 mm  | PN/TC               | BN/na                 |                       |                    |
| CRCW1210        | 8 mm       | 180 mm/7"  | 5000        | 4 mm  | P5/TA               | B5/RG1                |                       |                    |
|                 |            | 330 mm/13" | 20 000      | 4 mm  | PN/TC               | BN/na                 |                       |                    |
| CRCW1218        | 12 mm      | 180 mm/7"  | 4000        | 4 mm  |                     | TK                    |                       |                    |
| CRCW2010        | 12 mm      | 180 mm/7"  | 4000        | 4 mm  |                     | TF                    |                       |                    |
| CRCW2512        | 12 mm      | 180 mm/7"  | 2000        | 8 mm  |                     | B2/TG                 |                       |                    |
|                 |            |            | 4000        | 4 mm  |                     | TH                    |                       |                    |


## Notes

- On request
- European/N.American packaging codes: na = NOT AVAILABLE




- Further information about packaging: see appropriate catalog or web page.



Stability nomogram typical values (for handling see general explanations)



Power rating as a function of packaging density (guideline)





| <b>PERFORMANCE</b>                                                           |                                                                           |                                 |                      |                      |
|------------------------------------------------------------------------------|---------------------------------------------------------------------------|---------------------------------|----------------------|----------------------|
| TEST                                                                         | CONDITIONS OF TEST                                                        | REQUIREMENTS IN % <sup>1)</sup> |                      |                      |
|                                                                              |                                                                           | 0402<br>0603                    | 0805<br>1206<br>1210 | 1218<br>2010<br>2512 |
| Endurance Test at 70 °C<br>IEC 60115-1 4.25.1; EIA-575                       | 1000 hours at 70 °C, 1.5 hours "ON", 0.5 hours "OFF"                      | ≤ ± 1.0                         | ≤ ± 0.5              | ≤ ± 1.0              |
| Endurance at UCT<br>IEC 60115-1 4.25.3                                       | 1000 hours at 125 °C without load                                         | ≤ ± 1.0                         | ≤ ± 0.5              | ≤ ± 1.0              |
| Overload Test<br>IEC 60115-1 4.13; EIA-575                                   | Short time overload, 2.5 x rated voltage or 2 x limiting element voltage. | ≤ ± 0.25                        | ≤ ± 0.25             | ≤ ± 0.5              |
| Thermal Shock<br>IEC 60115-1 4.19; IEC 60068-2-14;<br>EIA-575                | Rapid change between upper and lower category temperature                 | ≤ ± 0.25                        | ≤ ± 0.25             | ≤ ± 0.5              |
| Damp Heat Steady State<br>IEC 60115-1 4.24; IEC 60068-2-3                    | 56 days at 40 °C and 93 % relative humidity                               | ≤ ± 1.0                         | ≤ ± 0.5              | ≤ ± 1.0              |
| Resistance to Soldering Heat<br>IEC 60115-1 4.18; IEC 60068-2-20;<br>EIA-575 | 10 seconds at 260 °C solder bath temperature                              | ≤ ± 0.25                        | ≤ ± 0.25             | ≤ ± 0.5              |

**Note**

1. Limits for change of resistance at test acc. to CECC

| <b>APPLICABLE SPECIFICATIONS</b>                                                                                                            |
|---------------------------------------------------------------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"><li>• CECC40000/40400/40401-004,-006,-007,-802</li><li>• EN140400/IEC 60115-1</li><li>• EIA-575</li></ul> |



### Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.