

HONEYWELL PART NUMBER
21SM157-T
PRODUCT CODE TXK5750

REV	DOCUMENT	CHANGED BY	CHECK
4	0038444	KVS 09APR08	ASD



B

A

A

B

A



NOTE -

▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS

2-TERMINALS ARE PLATED FOR SOLDERING

3-SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO.
PR-709
REPLACES
-

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH		DRAWN		VK		15 FEB 08		Honeywell				
OPERATING FORCE — — — — 3 - 7 OZ		CONTACT ARRANGEMENT SPDT		TOLERANCES UNLESS NOTED:		CHECK		RJ		15 FEB 08						
RELEASE FORCE— — — — 1 OZ MIN		30 VOLTS DC RATING		NO PLACE X ±		0.030		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL— — — .004 MAX				ONE PLACE .X ±		0.015										
OVERTRAVEL — — — — — .005 MIN		SEA LEVEL		TWO PLACE .XX ±		0.005										
		INDUCTIVE 5 AMP		THREE PLACE .XXX ±												
		RESISTIVE 10 AMP		FOUR PLACE .XXXX ±				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV
				THIRD ANGLE PROJECTION		RASTER						B	I	21SM157-T		4
														SCALE	-	WEIGHT .006 LB MAX