





CIRCUIT: SPDT
CONTACT CONFIGURATION

SWITCH FUNCTION	
POS 1	POS 2
↗	⇒
DN	DN



LEGEND

- =INDICATES KEY PULL
- ✕ =INDICATES NO KEY PULL

- NOTES:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
 3. TERM. NOS. FDR REFERENCE ONLY.
 4. RATING: 3A @125VAC, 1.5A @250VAC
 5. CONTACT RESISTANCE: 10mILLI-OHMS
 6. DIELECTRIC STRENGTH: 1000 VAC-1Minute
 7. INSULATION RESISTANCE: 200 Mega-OHMS min.
 8. MATERIALS:

HOUSING: ZINC ALLOY DIE CAST
CYLINDER: ZINC ALLOY W/CHROME PLATING
TERMINAL AND CONTACTS: SILVER PLATED
KEYS (2) KEY CODE 10001: TUBULAR
ZINC ALLOY, CHROME PLATING W/PLASTIC COVER

REV.	ECN No.	DESCRIPTION	DATE	CHKD
A	11756	RELEASED FOR PRODUCTION	10/18/01	CJB

TITLE				
K0104B-10001				
E-SWITCH®				
SCALE	DATE	DR	DWG	REV
1.5:1	10/18/01	CJB	K300102	A