

## GaAs SP4T Switch, Absorptive, Single Supply DC - 4.0 GHz

MASWCC0010  
V2

### Features

- Operates DC - 4 GHz on Single Supply
- ASIC TTL / CMOS Driver
- Leadless 4 x 7 mm Chip Scale Plastic Package
- Low DC Power Consumption
- 50 Ohm Nominal Impedance
- Test Boards are Available
- Tape and Reel is Available
- Lead-Free CSP-2 Package
- 100% Matte Tin Plating over Copper
- Halogen-Free "Green" Mold Compound
- 260°C Reflow Compatible
- RoHS\* Compliant Version of SW90-0003

### Description

M/A-COM's MASWCC0010 is a SP4T absorptive pHEMT switch with integral TTL driver. This device is in an MLP plastic surface mount package. This switch offers excellent broadband performance and repeatability from DC to 4 GHz, while maintaining low DC power dissipation. The MASWCC0010 is ideally suited for wireless infrastructure applications.

### Pin Configuration<sup>2, 3, 4</sup>

Pin No.	Function	Pin No.	Function
1	CP2	19	GND
2	Vee	20	NC <sup>1</sup>
3	NC <sup>1</sup>	21	GND
4	C4	22	RFC
5	C3	23	GND
6	C2	24	NC <sup>1</sup>
7	C1	25	RF3
8	NC <sup>1</sup>	26	GND
9	NC <sup>1</sup>	27	NC <sup>1</sup>
10	NC <sup>1</sup>	28	GND
11	NC <sup>1</sup>	29	RF4
12	NC <sup>1</sup>	30	GND
13	GND	31	NC <sup>1</sup>
14	RF1	32	Vee
15	GND	33	Vcc
16	NC <sup>1</sup>	34	NC <sup>1</sup>
17	GND	35	Vcc
18	RF2	36	CP1

1. NC = No Connection
2. For single supply operation VEE is internally generated and must remain isolated from external power supplies. Generated noise is typical of switching DC-DC converters.
3. Connections and external components shown in functional schematic are required. 0.1µF Capacitors need to be located near pins 32 & 33.
4. The exposed pad centered on the package bottom must be connected to RF and DC ground. (For PQFN Packages)

### Ordering Information

Part Number	Package
MASWCC0010	Bulk Packaging
MASWCC0010TR	1000 piece reel
MASWCC0010-TB	Sample Test Board

Note: Reference Application Note M513 for reel size information.

Note: Die quantity varies.

\* Restrictions on Hazardous Substances, European Union Directive 2002/95/EC.

GaAs SP4T Switch, Absorptive, Single Supply  
DC - 4.0 GHz

MASWCC0010

V2

Electrical Specifications:  $T_A = 25^\circ\text{C}$ 

Parameter	Test Conditions	Frequency	Units	Min.	Typ.	Max.
Insertion Loss	RFC-RF1, 2, 3, 4	DC - 4.0 GHz	dB	—	—	2.3
Isolation	—	DC - 4.0 GHz	dB	38	—	—
VSWR	On (RFC, RF1-RF4) Logic per Truth Table Off (RF1-RF4) Logic per Truth Table	DC - 4.0 GHz DC - 4.0 GHz	Ratio Ratio	— —	— —	2.0:1 2.0:1
1 dB Compression	— —	50 MHz 0.5 - 4.0 GHz	dBm dBm	— —	+15 +27	— —
Input IP <sub>3</sub>	Two-tone inputs up to +5 dBm	50 MHz 0.5-4.0 GHz	dBm dBm	— —	30 40	— —
Switching Speed	Ton (50% Control to 90% RF) Toff (50% Control to 10% RF) Trise (10% to 90% RF) Tfall (90% to 10% RF)		ns ns ns ns	— — — —	35 20 12 2	— — — —
V <sub>cc</sub>	—	—	V	4.5	5.0	5.5
Logic "0"	Sink Current is 20 $\mu\text{A}$ max.	—	V	0.0	—	0.8
Logic "1"	Source Current is 20 $\mu\text{A}$ max.	—	V	2.0	—	5.0
I <sub>cc</sub> <sup>5</sup>	V <sub>cc</sub> min to max, Logic "0" or "1"	—	mA	—	5	8
Turn-on Current <sup>6</sup>	For guaranteed start-up	—	mA	—	—	125
Switching Noise	Generated from DC-DC Converter with recommended capacitors	3.5 MHz	dBm	—	-93	—
Thermal Resistance $\theta_{JC}$	—	—	$^\circ\text{C}/\text{W}$	—	15	—

- During turn-on, the device requires an initial start up current (I<sub>cc</sub>) specified as "Turn-on Current". Once operational, I<sub>cc</sub> will drop to the specified levels. This is not applicable to dual supply operation.
- The DC-DC converter is guaranteed to start in 100  $\mu\text{s}$  as long as the power supplies have the maximum turn-on current available for start-up.

Absolute Maximum Ratings <sup>7,8,9</sup>

Parameter	Absolute Maximum
Max. Input Power 0.05 GHz 0.5 - 4.0 GHz	+27 dBm +34 dBm
Bias Voltages V <sub>cc</sub> Control Voltage <sup>10</sup>	+5.5V -0.5V to V <sub>cc</sub> +0.5V
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to +125°C

## Truth Table (Switch)

C1	C2	C3	C4	RFC-RF1	RFC-RF2	RFC-RF3	RFC-RF4
1	0	0	0	On	Off	Off	Off
0	1	0	0	Off	On	Off	Off
0	0	1	0	Off	Off	On	Off
0	0	0	1	Off	Off	Off	On

- Exceeding any one or combination of these limits may cause permanent damage to this device.
- M/A-COM does not recommend sustained operation near these survivability limits.
- When the RF input is applied to the terminated port, the absolute maximum power is +30 dBm.
- Standard CMOS TTL interface, latch-up will occur if logic signal is applied prior to power supply.

2

M/A-COM Inc. and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice. M/A-COM makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does M/A-COM assume any liability whatsoever arising out of the use or application of any product(s) or information.

- North America Tel: 800.366.2266 / Fax: 978.366.2266
- Europe Tel: 44.1908.574.200 / Fax: 44.1908.574.300
- Asia/Pacific Tel: 81.44.844.8296 / Fax: 81.44.844.8298

Visit [www.macom.com](http://www.macom.com) for additional data sheets and product information.


## GaAs SP4T Switch, Absorptive, Single Supply DC - 4.0 GHz

MASWCC0010  
V2

### Functional Schematic

#### Single Supply Operation


V<sub>CC</sub> = +5V




#### Dual Supply Operation

V<sub>CC</sub> = +5V

V<sub>EE</sub> = -5V to -8V



### Recommended PCB Configuration<sup>11</sup>







11. Application Note C2083 is available on line at [www.macom.com](http://www.macom.com)

### Handling Procedures

Please observe the following precautions to avoid damage:

### Static Sensitivity


Gallium Arsenide Integrated Circuits are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these devices.

**GaAs SP4T Switch, Absorptive, Single Supply  
DC - 4.0 GHz**
**MASWCC0010  
V2**
**Typical Performance Curves**
*Insertion Loss vs. Frequency**Isolation (dB) vs. Frequency**On VSWR vs. Frequency**VSWR (Terminations) vs. Frequency*

**GaAs SP4T Switch, Absorptive, Single Supply  
DC - 4.0 GHz**

MASWCC0010

V2

**CSP-2, Lead-Free, 4 x 7 mm, 36-lead,  
PQFN<sup>†</sup>**

<sup>†</sup> Reference Application Note M538 for lead-free solder reflow recommendations.