

PRODUCT NUMBER
73304-XXXLF

PLATING OPTION
1= GXT 0.76 μ m
3= GOLD 0.76 μ m
5= GOLD 1.27 μ m


PACKAGE OPTION
1= TAPE ON REEL
2= TUBE
3= TAPE ON REEL
IN PLASTIC BAG

TERMINAL LOADING
1= FULLY LOADED
2= POS 1,2,7,8
3= POS 3,4,5,6

WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 4.

NOTES:

- 1- MATERIAL: HOUSING: HIGH TEMP. PCT, COLOUR BLACK.
TERMINAL: PHOSPHOR BRONZE.
- 2 - PLATING: CONTACT AREA: SEE TABLE.
SOLDER TAIL : 90/10 SnPb 2 μ m MIN.
WHEN SUFFIX "LF" IS REQUIRED, 2 μ m MIN MATTE
TIN OVER 1.27 MIN Ni IS SUPPLIED INSTEAD OF SnPb.
NO RAW EDGES EXEPT SOLDER TAIL TIPS
- 3 - SOLDER TAILS COPLANARITY : 0.1 mm
- 4 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE,
2 μ m MINIMUM MATTE TIN OVER 1.27 μ m
MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO
245°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.
 - c - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
 - d - LEGAL STATEMENT: SEE GS-47-0004
- 5 - PACKAGING FOR OPTION 3 : EACH REEL IS WRAPPED INTO A PLASTIC BAG
TO PROTECT FROM MOISTURE DURING STACKING TIME.








CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface	tolerance	projection	product family
				ISO 1302	ISO 406 ISO 1101		MOD JACK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title
H	F06-0240	DLE	06.07.18	angles	linear	mm	SMT RA JACK
J	F09-0070	LSA	02.07.23	±2'			8 POS OUTSIDE
K	B-15798	JFA	13.09.09			scale 2:1	
L	F-21888	AMA	15.09.09	dr	D LEGRAND	03.01.27	dwg no
				enr	F TISSERAND	03.01.27	sheet 1 of 3
F	F04-0363	DLE	04.10.18	chr	JF NOTTEAU	03.01.27	73304
G	F05-0247	DLE	05.09.12	appd	F.TI	03.01.27	A3
sheet	revision	L	E	B			type
index	sheet	1	2	3			CUSTOMER Drawing

PRODUCT NUMBER
SEE SHEET 1

LTR	PART NAME	QTY
1	PRODUCT	230
2	TAPE	1
3	REEL	1
4	COVER TAPE	1



1- IN ACCORDANCE WITH EIA-481 AND IEC 296-3

CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code		surface		tolerance		projection		product family	
		ISO 1302		ISO 406 ISO 1101		mm		MOD-JACK	
ltr	ecr no	dr	date	tolerances unless otherwise specified				title	
D	D80620	DLE	98.11.26	angles				SMT RA JACK	
E	F06-0240	DLE	06.07.18	linear				8 POS. OUTSIDE	
				dr		D LEGRAND		04.10.18	
				enrg		P NIZZI		04.10.18	
				chr		D LEGRAND		04.10.18	
				appd		P NIZZI		04.10.18	
sheet index		revision sheet						dwg no	
								73304	
								sheet 2 of 3	
								A3	
								type	
								CUSTOMER Drawing	




FCJconnect.com

Copyright FCJ



FCconnect.com

Copyright FCJ



CUSTOMER COPY FOR REFERENCE ONLY

mat'l. code				surface ☒ tolerance		projection		product family						
				ISO 1302 ☒ ISO 406 ISO 1101				MOD JACK						
ltr	ecr no	dr	date	tolerances unless otherwise specified				title SMT RA JACK 8 POS OUTSIDE						
A	F04-0363	DLE	04.10.18	±0.13										
B	F06-0240	DLE	06.07.18	angles	linear									
				±2'		scale 2:1								
				dr	D LEGRAND	04.10.18	dwg no					sheet 3 of -	size	
				engr	P NIZZI	04.10.18	73304						A4	
				chr	D LEGRAND	04.10.18								
				appd	P.NZ	04.10.18								
sheet index	revision sheet							type	CUSTOMER Drawing					

form: A4