


## Pan-Ty® Lashing Ties – Nylon 6.6

- For indoor use
- Typically used for heavy duty applications

- Strongest Pan-Ty® Cable Tie available
- Can be used with MCEH mounting clip



|                           | Length |      | Width |      | Thickness |     | Max. Bundle Dia. |     | Min. Loop Tensile Str. |      | Recommended Installation Tool | Std. Pkg. Qty. | Std. Ctn. Qty. |
|---------------------------|--------|------|-------|------|-----------|-----|------------------|-----|------------------------|------|-------------------------------|----------------|----------------|
| Part Number               | In.    | mm   | In.   | mm   | In.       | mm  | In.              | mm  | Lbs.                   | N    |                               |                |                |
| Extra-Heavy Cross Section |        |      |       |      |           |     |                  |     |                        |      |                               |                |                |
| PLT2EH-C                  | 9.0    | 229  | .500  | 12.7 | .075      | 1.9 | 2.00             | 51  | 250                    | 1112 | GS4EH, ST3EH                  | 100            | 1000           |
| PLT5EH-Q                  | 20.1   | 511  | .500  | 12.7 | .075      | 1.9 | 5.00             | 127 | 250                    | 1112 |                               | 25             | 250            |
| PLT6EH-Q                  | 22.2   | 564  | .500  | 12.7 | .075      | 1.9 | 6.00             | 152 | 250                    | 1112 |                               | 25             | 250            |
| PLT8EH-C                  | 28.3   | 719  | .500  | 12.7 | .085      | 2.2 | 8.00             | 203 | 250                    | 1112 |                               | 100            | 1000           |
| PLT10EH-C                 | 34.2   | 869  | .500  | 12.7 | .085      | 2.2 | 10.00            | 254 | 250                    | 1112 |                               | 100            | 500            |
| PLT12EH-C                 | 40.1   | 1019 | .500  | 12.7 | .085      | 2.2 | 12.00            | 305 | 250                    | 1112 |                               | 100            | 500            |

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index