



FR601G THRU FR607G

GLASS PASSIVATED JUNCTION FAST SWITCHING RECTIFIER


Reverse Voltage - 50 to 1000 Volts

Forward Current - 6.0 Amperes

Features

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0 utilizing Flame retardant epoxy molding compound
- Glass passivated junction in R-6 package
- 6.0 ampere operation at $T_A = 75^\circ\text{C}$ with no thermal runaway
- Fast switching for high efficiency

R-6



Mechanical Data

- **Case:** Molded plastic, R-6
- **Terminals:** Axial leads, solderable per MIL-STD-202, method 208
- **Polarity:** Band denotes cathode
- **Mounting Position:** Any
- **Weight:** 0.074 ounce, 2.105 grams

DIMENSIONS					
DIM	inches		mm		Note
	Min.	Max.	Min.	Max.	
A	0.339	0.358	8.6	9.1	
B	0.339	0.358	8.6	9.1	φ
C	0.047	0.052	1.2	1.3	φ
D	1.000	-	25.40	-	

Maximum Ratings and Electrical Characteristics @25°C unless otherwise specified


	Symbols	FR 601G	FR 602G	FR 603G	FR 604G	FR 605G	FR 606G	FR 607G	Units
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	Volts
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	Volts
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	Volts
Average forward rectified current at T _A =75℃	I _(AV)	6.0							Amps
Peak forward surge current 8.3mS single half sine-wave	I _{FSM}	300.0							Amps
Maximum instantaneous forward voltage I _{FM} =6.0A; T _A =25℃ (Note 1)	V _F	1.3							Volts
Maximum DC reverse current at rated DC blocking voltage T _A =25℃ T _A =55℃	I _R	10.0 150.0							μ A
Maximum reverse recovery time at I _F =0.5A, I _R =1.0A, I _{rr} =0.25A	T _{rr}	150				250	500		nS
Typical junction capacitance Measured at 1.0MHz, V _R =4.0V	C _J	150							p F
Operating and storage temperature range	T _J , T _{STG}	-65 to +150							℃

Note:

(1) Pulse test: Pulse width 300uSec, Duty cycle 1%


RATINGS AND CHARACTERISTIC CURVES

Figure 1
Typical Forward Characteristics




Instantaneous Forward Current - Amperes *versus*
Instantaneous Forward Voltage - Volts

Figure 2
Forward Derating Curve



Average Forward Rectified Current - Amperes *versus*
Ambient Temperature - °C

Figure 3
Junction Capacitance



Junction Capacitance - pF *versus*
Reverse Voltage - Volts

RATINGS AND CHARACTERISTIC CURVES




Figure 5
Reverse Recovery Time Characteristic And Test Circuit Diagram

