


- Advanced Process Technology
- Optimized for Automotive Motor Drive, DC-DC and other Heavy Load Applications
- Exceptionally Small Footprint and Low Profile
- High Power Density
- Low Parasitic Parameters
- Dual Sided Cooling
- 175°C Operating Temperature
- Repetitive Avalanche Capability for Robustness and Reliability
- Lead Free, RoHS Compliant and Halogen Free
- Automotive Qualified \*

Automotive DirectFET® Power MOSFET ②

$V_{(BR)DSS}$	75V
$R_{DS(on)}$ typ.	1.8mΩ
	max. 2.3mΩ
$I_D$ (Silicon Limited)	160A
$Q_g$	200nC



DirectFET® ISOMETRIC

Applicable DirectFET® Outline and Substrate Outline ①

SB	SC		M2	M4		L4	L6	L8	
----	----	--	----	----	--	----	----	----	--

## Description

The AUIRF7759L2TR(1) combines the latest Automotive HEXFET® Power MOSFET Silicon technology with the advanced DirectFET® packaging to achieve the lowest on-state resistance in a package that has the footprint of a DPak (TO-252AA) and only 0.7 mm profile. The DirectFET® package is compatible with existing layout geometries used in power applications, PCB assembly equipment and vapor phase, infra-red or convection soldering techniques, when application note AN-1035 is followed regarding the manufacturing methods and processes. The DirectFET® package allows dual sided cooling to maximize thermal transfer in automotive power systems.

This HEXFET® Power MOSFET is designed for applications where efficiency and power density are essential. The advanced DirectFET® packaging platform coupled with the latest silicon technology allows the AUIRF7759L2TR(1) to offer substantial system level savings and performance improvement specifically in motor drive, high frequency DC-DC and other heavy load applications on ICE, HEV and EV platforms. This MOSFET utilizes the latest processing techniques to achieve low on-resistance and low  $Q_g$  per silicon area. Additional features of this MOSFET are 175°C operating junction temperature and high repetitive peak current capability. These features combine to make this MOSFET a highly efficient, robust and reliable device for high current automotive applications.

	Parameter	Max.	Units
$V_{DS}$	Drain-to-Source Voltage	75	V
$V_{GS}$	Gate-to-Source Voltage	±20	
$I_D$ @ $T_C = 25^\circ\text{C}$	Continuous Drain Current, $V_{GS}$ @ 10V (Silicon Limited)④	160	
$I_D$ @ $T_C = 100^\circ\text{C}$	Continuous Drain Current, $V_{GS}$ @ 10V (Silicon Limited)④	113	
$I_D$ @ $T_A = 25^\circ\text{C}$	Continuous Drain Current, $V_{GS}$ @ 10V (Silicon Limited)③	26	A
$I_D$ @ $T_C = 25^\circ\text{C}$	Continuous Drain Current, $V_{GS}$ @ 10V (Package Limited) ④	375	
$I_{DM}$	Pulsed Drain Current ⑤	640	
$P_D$ @ $T_C = 25^\circ\text{C}$	Power Dissipation ④	125	
$P_D$ @ $T_C = 100^\circ\text{C}$	Power Dissipation ④	63	
$P_D$ @ $T_A = 25^\circ\text{C}$	Power Dissipation ①	3.3	
$E_{AS}$	Single Pulse Avalanche Energy ⑥	257	mJ
$I_{AR}$	Avalanche Current ⑤	See Fig.18a, 18b, 16, 17	A
$E_{AR}$	Repetitive Avalanche Energy ⑤		mJ
$T_P$	Peak Soldering Temperature	270	
$T_J$	Operating Junction and	-55 to + 175	°C
$T_{STG}$	Storage Temperature Range		

## Thermal Resistance

	Parameter	Typ.	Max.	Units
$R_{0JA}$	Junction-to-Ambient ③	—	45	
$R_{0JA}$	Junction-to-Ambient ⑧	12.5	—	
$R_{0JA}$	Junction-to-Ambient ⑨	20	—	°C/W
$R_{0J-Can}$	Junction-to-Can ④⑩	—	1.2	
$R_{0J-PCB}$	Junction-to-PCB Mounted	—	0.5	
	Linear Derating Factor ④	0.83		W/°C

HEXFET® is a registered trademark of International Rectifier.


## Static Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise stated)


	Parameter	Min.	Typ.	Max.	Units	Conditions
$\text{BV}_{\text{DSS}}$	Drain-to-Source Breakdown Voltage	75	—	—	V	$V_{\text{GS}} = 0\text{V}$ , $I_D = 250\mu\text{A}$
$\Delta \text{BV}_{\text{DSS}}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	—	0.02	—	V/ $^\circ\text{C}$	Reference to $25^\circ\text{C}$ , $I_D = 2\text{mA}$
$R_{\text{DS(on)}}$	Static Drain-to-Source On-Resistance	—	1.8	2.3	$\text{m}\Omega$	$V_{\text{GS}} = 10\text{V}$ , $I_D = 96\text{A}$ ⑦
$V_{\text{GS(th)}}$	Gate Threshold Voltage	2.0	3.0	4.0	V	
$\Delta V_{\text{GS(th)}}/\Delta T_J$	Gate Threshold Voltage Coefficient	—	-11	—	$\text{mV}/^\circ\text{C}$	
$g_{\text{fs}}$	Forward Transconductance	74	—	—	S	$V_{\text{DS}} = 25\text{V}$ , $I_D = 96\text{A}$
$I_{\text{DSS}}$	Drain-to-Source Leakage Current	—	—	20	$\mu\text{A}$	$V_{\text{DS}} = 75\text{V}$ , $V_{\text{GS}} = 0\text{V}$
		—	—	250		$V_{\text{DS}} = 60\text{V}$ , $V_{\text{GS}} = 0\text{V}$ , $T_J = 125^\circ\text{C}$
$I_{\text{GSS}}$	Gate-to-Source Forward Leakage	—	—	100	$\text{nA}$	$V_{\text{GS}} = 20\text{V}$
	Gate-to-Source Reverse Leakage	—	—	-100		$V_{\text{GS}} = -20\text{V}$

## Dynamic Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise stated)

$Q_g$	Total Gate Charge	—	200	300	nC	
$Q_{\text{gs}1}$	Pre-V <sub>th</sub> Gate-to-Source Charge	—	37	—		$V_{\text{DS}} = 38\text{V}$
$Q_{\text{gs}2}$	Post-V <sub>th</sub> Gate-to-Source Charge	—	11	—		$V_{\text{GS}} = 10\text{V}$
$Q_{\text{gd}}$	Gate-to-Drain Charge	—	62	93		$I_D = 96\text{A}$
$Q_{\text{godr}}$	Gate Charge Overdrive	—	91	—		See Fig. 9
$Q_{\text{sw}}$	Switch Charge ( $Q_{\text{gs}2} + Q_{\text{gd}}$ )	—	73	—		
$Q_{\text{oss}}$	Output Charge	—	60	—	nC	$V_{\text{DS}} = 16\text{V}$ , $V_{\text{GS}} = 0\text{V}$
$R_G$	Gate Resistance	—	1.1	—	$\Omega$	
$t_{\text{d(on)}}$	Turn-On Delay Time	—	18	—	ns	$V_{\text{DD}} = 38\text{V}$ , $V_{\text{GS}} = 10\text{V}$ ⑦
$t_r$	Rise Time	—	37	—		$I_D = 96\text{A}$
$t_{\text{d(off)}}$	Turn-Off Delay Time	—	80	—		$R_G = 1.8\Omega$
$t_f$	Fall Time	—	33	—		
$C_{\text{iss}}$	Input Capacitance	—	12222	—	pF	$V_{\text{GS}} = 0\text{V}$
$C_{\text{oss}}$	Output Capacitance	—	1465	—		$V_{\text{DS}} = 25\text{V}$
$C_{\text{rss}}$	Reverse Transfer Capacitance	—	609	—		$f = 1.0\text{MHz}$
$C_{\text{oss}}$	Output Capacitance	—	7457	—		$V_{\text{GS}} = 0\text{V}$ , $V_{\text{DS}} = 1.0\text{V}$ , $f = 1.0\text{MHz}$
$C_{\text{oss}}$	Output Capacitance	—	955	—		$V_{\text{GS}} = 0\text{V}$ , $V_{\text{DS}} = 60\text{V}$ , $f = 1.0\text{MHz}$


## Diode Characteristics @ $T_J = 25^\circ\text{C}$ (unless otherwise stated)

	Parameter	Min.	Typ.	Max.	Units	Conditions
$I_s$	Continuous Source Current (Body Diode)	—	—	160	A	MOSFET symbol showing the integral reverse p-n junction diode.
$I_{\text{SM}}$	Pulsed Source Current (Body Diode) ⑤	—	—	640		
$V_{\text{SD}}$	Diode Forward Voltage	—	—	1.3	V	$T_J = 25^\circ\text{C}$ , $I_s = 96\text{A}$ , $V_{\text{GS}} = 0\text{V}$ ⑦
$t_{\text{rr}}$	Reverse Recovery Time	—	64	96	ns	$T_J = 25^\circ\text{C}$ , $I_F = 96\text{A}$ , $V_{\text{DD}} = 38\text{V}$
$Q_{\text{rr}}$	Reverse Recovery Charge	—	150	225	nC	$di/dt = 100\text{A}/\mu\text{s}$ ⑦




⑤ Surface mounted on 1 in. square Cu (still air).

Notes ① through ⑩ are on page 10



⑤ Mounted to a PCB with small clip heatsink (still air)



⑤ Mounted on minimum footprint full size board with metallized back and with small clip heatsink (still air)

**Qualification Information<sup>†</sup>**

		Automotive (per AEC-Q101) <sup>††</sup>	
<b>Qualification Level</b>		Comments: This part number(s) passed Automotive qualification. IR's Industrial and Consumer qualification level is granted by extension of the higher Automotive level.	
<b>Moisture Sensitivity Level</b>		LARGE-CAN	MSL1
<b>ESD</b>	Machine Model	Class M4 (+/- 800V) (per AEC-Q101-002)	
	Human Body Model	Class H2 (+/- 6000V) (per AEC-Q101-001)	
	Charged Device Model	N/A (per AEC-Q101-005)	
<b>RoHS Compliant</b>		Yes	

<sup>†</sup> Qualification standards can be found at International Rectifier's web site: <http://www.irf.com/>

<sup>††</sup> Exceptions (if any) to AEC-Q101 requirements are noted in the qualification report.

# AUIRF7759L2TR/TR1

International  
Rectifier




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. Typical On-Resistance vs. Gate Voltage




Fig 4. Typical On-Resistance vs. Drain Current




Fig 5. Typical Transfer Characteristics







Fig 6. Normalized On-Resistance vs. Temperature



**Fig 7.** Typical Threshold Voltage vs. Junction Temperature




**Fig 9.** Typical Forward Transconductance vs. Drain Current




**Fig 11** Typical Gate Charge vs. Gate-to-Source Voltage


## AUIRF7759L2TR/TR1



**Fig 8.** Typical Source-Drain Diode Forward Voltage



**Fig 10.** Typical Capacitance vs. Drain-to-Source Voltage



**Fig 12.** Maximum Drain Current vs. Case Temperature




Fig 13. Maximum Safe Operating Area




Fig 14. Maximum Avalanche Energy vs. Temperature




Fig 15. Maximum Effective Transient Thermal Impedance, Junction-to-Case




Fig 16. Typical Avalanche Current vs. Pulsewidth




Fig 17. Maximum Avalanche Energy vs. Temperature




Fig 18a. Unclamped Inductive Test Circuit

$$P_D(\text{ave}) = 1/2 (1.3 \cdot BV \cdot I_{av}) = \Delta T / Z_{thJC}$$

$$I_{av} = 2\Delta T / [1.3 \cdot BV \cdot Z_{th}]$$

$$E_{AS(AR)} = P_D(\text{ave}) \cdot t_{av}$$




Fig 18b. Unclamped Inductive Waveforms




Fig 19a. Gate Charge Test Circuit




Fig 19b. Gate Charge Waveform





Fig 20a. Switching Time Test Circuit

Fig 20b. Switching Time Waveforms

Notes on Repetitive Avalanche Curves , Figures 14, 17:  
(For further info, see AN-1005 at [www.irf.com](http://www.irf.com))


1. Avalanche failures assumption:  
Purely a thermal phenomenon and failure occurs at a temperature far in excess of  $T_{jmax}$ . This is validated for every part type.
2. Safe operation in Avalanche is allowed as long as  $T_{jmax}$  is not exceeded.
3. Equation below based on circuit and waveforms shown in Figures 18a, 18b.
4.  $P_D(\text{ave})$  = Average power dissipation per single avalanche pulse.
5.  $BV$  = Rated breakdown voltage (1.3 factor accounts for voltage increase during avalanche).
6.  $I_{av}$  = Allowable avalanche current.
7.  $\Delta T$  = Allowable rise in junction temperature, not to exceed  $T_{jmax}$  (assumed as 25°C in Figure 15, 16).  
 $t_{av}$  = Average time in avalanche.  
 $D$  = Duty cycle in avalanche =  $t_{av} / f$   
 $Z_{thJC}(D, t_{av})$  = Transient thermal resistance, see figure 11



**Fig 21.** Diode Reverse Recovery Test Circuit for HEXFET® Power MOSFETs


## Automotive DirectFET® Board Footprint, L8 (Large Size Can).

Please see AN-1035 for DirectFET® assembly details and stencil and substrate design recommendations.




Note: For the most current drawing please refer to IR website at <http://www.irf.com/package>

**Automotive DirectFET® Outline Dimension, L8 Outline (LargeSize Can).**  
Please see AN-1035 for DirectFET® assembly details and stencil and substrate design recommendations




CODE	DIMENSIONS		IMPERIAL	
	Metric		MIN	MAX
A	9.05	9.15	0.356	0.360
B	6.85	7.10	0.270	0.280
C	5.90	6.00	0.232	0.236
D	0.55	0.65	0.022	0.026
E	0.58	0.62	0.023	0.024
F	1.18	1.22	0.046	0.048
G	0.98	1.02	0.039	0.040
H	0.73	0.77	0.029	0.030
J	0.38	0.42	0.015	0.017
K	1.35	1.45	0.053	0.057
L	2.55	2.65	0.100	0.104
L1	5.35	5.45	0.211	0.215
M	0.68	0.74	0.027	0.029
P	0.09	0.17	0.003	0.007
R	0.02	0.08	0.001	0.003

**Automotive DirectFET® Part Marking**




## Automotive DirectFET® Tape & Reel Dimension (Showing component orientation).



NOTE: Controlling dimensions in mm  
 Std reel quantity is 4000 parts. (ordered as AUIRF7759L2TR). For 1000 parts on 7" reel, order AUIRF7759L2TR1

REEL DIMENSIONS								
CODE	STANDARD OPTION (QTY 4000)		TR1 OPTION (QTY 1000)		STANDARD OPTION (QTY 4000)		TR1 OPTION (QTY 1000)	
	METRIC	IMPERIAL	METRIC	IMPERIAL	METRIC	IMPERIAL	METRIC	IMPERIAL
A	330.00	N.C	12.992	N.C	177.80	N.C	7.000	N.C
B	20.20	N.C	0.795	N.C	20.20	N.C	0.795	N.C
C	12.80	13.20	0.504	0.520	12.98	13.50	0.331	0.50
D	1.50	N.C	0.059	N.C	1.50	2.50	0.059	N.C
E	99.00	100.00	3.900	3.940	62.48	N.C	2.460	N.C
F	N.C	22.40	N.C	0.880	N.C	N.C	N.C	0.53
G	16.40	18.40	0.650	0.720	N.C	N.C	N.C	N.C
H	15.90	19.40	0.630	0.760	16.00	N.C	0.630	N.C



NOTE: CONTROLLING DIMENSIONS IN MM

DIMENSIONS			
	METRIC	IMPERIAL	
CODE	MIN	MAX	MIN
A	11.90	12.10	4.69
B	3.90	4.10	0.154
C	15.90	16.30	0.623
D	7.40	7.60	0.291
E	7.20	7.40	0.283
F	9.90	10.10	0.390
G	1.50	N.C	0.059
H	1.50	1.60	0.059
			0.063

Note: For the most current drawing please refer to IR website at <http://www.irf.com/package>

### Notes:

- ① Click on this section to link to the appropriate technical paper.
- ② Click on this section to link to the DirectFET® Website.
- ③ Surface mounted on 1 in. square Cu board, steady state.
- ④  $T_C$  measured with thermocouple mounted to top (Drain) of part.
- ⑤ Repetitive rating; pulse width limited by max. junction temperature.
- ⑥ Starting  $T_J = 25^\circ\text{C}$ ,  $L = 0.056\text{mH}$ ,  $R_G = 25\Omega$ ,  $I_{AS} = 96\text{A}$ .
- ⑦ Pulse width  $\leq 400\mu\text{s}$ ; duty cycle  $\leq 2\%$ .
- ⑧ Used double sided cooling, mounting pad with large heatsink.
- ⑨ Mounted on minimum footprint full size board with metalized back and with small clip heatsink.
- ⑩  $R_\theta$  is measured at  $T_J$  of approximately  $90^\circ\text{C}$ .

**Ordering Information**

Base part number	Package Type	Standard Pack		Complete Part Number
		Form	Quantity	
AUIRF7759L2	DirectFET2 Large Can	Tape and Reel	4000	AUIRF7759L2TR
		Tape and Reel	1000	AUIRF7759L2TR1

**IMPORTANT NOTICE**

Unless specifically designated for the automotive market, International Rectifier Corporation and its subsidiaries (IR) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or services without notice. Part numbers designated with the "AU" prefix follow automotive industry and / or customer specific requirements with regards to product discontinuance and process change notification. All products are sold subject to IR's terms and conditions of sale supplied at the time of order acknowledgment.

IR warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with IR's standard warranty. Testing and other quality control techniques are used to the extent IR deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

IR assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using IR components. To minimize the risks with customer products and applications, customers should provide adequate design and operating safeguards.

Reproduction of IR information in IR data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alterations is an unfair and deceptive business practice. IR is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of IR products or serviced with statements different from or beyond the parameters stated by IR for that product or service voids all express and any implied warranties for the associated IR product or service and is an unfair and deceptive business practice. IR is not responsible or liable for any such statements.

IR products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or in any other application in which the failure of the IR product could create a situation where personal injury or death may occur. Should Buyer purchase or use IR products for any such unintended or unauthorized application, Buyer shall indemnify and hold International Rectifier and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that IR was negligent regarding the design or manufacture of the product.

Only products certified as military grade by the Defense Logistics Agency (DLA) of the US Department of Defense, are designed and manufactured to meet DLA military specifications required by certain military, aerospace or other applications. Buyers acknowledge and agree that any use of IR products not certified by DLA as military-grade, in applications requiring military grade products, is solely at the Buyer's own risk and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

IR products are neither designed nor intended for use in automotive applications or environments unless the specific IR products are designated by IR as compliant with ISO/TS 16949 requirements and bear a part number including the designation "AU". Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, IR will not be responsible for any failure to meet such requirements.

For technical support, please contact IR's Technical Assistance Center  
<http://www.irf.com/technical-info/>

**WORLD HEADQUARTERS:**  
101 N. Sepulveda Blvd., El Segundo, California 90245  
Tel: (310) 252-7105

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[International Rectifier:](#)

[AUIRF7759L2TR](#)