

# HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS



PH08XXNL Series (up to 160W)




- Power Rating: up to 160 W
- Height: 8.6mm to 9.1mm Max
- Footprint: 23.4mm x 21.6mm Max
- Frequency Range: 200kHz to 700kHz
- Isolation (Primary to Secondary): 1500 V<sub>DC</sub>

Electrical Specifications @ 25°C - Operating Temperature -40°C to +125°C


| Part <sup>3</sup><br>Number | Turns     |           |                  | Schematic | Primary <sup>1</sup><br>Inductance<br>(μ MIN) | Leakage <sup>2</sup><br>Inductance<br>(μ MAX) | DCR (mΩ MAX) |           |             | Maximum<br>Height<br>(mm) |
|-----------------------------|-----------|-----------|------------------|-----------|-----------------------------------------------|-----------------------------------------------|--------------|-----------|-------------|---------------------------|
|                             | Primary A | Primary B | Secondary        |           |                                               |                                               | Primary A    | Primary B | Secondary   |                           |
| PH0801NL                    | 4T        | 4T        | 4T<br>(1T:1T:1T) | A1        | 153                                           | 0.45                                          | 8.5          | 8.5       | 7           | 8.6                       |
| PH0802NL                    | 4T        | 5T        |                  |           | 194                                           | 0.45                                          | 8.5          | 12.5      | 7           | 8.6                       |
| PH0803NL                    | 5T        | 5T        |                  |           | 240                                           | 0.55                                          | 12.5         | 12.5      | 7           | 8.6                       |
| PH0804NL                    | 5T        | 6T        |                  |           | 290                                           | 0.60                                          | 12.5         | 14.2      | 7           | 9.1                       |
| PH0805NL                    | 6T        | 6T        |                  |           | 345                                           | 0.65                                          | 14.2         | 14.2      | 7           | 9.1                       |
| PH0806NL                    | 4T        | 4T        | 1T & 1T          | A2        | 153                                           | 0.45                                          | 8.5          | 8.5       | .875 & .875 | 8.6                       |
| PH0807NL                    | 4T        | 5T        |                  |           | 194                                           | 0.55                                          | 8.5          | 12.5      | .875 & .875 | 8.6                       |
| PH0808NL                    | 5T        | 5T        |                  |           | 240                                           | 0.55                                          | 12.5         | 12.5      | .875 & .875 | 8.6                       |
| PH0809NL                    | 5T        | 6T        |                  |           | 290                                           | 0.90                                          | 12.5         | 14.2      | .875 & .875 | 9.1                       |
| PH0810NL                    | 6T        | 6T        |                  |           | 345                                           | 1.00                                          | 14.2         | 14.2      | .875 & .875 | 9.1                       |
| PH0811NL                    | 4T        | 4T        | 2T & 1T          | A3        | 153                                           | 0.45                                          | 8.5          | 8.5       | 1.75 & 1.75 | 8.6                       |
| PH0812NL                    | 4T        | 5T        |                  |           | 194                                           | 0.45                                          | 8.5          | 12.5      | 1.75 & 1.75 | 8.6                       |
| PH0813NL                    | 5T        | 5T        |                  |           | 240                                           | 0.55                                          | 12.5         | 12.5      | 1.75 & 1.75 | 9.1                       |
| PH0814NL                    | 5T        | 6T        |                  |           | 290                                           | 0.65                                          | 12.5         | 14.2      | 1.75 & 1.75 | 9.1                       |
| PH0815NL                    | 6T        | 6T        |                  |           | 345                                           | 0.85                                          | 14.2         | 14.2      | 1.75 & 1.75 | 9.1                       |

## Mechanicals

### PH08XXNL




### SUGGESTED PAD LAYOUT



Weight ..... 11.0 grams  
Tape & Reel ..... 180/reel  
Tray ..... 40/tray

Dimensions: Inches  
mm  
Unless otherwise specified,  
all tolerances are ± .010  
0,25

### Tape & Reel Layout for PH0801NL THRU PH0815NL



**NOTE:** The above is a universal footprint for a component that has all 11 pins populated. For a given part number, it is only necessary to provide pads for the terminations shown in the schematics on the next page.


# HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS

PH08XXNL Series (up to 160W)


## Schematics

### PH08XXNL


#### A1 PH0801 / 02 / 03 / 04 / 05



#### A2 PH0806 / 07 / 08 / 09 / 10



#### A3 PH0811 / 12 / 13 / 14 / 15




### Notes:

1. Inductance is measured with both primary windings connected in services (2 to 5, with 3 and 4 shorted).
2. Leakage inductance is measured on winding (2-5) with (3-4) and (7, 8, 9, 10, 11) shorted.
3. The "NL" suffix indicates an RoHS-compliant part number.
4. It is possible to add a primary side aux. winding to any of the above configurations as shown in the schematics. Transformers with primary side aux. winding are non-standard and can be made available upon request. The primary aux. winding can be between 2 and 16 turns. To add a primary aux. winding to a given base, use the

- extension .xxx. For example, to add a 4T aux. winding to the base part number PH0801NL, use the part number PH0801.004NL. The height increases by 0.5mm for .xxx part. For example, **PH0801NL** is 8.6mm MAX, **PH0801.004NL** is 9.1mm MAX.
5. Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the complete number (i.e. **PH0801.009NL** becomes **PH0801.009NLT**).
6. To determine if the transformer is suitable for your application, it is necessary to ensure that the temperature rise of the component (ambient plus temperature rise) not exceed its operating temperature. To determine the approximate temperature rise of the transformer, refer to the graphs below.

## Core Loss vs Flux Density




# HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS

PH08XXNL Series (up to 160W)



## Temperature Rise vs. Power (W) Dissipation



### For More Information

#### Pulse Worldwide Headquarters

15255 Innovation Drive Ste 100  
San Diego, CA 92128  
U.S.A.

Tel: 858 674 8100  
Fax: 858 674 8262

#### Pulse Europe

Pulse Electronics GmbH  
Am Rottland 12  
58540 Meinerzhagen  
Germany

Tel: 49 2354 777 100  
Fax: 49 2354 777 168

#### Pulse China Headquarters

Pulse Electronics (ShenZhen) CO., LTD  
D708, Shenzhen Academy of  
Aerospace Technology,  
The 10th Keji South Road,  
Nanshan District, Shenzhen, P.R.  
China 518057

Tel: 86 755 33966678  
Fax: 86 755 33966700

#### Pulse North China

Room 2704/2705  
Super Ocean Finance Ctr.  
2067 Yan An Road West  
Shanghai 200336  
China

Tel: 86 21 62787060  
Fax: 86 2162786973

#### Pulse South Asia

3 Fraser Street  
0428 DUO Tower  
Singapore 189352

Tel: 65 6287 8998  
Fax: 65 6280 0080

#### Pulse North Asia

1F, No.111  
Xiyuan Road  
Zhongli District  
Taoyuan City 32057  
Taiwan (R.O.C)

Tel: 886 3 4356768  
Fax: 886 3 4356820

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2018. Pulse Electronics, Inc. All rights reserved.