


High Speed Switching Transistors



Features:

- NPN silicon planar epitaxial transistors
- Fast switching devices exhibiting short turn-off and low saturation voltage characteristics
- NPN silicon high speed saturated switching, transistors with low power and high speed switching applications

TO-18 Metal Can Package



Dimensions	Minimum	Maximum
A	5.24	5.84
B	4.52	4.97
C	4.31	5.33
D	0.4	0.53
E	-	0.76
F	-	1.27
G	-	2.97
H	0.91	1.17
J	0.71	1.21
K	12.7	-
L	45°	

Dimensions : Millimetres



Pin Configuration

1. Emitter
2. Base
3. Collector

High Speed Switching Transistors

Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Collector Emitter Voltage	V _{CEO}	15	V
	V _{CES}	40	
Collector Base Voltage	V _{CBO}		
Emitter Base Voltage	V _{EBO}	4.5	
Collector Current Continuous	I _C	200	mA
Collector Current Peak (10 μs Pulse)	I _C (Peak)	500	
Power Dissipation at T _C = 25°C Derate above 25°C	P _D	360 2.06	mW mW / °C
Power Dissipation at T _C = 25°C T _C = 100°C Derate above 100°C	P _D	1.2 0.68 6.85	W mW / °C
Operating and Storage Junction Temperature Range	T _j , T _{stg}	-65 to +200	°C

Electrical Characteristics ($T_a = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	2N2369	2N2369A	Unit
Collector Emitter Voltage	V _{CEO} * (sus)	I _C = 10 mA, I _B = 0	>15		V
	V _{CES}	I _C = 10 μA, V _{BE} = 0	>40		
Collector Base Voltage	V _{CBO}	I _C = 10 μA, I _E = 0	>40		
Emitter Base Voltage	V _{EBO}	I _E = 10 μA, I _C = 0	>4.5		
Collector Cut off Current	I _{CBO}	V _{CB} = 20 V, I _E = 0	<400	-	nA
	I _{CES}	V _{CB} = 20 V, I _E = 0, T _a = 150°C	<30	-	μA
		V _{CE} = 20 V, V _{BE} = 0	-	<400	nA
Base Current	I _B	V _{CE} = 20 V, V _{BE} = 0	-	<400	nA
Collector Emitter Saturation Voltage	V _{CE (sat)} *	I _C = 10 mA, I _B = 1 mA	<0.25	<0.2	V
		I _C = 30 mA, I _B = 3 mA	-	<0.25	
		I _C = 100 mA, I _B = 10 mA	-	<0.5	
		I _C = 10 mA, I _B = 1 mA, T _a = 125°C	-	<0.3	
Base Emitter Saturation Voltage	V _{BE (sat)} *	I _C = 10 mA, I _B = 1 mA	0.7 to 0.85	0.7 to 0.85	
		I _C = 30 mA, I _B = 3 mA	-	<1.15	
		I _C = 100 mA, I _B = 10 mA	-	<1.6	
		I _C = 10 mA, I _B = 1 mA, T _a = +125°C	-	>0.59	
		I _C = 10 mA, I _B = 1 mA, T _a = -55°C	-	<1.2	
DC Current Gain	h _{FE} *	I _C = 10 mA, V _{CE} = 1 V	40 to 120	40 to 120	-
		I _C = 10 mA, V _{CE} = 1 V, T _a = -55°C	>20	-	
		I _C = 100 mA, V _{CE} = 0.35 V, T _a = -55°C	-	>20	
		I _C = 10 mA, V _{CE} = 0.35 V	-	40 to 120	
		I _C = 30 mA, V _{CE} = 0.4 V	-	>30	
		I _C = 100 mA, V _{CE} = 1 V	-	>20	
		I _C = 100 mA, V _{CE} = 2 V	>20	-	

High Speed Switching Transistors

Parameter	Symbol	Test Condition	2N2369	2N2369A	Unit
Small Signal Characteristic					
Transition Frequency	f _t	V _{CE} = 10 V, I _C = 10 mA, f = 100 MHz	>500		MHz
Output Capacitance	C _{obo}	V _{CB} = 5 V, I _E = 0, f = 140 kHz	<4		pF
Turn on Time	t _{on}	I _C = 10 mA, I _{B1} = 3 mA, I _B = -1.5 mA, V _{CC} = 3 V	<12		ns
Turn off Time	t _{off}	I _C = 10 mA, I _{B1} = 3 mA, I _B = -1.5 mA, V _{CC} = 3 V	-	<15	
Storage time	t _s	I _C = 100 mA, I _{B1} = I _B = 10 mA, V _{CC} = 10 V	<13		

*Pulse Test : Pulse Width = 300 μ s, Duty Cycle = 2%

Specification Table

V_{CEO} Maximum (V)	I_C Maximum (A)	$V_{CE(sat)}$ Maximum (V) at $I_C = 10\text{ mA}$	t_{off} Maximum (ns) at $I_C = 10\text{ mA}$	h_{FE} Minimum at $I_C = 10\text{ mA}$	P_D at $T_a = 25^\circ\text{C}$ (mW)	Package and Pin Out	Part Number
15	0.2	0.25	18	40	360	TO-18	2N2369
		0.2					2N2369A

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.