

## Solid State Relays for Heaters

# G3PE-Single-phase

**Slim Width Industrial SSR with heat sink  
ideal for Heater Control.**



- 15A and 25A models have 22.5mm width.
- Single-phase models have attached heat sink allowing for quick easy track mount installation.
- Load voltage available in 240VAC and 480VAC.
- Zero cross or "random turn on" models.
- Snubber circuit provides excellent short-term surge absorption.
- UL, CSA, and TUV Approved. Also CE Marked.
- RoHS Compliant.



 Refer to *Safety Precautions for All G3PE Models.*

## Ordering Information

### List of Models

| Number of phases | Insulation method  | Operation indicator | Rated input voltage | Zero cross function | Applicable load *    | Model                     |
|------------------|--------------------|---------------------|---------------------|---------------------|----------------------|---------------------------|
| Single-phase     | Phototriac coupler | Yes (yellow)        | 12 to 24 VDC        | Yes                 | 15 A, 100 to 240 VAC | <b>G3PE-215B DC12-24</b>  |
|                  |                    |                     |                     |                     | 25 A, 100 to 240 VAC | <b>G3PE-225B DC12-24</b>  |
|                  |                    |                     |                     |                     | 35 A, 100 to 240 VAC | <b>G3PE-235B DC12-24</b>  |
|                  |                    |                     |                     |                     | 45 A, 100 to 240 VAC | <b>G3PE-245B DC12-24</b>  |
|                  |                    |                     |                     | No                  | 15 A, 100 to 240 VAC | <b>G3PE-215BL DC12-24</b> |
|                  |                    |                     |                     |                     | 25 A, 100 to 240 VAC | <b>G3PE-225BL DC12-24</b> |
|                  |                    |                     |                     |                     | 35 A, 100 to 240 VAC | <b>G3PE-235BL DC12-24</b> |
|                  |                    |                     |                     |                     | 45 A, 100 to 240 VAC | <b>G3PE-245BL DC12-24</b> |
|                  |                    |                     |                     | Yes                 | 15 A, 200 to 480 VAC | <b>G3PE-515B DC12-24</b>  |
|                  |                    |                     |                     |                     | 25 A, 200 to 480 VAC | <b>G3PE-525B DC12-24</b>  |
|                  |                    |                     |                     |                     | 35 A, 200 to 480 VAC | <b>G3PE-535B DC12-24</b>  |
|                  |                    |                     |                     |                     | 45 A, 200 to 480 VAC | <b>G3PE-545B DC12-24</b>  |
|                  |                    |                     |                     | No                  | 15 A, 200 to 480 VAC | <b>G3PE-515BL DC12-24</b> |
|                  |                    |                     |                     |                     | 25 A, 200 to 480 VAC | <b>G3PE-525BL DC12-24</b> |
|                  |                    |                     |                     |                     | 35 A, 200 to 480 VAC | <b>G3PE-535BL DC12-24</b> |
|                  |                    |                     |                     |                     | 45 A, 200 to 480 VAC | <b>G3PE-545BL DC12-24</b> |

\* The applicable load current depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature* in *Engineering Data* on page 3.

## Specifications

## Certification

UL508, CSA22.2 No.14, and EN60947-4-3

## Ratings

## Input (at an Ambient Temperature of 25°C)

| Model      | Item | Rated voltage | Operating voltage range | Rated input current | Voltage level        |                      |
|------------|------|---------------|-------------------------|---------------------|----------------------|----------------------|
|            |      |               |                         |                     | Must operate voltage | Must release voltage |
| G3PE-□□□B  |      | 12 to 24 VDC  | 9.6 to 30 VDC           | 7 mA max.           | 9.6 VDC max.         | 1.0 VDC max.         |
| G3PE-□□□BL |      |               |                         | 15 mA max.          |                      |                      |

## Output

| Model                                             | G3PE-215B(L)                 | G3PE-225B(L)                 | G3PE-235B(L)              | G3PE-245B(L)             | G3PE-515B(L)                 | G3PE-525B(L)                 | G3PE-535B(L)              | G3PE-545B(L)             |
|---------------------------------------------------|------------------------------|------------------------------|---------------------------|--------------------------|------------------------------|------------------------------|---------------------------|--------------------------|
| Item                                              |                              |                              |                           |                          |                              |                              |                           |                          |
| Rated load voltage                                | 100 to 240 VAC (50/60 Hz)    |                              |                           |                          | 200 to 480 VAC (50/60 Hz)    |                              |                           |                          |
| Load voltage range                                | 75 to 264 VAC (50/60 Hz)     |                              |                           |                          | 180 to 528 VAC (50/60 Hz)    |                              |                           |                          |
| Applicable load current *                         | 0.1 to 15 A<br>(at 40°C)     | 0.1 to 25 A<br>(at 40°C)     | 0.5 to 35 A<br>(at 25°C)  | 0.5 to 45 A<br>(at 25°C) | 0.1 to 15 A<br>(at 40°C)     | 0.1 to 25 A<br>(at 40°C)     | 0.5 to 35 A<br>(at 25°C)  | 0.5 to 45 A<br>(at 25°C) |
| Inrush current resistance                         | 150 A<br>(60 Hz,<br>1 cycle) | 220 A<br>(60 Hz,<br>1 cycle) | 440 A<br>(60 Hz, 1 cycle) |                          | 150 A<br>(60 Hz,<br>1 cycle) | 220 A<br>(60 Hz,<br>1 cycle) | 440 A<br>(60 Hz, 1 cycle) |                          |
| Permissible I <sup>2</sup> t<br>(reference value) | 121A <sup>2</sup> s          | 260A <sup>2</sup> s          | 1,260A <sup>2</sup> s     |                          | 128A <sup>2</sup> s          | 1,350A <sup>2</sup> s        |                           | 6,600A <sup>2</sup> s    |
| Applicable load<br>(resistive load)               | 3 kW<br>(at 200 VAC)         | 5 kW<br>(at 200 VAC)         | 7 kW<br>(at 200 VAC)      | 9 kW<br>(at 200 VAC)     | 6 kW<br>(at 400 VAC)         | 10 kW<br>(at 400 VAC)        | 14 kW<br>(at 400 VAC)     | 18 kW<br>(at 400 VAC)    |

\* The applicable load current depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature* in *Engineering Data* on page 3.

## Characteristics


| Model                         | G3PE<br>-215B                                                                                 | G3PE<br>-225B | G3PE<br>-235B | G3PE<br>-245B | G3PE<br>-215BL | G3PE<br>-225BL | G3PE<br>-235BL | G3PE<br>-245BL |
|-------------------------------|-----------------------------------------------------------------------------------------------|---------------|---------------|---------------|----------------|----------------|----------------|----------------|
| Item                          |                                                                                               |               |               |               |                |                |                |                |
| Operate time                  | 1/2 of load power source cycle + 1 ms max.                                                    |               |               |               | 1 ms max.      |                |                |                |
| Release time                  | 1/2 of load power source cycle + 1 ms max.                                                    |               |               |               |                |                |                |                |
| Output ON voltage drop        | 1.6 V (RMS) max.                                                                              |               |               |               |                |                |                |                |
| Leakage current               | 10 mA max. (at 200 VAC)                                                                       |               |               |               |                |                |                |                |
| Insulation resistance         | 100 MΩ min. (at 500 VDC)                                                                      |               |               |               |                |                |                |                |
| Dielectric strength           | 2,500 VAC, 50/60 Hz for 1 min                                                                 |               |               |               |                |                |                |                |
| Vibration resistance          | 10 to 55 to10 Hz, 0.375-mm single amplitude (0.75-mm double amplitude) (Mounted to DIN track) |               |               |               |                |                |                |                |
| Shock resistance              | Destruction: 294 m/s² (Mounted to DIN track)                                                  |               |               |               |                |                |                |                |
| Ambient storage temperature   | −30 to 100°C (with no icing or condensation)                                                  |               |               |               |                |                |                |                |
| Ambient operating temperature | −30 to 80°C (with no icing or condensation)                                                   |               |               |               |                |                |                |                |
| Ambient operating humidity    | 45% to 85%                                                                                    |               |               |               |                |                |                |                |
| Weight                        | Approx. 240 g                                                                                 |               | Approx. 400 g |               | Approx. 240 g  |                | Approx. 400 g  |                |

| Model<br>Item                 | G3PE<br>-515B                                                                                 | G3PE<br>-525B | G3PE<br>-535B | G3PE<br>-545B | G3PE<br>-515BL | G3PE<br>-525BL | G3PE<br>-535BL | G3PE<br>-545BL |
|-------------------------------|-----------------------------------------------------------------------------------------------|---------------|---------------|---------------|----------------|----------------|----------------|----------------|
| Operate time                  | 1/2 of load power source cycle + 1 ms max.                                                    |               |               |               | 1 ms max.      |                |                |                |
| Release time                  | 1/2 of load power source cycle + 1 ms max.                                                    |               |               |               |                |                |                |                |
| Output ON voltage drop        | 1.8 V (RMS) max.                                                                              |               |               |               |                |                |                |                |
| Leakage current               | 20 mA max. (at 480 VAC)                                                                       |               |               |               |                |                |                |                |
| Insulation resistance         | 100 MΩ min. (at 500 VDC)                                                                      |               |               |               |                |                |                |                |
| Dielectric strength           | 2,500 VAC, 50/60 Hz for 1 min                                                                 |               |               |               |                |                |                |                |
| Vibration resistance          | 10 to 55 to10 Hz, 0.375-mm single amplitude (0.75-mm double amplitude) (Mounted to DIN track) |               |               |               |                |                |                |                |
| Shock resistance              | Destruction: 294 m/s <sup>2</sup> (Mounted to DIN track)                                      |               |               |               |                |                |                |                |
| Ambient storage temperature   | −30 to 100°C (with no icing or condensation)                                                  |               |               |               |                |                |                |                |
| Ambient operating temperature | −30 to 80°C (with no icing or condensation)                                                   |               |               |               |                |                |                |                |
| Ambient operating humidity    | 45% to 85%                                                                                    |               |               |               |                |                |                |                |
| Weight                        | Approx. 240 g                                                                                 |               | Approx. 400 g |               | Approx. 240 g  |                | Approx. 400 g  |                |


# Engineering Data

## Input Voltage vs. Input Impedance and Input Voltage vs. Input Current


### G3PE-2□□B




### G3PE-2□□BL



### G3PE-5□□B




### G3PE-5□□BL




## Load Current vs. Ambient Temperature

### G3PE-215B(L), G3PE-225B(L) G3PE-515B(L), G3PE-525B(L)




### G3PE-235B(L), G3PE-245B(L) G3PE-535B(L), G3PE-545B(L)




## Inrush Current Resistance: Non-repetitive

Make sure the inrush current stays below the dashed line curve if it occurs repetitively.


### G3PE-215B(L), G3PE-515B(L)



### G3PE-225B(L), G3PE-525B(L)




### G3PE-235B(L), G3PE-245B(L) G3PE-535B(L), G3PE-545B(L)




# Close Mounting (3 or 8 SSRs)


**G3PE-215B(L)**




**G3PE-225B(L)**




**G3PE-235B(L)**




**G3PE-245B(L)**




**G3PE-515B(L)**




**G3PE-525B(L)**




**G3PE-535B(L)**



**G3PE-545B(L)**



## Close Mounting Example




## Dimensions

**Note:** All units are in millimeters unless otherwise indicated.


### Solid State Relays

G3PE-215B(L)  
G3PE-225B(L)  
G3PE-515B(L)  
G3PE-525B(L)




**Note:** Without terminal cover.


**Note:** With terminal cover.



#### Terminal Arrangement/Internal Circuit Diagram




G3PE-235B(L)  
G3PE-245B(L)  
G3PE-535B(L)  
G3PE-545B(L)




**Note:** Without terminal cover.

**Note:** With terminal cover.



#### Terminal Arrangement/Internal Circuit Diagram



## Read and Understand This Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

## Warranty and Limitations of Liability

### WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

### LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY.

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

## Application Considerations

### SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
- Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

### PROGRAMMABLE PRODUCTS

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

## Disclaimers

### CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the products may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased products.

### DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

### PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

### ERRORS AND OMISSIONS

The information in this document has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.


## Solid State Relays for Heaters

## G3PE-Three-phase

## DIN Track Mountable Solid State Contactors ideal for Three-phase Heater Applications.



- Slim relay units with three-phase output.
- DIN track models with attached heat sink allow for quick easy track mount installation.
- Load voltage available in 240VAC and 480VAC.
- Snubber circuit provides excellent short-term surge absorption.
- UL, CSA, and TUV Approved. Also CE Marked.
- RoHS Compliant.



## Ordering Information

 Refer to *Safety Precautions for All G3PE Models.*

## List of Models

### Models with Built-in Heat Sinks

| Number of phases | Insulation method  | Operation indicator | Rated input voltage | Zero cross function | Type                   | Applicable load *1   | Number of poles | Model                |
|------------------|--------------------|---------------------|---------------------|---------------------|------------------------|----------------------|-----------------|----------------------|
| Three-phase      | Phototriac coupler | Yes (yellow)        | 12 to 24 VDC        | Yes                 | DIN track mounting * 2 | 15 A, 100 to 240 VAC | 3               | G3PE-215B-3N DC12-24 |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-215B-2N DC12-24 |
|                  |                    |                     |                     |                     |                        | 25 A, 100 to 240 VAC | 3               | G3PE-225B-3N DC12-24 |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-225B-2N DC12-24 |
|                  |                    |                     |                     |                     |                        | 35 A, 100 to 240 VAC | 3               | G3PE-235B-3N DC12-24 |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-235B-2N DC12-24 |
|                  |                    |                     |                     |                     |                        | 45 A, 100 to 240 VAC | 3               | G3PE-245B-3N DC12-24 |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-245B-2N DC12-24 |
|                  |                    |                     |                     |                     |                        | 15 A, 200 to 480 VAC | 3               | G3PE-515B-3N DC12-24 |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-515B-2N DC12-24 |
|                  |                    |                     |                     |                     |                        | 25 A, 200 to 480 VAC | 3               | G3PE-525B-3N DC12-24 |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-525B-2N DC12-24 |
|                  |                    |                     |                     |                     |                        | 35 A, 200 to 480 VAC | 3               | G3PE-535B-3N DC12-24 |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-535B-2N DC12-24 |
|                  |                    |                     |                     |                     |                        | 45 A, 200 to 480 VAC | 3               | G3PE-545B-3N DC12-24 |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-545B-2N DC12-24 |
|                  |                    |                     |                     |                     | Screw mounting         | 15 A, 100 to 240 VAC | 3               | G3PE-215B-3 DC12-24  |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-215B-2 DC12-24  |
|                  |                    |                     |                     |                     |                        | 25 A, 100 to 240 VAC | 3               | G3PE-225B-3 DC12-24  |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-225B-2 DC12-24  |
|                  |                    |                     |                     |                     |                        | 35 A, 100 to 240 VAC | 3               | G3PE-235B-3 DC12-24  |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-235B-2 DC12-24  |
|                  |                    |                     |                     |                     |                        | 45 A, 100 to 240 VAC | 3               | G3PE-245B-3 DC12-24  |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-245B-2 DC12-24  |
|                  |                    |                     |                     |                     |                        | 15 A, 200 to 480 VAC | 3               | G3PE-515B-3 DC12-24  |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-515B-2 DC12-24  |
|                  |                    |                     |                     |                     |                        | 25 A, 200 to 480 VAC | 3               | G3PE-525B-3 DC12-24  |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-525B-2 DC12-24  |
|                  |                    |                     |                     |                     |                        | 35 A, 200 to 480 VAC | 3               | G3PE-535B-3 DC12-24  |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-535B-2 DC12-24  |
|                  |                    |                     |                     |                     |                        | 45 A, 200 to 480 VAC | 3               | G3PE-545B-3 DC12-24  |
|                  |                    |                     |                     |                     |                        |                      | 2               | G3PE-545B-2 DC12-24  |

\*1. The applicable load current depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature* in *Engineering Data* on page 5.

\*2. The applicable DIN Track is the TR35-15Fe (IEC 60715). For details, refer to the mounting information in the *Safety Precautions for All G3PE Models*.

## Models with Externally Attached Heat Sinks

| Number of phases | Insulation method  | Operation indicator | Rated input voltage | Zero cross function | Type                           | Applicable load *    | Number of poles | Model                |
|------------------|--------------------|---------------------|---------------------|---------------------|--------------------------------|----------------------|-----------------|----------------------|
| Three-phase      | Phototriac coupler | Yes (yellow)        | 12 to 24 VDC        | Yes                 | Externally attached heat sinks | 15 A, 100 to 240 VAC | 3               | G3PE-215B-3H DC12-24 |
|                  |                    |                     |                     |                     |                                |                      | 2               | G3PE-215B-2H DC12-24 |
|                  |                    |                     |                     |                     |                                | 25 A, 100 to 240 VAC | 3               | G3PE-225B-3H DC12-24 |
|                  |                    |                     |                     |                     |                                |                      | 2               | G3PE-225B-2H DC12-24 |
|                  |                    |                     |                     |                     |                                | 35 A, 100 to 240 VAC | 3               | G3PE-235B-3H DC12-24 |
|                  |                    |                     |                     |                     |                                |                      | 2               | G3PE-235B-2H DC12-24 |
|                  |                    |                     |                     |                     |                                | 45 A, 100 to 240 VAC | 3               | G3PE-245B-3H DC12-24 |
|                  |                    |                     |                     |                     |                                |                      | 2               | G3PE-245B-2H DC12-24 |
|                  |                    |                     |                     |                     |                                | 15 A, 200 to 480 VAC | 3               | G3PE-515B-3H DC12-24 |
|                  |                    |                     |                     |                     |                                |                      | 2               | G3PE-515B-2H DC12-24 |
|                  |                    |                     |                     |                     |                                | 25 A, 200 to 480 VAC | 3               | G3PE-525B-3H DC12-24 |
|                  |                    |                     |                     |                     |                                |                      | 2               | G3PE-525B-2H DC12-24 |
|                  |                    |                     |                     |                     |                                | 35 A, 200 to 480 VAC | 3               | G3PE-535B-3H DC12-24 |
|                  |                    |                     |                     |                     |                                |                      | 2               | G3PE-535B-2H DC12-24 |
|                  |                    |                     |                     |                     |                                | 45 A, 200 to 480 VAC | 3               | G3PE-545B-3H DC12-24 |
|                  |                    |                     |                     |                     |                                |                      | 2               | G3PE-545B-2H DC12-24 |

\* The rated load current depends on the heat sink or radiator that is mounted. It also depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature*.

## Accessories (Order Separately)

### Heat Sink

| Heat resistance Rth (s-a) (°C/W) | Model     |
|----------------------------------|-----------|
| 1.67                             | Y92B-P50  |
| 1.01                             | Y92B-P100 |
| 0.63                             | Y92B-P150 |
| 0.43                             | Y92B-P200 |
| 0.36                             | Y92B-P250 |

## Specifications

### Certification

UL508, CSA22.2 No.14, and EN60947-4-3

### Ratings (at an Ambient Temperature of 25°C)

#### Input Circuit (All Models)

| Item                            | Common characteristics |
|---------------------------------|------------------------|
| Rated operating voltage         | 12 to 24 VDC           |
| Operating voltage range         | 9.6 to 30 VDC          |
| Rated input current (impedance) | 10 mA max. (24 VDC)    |
| Must-operate voltage            | 9.6 VDC max.           |
| Must-release voltage            | 1 VDC min.             |
| Insulation method               | Phototriac             |
| Operation indicator             | Yellow LED             |

#### Output Circuit of Models with Built-in Heat Sinks

| Item                                            | Model | G3PE-215B-3(N)            | G3PE-215B-2(N) | G3PE-225B-3(N)            | G3PE-225B-2(N) | G3PE-235B-3(N)            | G3PE-235B-2(N) | G3PE-245B-3(N)          | G3PE-245B-2(N) | G3PE-515B-3(N)            | G3PE-515B-2(N) | G3PE-525B-3(N)          | G3PE-525B-2(N) | G3PE-535B-3(N)            | G3PE-535B-2(N) | G3PE-545B-3(N)          | G3PE-545B-2(N) |
|-------------------------------------------------|-------|---------------------------|----------------|---------------------------|----------------|---------------------------|----------------|-------------------------|----------------|---------------------------|----------------|-------------------------|----------------|---------------------------|----------------|-------------------------|----------------|
| Rated load voltage                              |       | 100 to 240 VAC            |                |                           |                |                           |                |                         |                | 200 to 480 VAC            |                |                         |                |                           |                |                         |                |
| Operating voltage range                         |       | 75 to 264 VAC             |                |                           |                |                           |                |                         |                | 180 to 528 VAC            |                |                         |                |                           |                |                         |                |
| Rated load current * 1                          |       | 15 A (at 40°C)            |                | 25 A (at 40°C)            |                | 35 A (at 25°C)            |                | 45 A (at 25°C)          |                | 15 A (at 40°C)            |                | 25 A (at 40°C)          |                | 35 A (at 25°C)            |                | 45 A (at 25°C)          |                |
| Minimum load current                            |       | 0.2 A                     |                |                           |                | 0.5 A                     |                |                         |                |                           |                |                         |                |                           |                |                         |                |
| Inrush current resistance (peak value)          |       | 150 A<br>(60 Hz, 1 cycle) |                | 220 A<br>(60 Hz, 1 cycle) |                | 440 A<br>(60 Hz, 1 cycle) |                |                         |                | 220 A<br>(60 Hz, 1 cycle) |                |                         |                | 440 A<br>(60 Hz, 1 cycle) |                |                         |                |
| Permissible I <sup>2</sup> t (reference value)  |       | 121A <sup>2</sup> s       |                | 260A <sup>2</sup> s       |                | 1,260A <sup>2</sup> s     |                |                         |                | 260A <sup>2</sup> s       |                |                         |                | 1,260A <sup>2</sup> s     |                |                         |                |
| Applicable load (resistive load: AC1 class) * 2 |       | 5.1 kW<br>(at 200 VAC)    |                | 8.6 kW<br>(at 200 VAC)    |                | 12.1 kW<br>(at 200 VAC)   |                | 15.5 kW<br>(at 200 VAC) |                | 12.5 kW<br>(at 480 VAC)   |                | 20.7 kW<br>(at 480 VAC) |                | 29.0 kW<br>(at 480 VAC)   |                | 37.4 kW<br>(at 480 VAC) |                |

\*1. The applicable load current depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature* in *Engineering Data* on page 5.

\*2. Applicable Load

Use the following formula to calculate the maximum total capacity of a heater load for a three-phase balanced load with delta connections.

Maximum load capacity = Load current × Load voltage ×  $\sqrt{3}$

Example: 15 A × 200 V ×  $\sqrt{3}$  = 5,196 W ≈ 5.1 kW

Example: 15 A × 400 V ×  $\sqrt{3}$  = 10,392 W ≈ 10.3 kW

#### Main Circuit of Models with Externally Attached Heat Sinks

| Item                                        | Model | G3PE-215B-3H                                | G3PE-215B-2H | G3PE-225B-3H              | G3PE-225B-2H | G3PE-235B-3H              | G3PE-235B-2H | G3PE-245B-3H   | G3PE-245B-2H | G3PE-515B-3H              | G3PE-515B-2H | G3PE-525B-3H   | G3PE-525B-2H | G3PE-535B-3H              | G3PE-535B-2H | G3PE-545B-3H   | G3PE-545B-2H |
|---------------------------------------------|-------|---------------------------------------------|--------------|---------------------------|--------------|---------------------------|--------------|----------------|--------------|---------------------------|--------------|----------------|--------------|---------------------------|--------------|----------------|--------------|
| Rated load voltage                          |       | 100 to 240 VAC                              |              |                           |              |                           |              |                |              | 200 to 480 VAC            |              |                |              |                           |              |                |              |
| Operating voltage range                     |       | 75 to 264 VAC                               |              |                           |              |                           |              |                |              | 180 to 528 VAC            |              |                |              |                           |              |                |              |
| Rated load current *                        |       | 15 A (at 40°C)                              |              | 25 A (at 40°C)            |              | 35 A (at 25°C)            |              | 45 A (at 25°C) |              | 15 A (at 40°C)            |              | 25 A (at 40°C) |              | 35 A (at 25°C)            |              | 45 A (at 25°C) |              |
| Minimum load current                        |       | 0.2 A                                       |              |                           |              | 0.5 A                     |              |                |              |                           |              |                |              |                           |              |                |              |
| Inrush current resistance (peak value)      |       | 150 A<br>(60 Hz, 1 cycle)                   |              | 220 A<br>(60 Hz, 1 cycle) |              | 440 A<br>(60 Hz, 1 cycle) |              |                |              | 220 A<br>(60 Hz, 1 cycle) |              |                |              | 440 A<br>(60 Hz, 1 cycle) |              |                |              |
| Permissible I²t (reference value)           |       | 121A²s                                      |              | 260A²s                    |              | 1,260A²s                  |              |                |              | 260A²s                    |              |                |              | 1,260A²s                  |              |                |              |
| Applicable load (resistive load: AC1 class) |       | Refer to <i>Engineering Data</i> on page 5. |              |                           |              |                           |              |                |              |                           |              |                |              |                           |              |                |              |

\* The rated load current depends on the heat sink or radiator that is mounted. It also depends on the ambient temperature. For details, refer to *Load Current vs. Ambient Temperature* in *Engineering Data* on page 5.

## Characteristics

### Models with Built-in Heat Sinks

| Model                         | G3PE-215B-3(N)                                                                                                                                                                             | G3PE-215B-2(N) | G3PE-225B-3(N)  | G3PE-225B-2(N)  | G3PE-235B-3(N)  | G3PE-235B-2(N)  | G3PE-245B-3(N) | G3PE-245B-2(N)  | G3PE-515B-3(N)  | G3PE-515B-2(N)          | G3PE-525B-3(N)  | G3PE-525B-2(N)  | G3PE-535B-3(N)  | G3PE-535B-2(N)  | G3PE-545B-3(N) | G3PE-545B-2(N)  |
|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------|-----------------|-----------------|-----------------|-----------------|----------------|-----------------|-----------------|-------------------------|-----------------|-----------------|-----------------|-----------------|----------------|-----------------|
| Item                          |                                                                                                                                                                                            |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Operate time                  | 1/2 of load power source cycle + 1 ms max.                                                                                                                                                 |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Release time                  | 1/2 of load power source cycle + 1 ms max.                                                                                                                                                 |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Output ON voltage drop        | 1.6 V (RMS) max.                                                                                                                                                                           |                |                 |                 |                 |                 |                |                 |                 | 1.8 V (RMS) max.        |                 |                 |                 |                 |                |                 |
| Leakage current *             | 10 mA max. (at 200 VAC)                                                                                                                                                                    |                |                 |                 |                 |                 |                |                 |                 | 20 mA max. (at 480 VAC) |                 |                 |                 |                 |                |                 |
| Insulation resistance         | 100 MΩ min. (at 500 VDC)                                                                                                                                                                   |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Dielectric strength           | 2,500 VAC, 50/60 Hz for 1 min                                                                                                                                                              |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Vibration resistance          | • DIN Track mounting: 10 to 55 to 10 Hz, 0.175-mm single amplitude (0.35-mm double amplitude)<br>• Screw mounting: 10 to 55 to 10 Hz, 0.375-mm single amplitude (0.75-mm double amplitude) |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Shock resistance              | 294 m/s² (reverse mounting: 98 m/s2)                                                                                                                                                       |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Ambient storage temperature   | -30 to 100°C (with no icing or condensation)                                                                                                                                               |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Ambient operating temperature | -30 to 80°C (with no icing or condensation)                                                                                                                                                |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Ambient operating humidity    | 45% to 85%                                                                                                                                                                                 |                |                 |                 |                 |                 |                |                 |                 |                         |                 |                 |                 |                 |                |                 |
| Weight                        | Approx. 1.25 kg                                                                                                                                                                            |                | Approx. 1.45 kg | Approx. 1.25 kg | Approx. 1.65 kg | Approx. 1.45 kg | Approx. 2.0 kg | Approx. 1.65 kg | Approx. 1.25 kg |                         | Approx. 1.45 kg | Approx. 1.25 kg | Approx. 1.65 kg | Approx. 1.45 kg | Approx. 2.0 kg | Approx. 1.65 kg |

\* The leakage current of phase S will be approximately  $\sqrt{3}$  times larger if the 2-element model is used.

### Models with Externally Attached Heat Sinks

| Model<br>Item                       | G3PE-<br>215B-<br>3H                                                    | G3PE-<br>215B-<br>2H | G3PE-<br>225B-<br>3H | G3PE-<br>225B-<br>2H | G3PE-<br>235B-<br>3H | G3PE-<br>235B-<br>2H | G3PE-<br>245B-<br>3H | G3PE-<br>245B-<br>2H | G3PE-<br>515B-<br>3H    | G3PE-<br>515B-<br>2H | G3PE-<br>525B-<br>3H | G3PE-<br>525B-<br>2H | G3PE-<br>535B-<br>3H | G3PE-<br>535B-<br>2H | G3PE-<br>545B-<br>3H | G3PE-<br>545B-<br>2H |
|-------------------------------------|-------------------------------------------------------------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|-------------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|----------------------|
| Operate time                        | 1/2 of load power source cycle + 1 ms max.                              |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Release time                        | 1/2 of load power source cycle + 1 ms max.                              |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Output ON<br>voltage drop           | 1.6 V (RMS) max.                                                        |                      |                      |                      |                      |                      |                      |                      | 1.8 V (RMS) max.        |                      |                      |                      |                      |                      |                      |                      |
| Leakage<br>current *                | 10 mA max. (at 200 VAC)                                                 |                      |                      |                      |                      |                      |                      |                      | 20 mA max. (at 480 VAC) |                      |                      |                      |                      |                      |                      |                      |
| Insulation<br>resistance            | 100 MΩ min. (at 500 VDC)                                                |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Dielectric<br>strength              | 2,500 VAC, 50/60 Hz for 1 min                                           |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Vibration<br>resistance             | 10 to 55 to 10 Hz, 0.375-mm single amplitude (0.75-mm double amplitude) |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Shock<br>resistance                 | Destruction: 294 m/s²                                                   |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Ambient<br>storage<br>temperature   | −30 to 100°C (with no icing or condensation)                            |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Ambient<br>operating<br>temperature | −30 to 80°C (with no icing or condensation)                             |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Ambient<br>operating<br>humidity    | 45% to 85%                                                              |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |
| Weight                              | Approx. 300 g                                                           |                      |                      |                      |                      |                      |                      |                      |                         |                      |                      |                      |                      |                      |                      |                      |

\* The leakage current of phase S will be approximately  $\sqrt{3}$  times larger if the 2-element model is used.


### Heat Sinks

| Model     | Weight          |
|-----------|-----------------|
| Y92B-P50  | Approx. 450 g   |
| Y92B-P100 | Approx. 450 g   |
| Y92B-P150 | Approx. 600 g   |
| Y92B-P200 | Approx. 850 g   |
| Y92B-P250 | Approx. 1,200 g |


# Engineering Data

## Input Voltage vs. Input Impedance and Input Voltage vs. Input Current

G3PE-2□□B-□□



G3PE-5□□B-□□



## Load Current vs. Ambient Temperature


### Models with Built-in Heat Sinks

G3PE-215B-3(N), G3PE-225B-3(N)

G3PE-215B-2(N), G3PE-225B-2(N)

G3PE-515B-3(N), G3PE-525B-3(N)

G3PE-515B-2(N), G3PE-525B-2(N)




G3PE-235B-3(N), G3PE-245B-3(N)

G3PE-235B-2(N), G3PE-245B-2(N)

G3PE-535B-3(N), G3PE-545B-3(N)

G3PE-535B-2(N), G3PE-545B-2(N)



\* The dotted lines in the charts are the UL derating curves for the G3PE-235B-3(N), G3PE-245B-3(N), G3PE-235B-2(N), G3PE-245B-2(N), G3PE-535B-3(N), G3PE-545B-3(N), G3PE-535B-2(N), G3PE-545B-2(N).


### Models with Externally Attached Heat Sinks

G3PE-215B-3H(-2H)

G3PE-225B-3H(-2H)

G3PE-515B-3H(-2H)

G3PE-525B-3H(-2H)




G3PE-235B-3H(-2H)

G3PE-245B-3H(-2H)

G3PE-535B-3H(-2H)

G3PE-545B-3H(-2H)



## Inrush Current Resistance: Non-repetitive

Make sure the inrush current stays below the dashed line curve if it occurs repetitively.

G3PE-215B-3(N)(H)

G3PE-215B-2(N)(H)

G3PE-225B-3(N)(H), G3PE-525B-3(N)(H)

G3PE-225B-2(N)(H), G3PE-525B-2(N)(H)

G3PE-515B-3(N)(H),




G3PE-515B-2(N)(H),

G3PE-235B-3(N)(H), G3PE-535B-3(N)(H)

G3PE-235B-2(N)(H), G3PE-535B-2(N)(H)

G3PE-245B-3(N)(H), G3PE-545B-3(N)(H)



G3PE-245B-2(N)(H), G3PE-545B-2(N)(H)



## Heat Sink Area vs. Load Current (40°C and 80°C)

G3PE-225B-3H

G3PE-525B-3H



**Note:** The heat sink area is the combined area of all surfaces of the heat sink that radiate heat.

For the G3PE-525B-3H, when a current of 18 A flows through the SSR at 40°C, the graph shows that a heat sink area of about 2,500 cm<sup>2</sup> would be required. Therefore, if the heat sink is square, one side of an aluminum plate in the heat sink must be 36 cm or longer ( $\sqrt{2,500 \text{ cm}^2}/2 = 36 \text{ cm}$  (rounded to a whole number)).

## Models with Externally Attached Heat Sinks

### Heat Resistance R<sub>th</sub> (Junction/SSR Back Surface)

| Model        | R <sub>th</sub> (°C/W) |
|--------------|------------------------|
| G3PE-215B-3H | 1.05                   |
| G3PE-225B-3H | 0.57                   |
| G3PE-235B-3H | 0.57                   |
| G3PE-245B-3H | 0.57                   |

### Heat Resistance of Heat Sinks

| Model     | R <sub>th</sub> (°C/W) |
|-----------|------------------------|
| Y92B-P50  | 1.67                   |
| Y92B-P100 | 1.01                   |
| Y92B-P150 | 0.63                   |
| Y92B-P200 | 0.43                   |
| Y92B-P250 | 0.36                   |

**Note:** If a commercially available heat sink is used, use one that has a heat resistance equal to or lower than a standard OMRON Heat Sink.



# Dimensions

**Note:** All units are in millimeters unless otherwise indicated.


## Solid State Relays

### Models with DIN Track Mounting


G3PE-215B-3N  
G3PE-215B-2N  
G3PE-225B-2N  
G3PE-515B-3N  
G3PE-515B-2N  
G3PE-525B-2N





**Note:** Without terminal cover.




**Note:** With terminal cover.



#### Mounting Holes




#### Terminal Arrangement/Internal Circuit Diagram




### Models with DIN Track Mounting


G3PE-225B-3N  
G3PE-235B-2N  
G3PE-525B-3N  
G3PE-535B-2N





**Note:** Without terminal cover.




**Note:** With terminal cover.



#### Mounting Holes




#### Terminal Arrangement/Internal Circuit Diagram





## Models with DIN Track Mounting

G3PE-235B-3N  
G3PE-245B-2N  
G3PE-535B-3N  
G3PE-545B-2N





**Note:** Without terminal cover.

**Mounting Holes**




**Note:** With terminal cover.




**Terminal Arrangement/Internal Circuit Diagram**


**G3PE-235B-3N**




**G3PE-245B-2N**



**G3PE-535B-3N**




**G3PE-545B-2N**





## Models with DIN Track Mounting

G3PE-245B-3N  
G3PE-545B-3N





**Note:** Without terminal cover.

**Mounting Holes**




**Note:** With terminal cover.




**Terminal Arrangement/Internal Circuit Diagram**

**G3PE245B-3N**



**G3PE-545B-3N**




## Models with Screw Mounting

G3PE-215B-2  
G3PE-515B-2





DIN Track or screw mounting




### Mounting Holes

Two, 4.5 dia. or M4




### Terminal Arrangement/Internal Circuit Diagram

G3PE-215B-2




G3PE-515B-2




## Models with Screw Mounting

G3PE-215B-3  
G3PE-225B-2  
G3PE-515B-3  
G3PE-525B-2





For screw mounting only




### Mounting Holes

Four, 4.5 dia. or M4




### Terminal Arrangement/Internal Circuit Diagram


G3PE-215B-3




G3PE-225B-2



G3PE-515B-3




G3PE-525B-2




## Models with Screw Mounting

G3PE-225B-3  
G3PE-235B-2  
G3PE-525B-3  
G3PE-535B-2





For screw mounting only




Note: Without terminal cover.

Note: With terminal cover.

### Mounting Holes



### Terminal Arrangement/Internal Circuit Diagram




## Models with Screw Mounting

G3PE-235B-3  
G3PE-245B-2  
G3PE-535B-3  
G3PE-545B-2





For screw mounting only




Note: Without terminal cover.

Note: With terminal cover.

### Mounting Holes



### Terminal Arrangement/Internal Circuit Diagram




## Models with Screw Mounting


G3PE-245B-3  
G3PE-545B-3



For screw mounting only





Note: Without terminal cover.





Note: With terminal cover.

### Mounting Holes




### Terminal Arrangement/Internal Circuit Diagram





## Models with Externally Attached Heat Sinks

G3PE-215B-3H  
G3PE-215B-2H  
G3PE-225B-3H  
G3PE-225B-2H  
G3PE-235B-3H  
G3PE-235B-2H  
G3PE-245B-3H  
G3PE-245B-2H  
G3PE-515B-3H  
G3PE-515B-2H  
G3PE-525B-3H  
G3PE-525B-2H  
G3PE-535B-3H  
G3PE-535B-2H  
G3PE-545B-3H  
G3PE-545B-2H







Note: Without terminal cover.

### Mounting Holes



Note: With terminal cover.

### Terminal Arrangement/Internal Circuit Diagram




# Accessories (Order Separately)

## Heat Sink

Y92B-P50 (Mounts to DIN Track.)


For G3PE-215B-2H and  
G3PE-515B-2H



## Heat Sink

Y92B-P100


For G3PE-215B-3H,  
G3PE-225B-2H,  
G3PE-515B-3H, and  
G3PE-525B-2H




## Heat Sink

Y92B-P150

For G3PE-225B-3H,  
G3PE-235B-2H,  
G3PE-525B-3H, and  
G3PE-535B-2H




Mounting Holes




## Heat Sink

Y92B-P200

For G3PE-235B-3H,  
G3PE-245B-2H,  
G3PE-535B-3H, and  
G3PE-545B-2H




Mounting Holes




## Heat Sink

Y92B-P250

For G3PE-245B-3H and  
G3PE-545B-3H



Mounting Holes



## Safety Precautions

Refer to *Safety Precautions for All Solid State Relays*.

### ⚠ CAUTION

Minor electrical shock may occasionally occur.  
Do not touch the G3PE terminal section (i.e., current-carrying parts) while the power is being supplied.  
Also, always attach the cover terminal.



The G3PE may rupture if short-circuit current flows.  
As protection against accidents due to short-circuiting, be sure to install protective devices, such as fuses and no-fuse breakers, on the power supply side.



Minor electrical shock may occasionally occur.  
Do not touch the main circuit terminals on the SSR immediately after the power supply has been turned OFF. Shock may result due to the electrical charge stored in the built-in snubber circuit.



Minor burns may occasionally occur.  
Do not touch the SSR or the heat sink while the power is being supplied or immediately after the power supply has been turned OFF. The SSR and heat sink become extremely hot.



### Precautions for Safe Use

OMRON constantly strives to improve quality and reliability. SSRs, however, use semiconductors, and semiconductors may commonly malfunction or fail. In particular, it may not be possible to ensure safety if the SSRs are used outside the rated ranges. Therefore, always use the SSRs within the ratings. When using an SSR, always design the system to ensure safety and prevent human accidents, fires, and social harm in the event of SSR failure. System design must include measures such as system redundancy, measures to prevent fires from spreading, and designs to prevent malfunction.

#### Transport

Do not transport the G3PE under the following conditions. Doing so may result in damage, malfunction, or deterioration of performance characteristics.

- Conditions in which the G3PE may be subject to water.
- Conditions in which the G3PE may be subject to high temperature or high humidity.
- Conditions in which the G3PE is not packaged.

#### Operating and Storage Environments

Do not use or store the G3PE in the following locations. Doing so may result in damage, malfunction, or deterioration of performance characteristics.

- Locations subject to rainwater or water splashes.
- Locations subject to exposure to water, oil, or chemicals.
- Locations subject to high temperature or high humidity.
- Do not store in locations subject to ambient storage temperatures outside the range -30 to 100°C.
- Do not use in locations subject to relative humidity outside the range 45% to 85%.
- Locations subject to corrosive gases.
- Locations subject to dust (especially iron dust) or salts.
- Locations subject to direct sunlight.
- Locations subject to shock or vibration.

### Installation and Handling

- Do not block the movement of the air surrounding the G3PE or heat sink. Abnormal heating of the G3PE may result in shorting failures of the output elements or burn damage.
- Do not use the G3PE if the heat radiation fins have been bent by being dropped. Doing so may result in malfunction due to a reduction in the heat radiation performance.
- Do not handle the G3PE with oily or dusty (especially iron dust) hands. Doing so may result in malfunction.
- Attach a heat sink or radiator when using an SSR. Not doing so may result in malfunction due to a reduction in the heat radiation performance.

### Installation and Mounting

- Mount the G3PE in the specified direction. Otherwise excessive heat generated by the G3PE may cause short-circuit failures of the output elements or burn damage.
- Make sure that there is no excess ambient temperature rise due to the heat generation of the G3PE. If the G3PE is mounted inside a panel, install a fan so that the interior of the panel is fully ventilated.
- Make sure the DIN track is securely mounted. Otherwise, the G3PE may fall.
- When mounting the heat sink, do not allow any foreign matter between the heat sink and the mounting surface. Foreign matter may cause malfunction due to a reduction in the heat radiation performance.
- If the G3PE is mounted directly in a control panel, use aluminum, steel plating, or similar material with a low heat resistance as a substitute for a heat sink. Using the G3PE mounted in wood or other material with a high heat resistance may result in fire or burning due to heat generated by the G3PE.

### Installation and Wiring

- Use wires that are suited to the load current. Otherwise, excessive heat generated by the wires may cause burning.
- Do not use wires with a damaged outer covering. Otherwise, it may result in electric shock or ground leakage.
- Do not wire any wiring in the same duct or conduit as power or high-tension lines. Otherwise, inductive noise may damage the G3PE or cause it to malfunction.
- When tightening terminal screws, prevent any non-conducting material from becoming caught between the screws and the tightening surface. Otherwise, excessive heat generated by the terminal may cause burning.
- Do not use the G3PE with loose terminal screws. Otherwise, excessive heat generated by the wire may cause burning.
- For the G3PE models with a carry current of 35 A or larger, use M5 crimp terminals that are an appropriate size for the diameter of the wire.
- Always turn OFF the power supply before performing wiring. Not doing so may cause electrical shock.

### Installation and Usage

- Select a load within the rated values. Not doing so may result in malfunction, failure, or burning.
- Select a power supply within the rated frequencies. Not doing so may result in malfunction, failure, or burning.
- The G3PE provides a circuit to prevent photocoupler damage by forcibly arcing the output element for surge voltages applied to the load. The G3PE therefore cannot be used for motor loads. Doing so may result in load motor malfunction.

# Safety Precautions

## Precautions for Correct Use

The SSR in operation may cause an unexpected accident. Therefore it is necessary to test the SSR under the variety of conditions that are possible. As for the characteristics of the SSR, it is necessary to consider differences in characteristics between individual SSRs.

The ratings in this catalog are tested values in a temperature range between 15°C and 30°C, a relative humidity range between 25% and 85%, and an atmospheric pressure range between 86 and 106 kPa. It will be necessary to provide the above conditions as well as the load conditions if the user wants to confirm the ratings of specific SSRs.

## Causes of Failure

- Do not drop the G3PE or subject it to abnormal vibration or shock during transportation or mounting. Doing so may result in deterioration of performance, malfunction, or failure.
- Tighten each terminal to the torque specified below. Improper tightening may result in abnormal heat generation at the terminal, which may cause burning.

| Terminals        | Screw terminal diameter | Tightening torque |
|------------------|-------------------------|-------------------|
| Input terminals  | M3.5                    | 0.59 to 1.18 N·m  |
| Output terminals | M4                      | 0.98 to 1.47 N·m  |
|                  | M5                      | 1.57 to 2.45 N·m  |


- Do not supply overvoltage to the input circuits or output circuits. Doing so may result in failure or burning.
- Do not use or store the G3PE in the following conditions. Doing so may result in deterioration of performance.
  - Locations subject to static electricity or noise
  - Locations subject to strong electric or magnetic fields
  - Locations subject to radioactivity

## Mounting

- The G3PE is heavy. Firmly mount the DIN Track and secure both ends with End Plates for DIN Track mounting models. When mounting the G3PE directly to a panel, firmly secure it to the panel.

Screw diameter: M4

Tightening torque: 0.98 to 1.47 N·m



**Note:** Make sure that the load current is 50% of the rated load current when the G3PE is mounted horizontally. For details on close mounting, refer to the related information under performance characteristics. Mount the G3PE in a direction so that the markings read naturally.


- The G3PE-2N/-3N (DIN Track mounting models) can be mounted on the following TR35-15Fe (IEC 60715) DIN Tracks.

| Manufacturer | Thickness        | 1.5 mm | 2.3 mm      |
|--------------|------------------|--------|-------------|
| Schneider    | AM1-DE200        | ---    | ---         |
| WAGO         | 210-114, 210-197 | ---    | 210-118     |
| PHOENIX      | NS35/15          | ---    | NS35/15-2.3 |


## Wiring

- When using crimp terminals, refer to the terminal clearances shown below.


### Output Terminal Section for Three-phase Models



### Output Terminal Section for Single-phase Models



### Input Terminal Section



- Make sure that all lead wires are thick enough for the current.
- For three-element and two-element models, the output terminal will be charged even when the Relay is OFF. Touching the terminal may result in electric shock. To isolate the Relay from the power supply, install an appropriate circuit breaker between the power supply and the Relay.

Always turn OFF the power supply before wiring the Unit.

- Terminal L2 and terminal T2 of a 2-element model are internally connected to each other. Connect terminal L2 to the ground terminal of the power supply. If terminal L2 is connected to a terminal other than the ground terminal, cover all the charged terminals, such as heater terminals, to prevent electric shock and ground faults.

## Fuses

- Use a quick-burning fuse on the output terminals to prevent accidents due to short-circuiting. Use a fuse with equal or greater performance than those given in the following table.

### Recommended Fuse Capacity


| Rated G3PE output current | Applicable SSR  | Fuse (IEC 60269-4) |
|---------------------------|-----------------|--------------------|
| 15 A                      | G3PE□15B Series | 32 A               |
| 25 A                      | G3PE□25B Series |                    |
| 35 A                      | G3PE□35B Series | 63 A               |
| 45 A                      | G3PE□45B Series |                    |

## Safety Precautions

### EMC Connection

Make EMC connections according to the following figure.

- Connect a capacitor to the load power supply.
- The input cable must be no longer than 3 m.



### EMI

This is a Class A product (for industrial environments). In a domestic environment, the G3PE may cause radio interference, in which case the user may be required to take appropriate measures.

### Noise and Surge Effects

If noise or an electrical surge occurs that exceeds the malfunction withstand limit for the G3PE output circuit, the output will turn ON for a maximum of one half cycle to absorb the noise or surge. Confirm that turning the output ON for a half cycle will not cause a problem for the device or system in which the G3PE is being used prior to actual use. The G3PE malfunction withstand limit is shown below.

- Malfunction withstand limit (reference value): 500 V

**Note:** This value was measured under the following conditions.

Noise duration: 100 ns and 1  $\mu$ s  
Repetition period: 100 Hz  
Noise application time: 3 min

### Mounting Models with Externally Attached Heat Sinks

- Before attaching an external Heat Sink or Radiator to the Unit, always apply silicone grease, such as Toshiba Silicone's YG6260 or Sinetsu Silicone's G746, to the mounting surface to enable proper heat radiation.
- Tighten the screws to the following torque to secure the Unit and external Heat Sink or Radiator to enable proper heat dissipation.  
Tightening torque: 2.0 N·m


### Mounting to Control Panel

The G3PE is heavy. Firmly mount the DIN track and secure both ends with End Plates for DIN-track-mounting models. When mounting the G3PE directly to a panel, firmly secure it to the panel.


If the panel is airtight, heat from the SSR will build up inside, which may reduce the current carry ability of the SSR or adversely affect other electrical devices. Be sure to install ventilation holes on the top and bottom of the panel.

### SSR Mounting Pitch (Panel Mounting)

- Single-phase Model




- Three-phase Models




## Safety Precautions

### Relationship between the G3PE and Ducts or Other Objects Blocking Airflow



### Ventilation Outside the Control Panel



- Note:**
1. If the air inlet or air outlet has a filter, clean the filter regularly to prevent it from clogging to ensure an efficient flow of air.
  2. Do not locate any objects around the air inlet or air outlet, otherwise the objects may obstruct the proper ventilation of the control panel.
  3. A heat exchanger, if used, should be located in front of the G3PE to ensure the efficiency of the heat exchanger.

### G3PE Ambient Temperature

The rated current of the G3PE is measured at an ambient temperature of 40°C.

The G3PE uses a semiconductor to switch the load. This causes the temperature inside the control panel to increase due to heating resulting from the flow of electrical current through the load. The G3PE reliability can be increased by adding a ventilation fan to the control panel to disperse this heat, thus lowering the ambient temperature of the G3PE.

(Arrhenius's law suggests that life expectancy is doubled by each 10°C reduction in ambient temperature.)

| SSR rated current (A)           | 15 A | 25 A | 35 A | 45 A |
|---------------------------------|------|------|------|------|
| Required number of fans per SSR | 0.23 | 0.39 | 0.54 | 0.70 |

Example: For 10 G3PE SSRs with load currents of 15 A,  
 $0.23 \times 10 = 2.3$

Thus, 3 fans would be required.

- Note:**
1. Size of fans: 92 mm × 92 mm, Air volume: 0.7 m³/min, Ambient temperature of control panel: 30°C
  2. If there are other instruments that generate heat in the control panel in addition to SSRs, more ventilation will be required.
  3. Ambient temperature: The temperature that will allow the SSR to cool by convection or other means.

## Read and Understand This Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

## Warranty and Limitations of Liability

### WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

### LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY.

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

## Application Considerations

### SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
- Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

### PROGRAMMABLE PRODUCTS

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

## Disclaimers

### CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the products may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased products.

### DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

### PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

### ERRORS AND OMISSIONS

The information in this document has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.



**OMRON ELECTRONICS LLC • THE AMERICAS HEADQUARTERS** • Schaumburg, IL USA • 847.843.7900 • 800.556.6766 • [www.omron247.com](http://www.omron247.com)

**OMRON CANADA, INC. • HEAD OFFICE**

Toronto, ON, Canada • 416.286.6465 • 866.986.6766  
[www.omron247.com](http://www.omron247.com)

**OMRON ELETRÔNICA DO BRASIL LTDA • HEAD OFFICE**

São Paulo, SP, Brasil • 55.11.2101.6300 • [www.omron.com.br](http://www.omron.com.br)

**OMRON ELECTRONICS MEXICO SA DE CV • HEAD OFFICE**

Apodaca, N.L. • 52.811.156.99.10 • 001.800.556.6766 • [mela@omron.com](mailto:mela@omron.com)

**OMRON ARGENTINA • SALES OFFICE**

Cono Sur • 54.11.4783.5300

**OMRON CHILE • SALES OFFICE**

Santiago • 56.9.9917.3920

**OTHER OMRON LATIN AMERICA SALES**

54.11.4783.5300

**OMRON EUROPE B.V.** Wegalaan 67-69, NL-2132 JD, Hoofddorp, The Netherlands. Tel: +31 (0) 23 568 13 00 Fax: +31 (0) 23 568 13 88 [www.industrial.omron.eu](http://www.industrial.omron.eu)