

SmartOnline 1.5kVA On-Line Double-Conversion UPS, Tower, 100/110/120V NEMA outlets

MODEL NUMBER: **SU1500XL**



Description

Tripp Lite's SmartOnline SU1500XL on-line, double conversion UPS protects critical server, networking or telecommunications equipment from blackouts, brownouts, voltage fluctuations and surges. Large-capacity 1.5kVA/1200W UPS continuously converts incoming AC to DC, then back to perfect sine wave AC output at 120V AC (+/-2%). Removes harmonic distortion, fast electrical impulses, frequency fluctuations and other hard-to-solve power problems not addressed by other UPS systems. True sine wave output and zero transfer time provides guaranteed compatibility with all equipment types. Highly efficient operation in optional economy mode setting, saving BTU heat output and energy costs. Includes 6 UPS-supported outlets. 2 load banks, each with 3 outlets, can be independently controlled via a software interface to selectively reboot remote equipment or automatically shed less critical loads to extend battery runtime for the most critical equipment. Battery backup time can be extended with the addition of multiple external battery packs. Includes slot for internal SNMP/web card, plus DB9 enhanced serial monitoring port for unattended shutdown, remote control and monitoring of UPS system and power data. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Includes Tripp Lite's PowerAlert UPS Power Management Software. Compatible with Tripp Lite's Watchdog Service Monitoring/Rebooting Software. Attractive all-black upright tower format. \$250,000 Ultimate Lifetime Insurance

Features

- True on-line, double conversion UPS provides constant, pure sine wave AC output
- Zero transfer time, on-line, double-conversion and economy-mode operation supported
- Maintains continuous operation through blackouts, brownouts, voltage fluctuations and surges with zero transfer time
- Removes harmonic distortion, electrical impulses, frequency variations and other hard-to-solve power problems
- Accepts input voltages between 80V and 150V (65V to 150V at loads under 70%), regulating output to 120V AC +/-2%
- 1500VA/1200W output capacity with 6 NEMA 5-15R outlets
- Two built-in, individually switchable load banks, each with 3 outlets, can be controlled via software interface to selectively reboot remote equipment or automatically shed less critical loads to extend battery runtime for the most critical equipment
- Standard internal battery set provides 14 min. runtime at half load and 4.5 min. at full load
- Runtime is expandable with BP48V24-2U (limit 1), BP48V60RT-3U (multi-pack compatible) and BP48V27-2US (multi-pack compatible) external battery

Highlights

- 1500VA / 1.5kVA / 1200 watt on-line double-conversion tower UPS
- 110/120V +/-2% output at 50/60Hz, high efficiency economy mode option
- Expandable runtime, Hot-swappable battery modules
- USB, RS232 & EPO ports; support for SNMP/WEB card options
- Front panel status LEDs with detailed load and battery metering
- 2 independently switchable output load banks
- NEMA 5-15P input; 5-15R outlets

Package Includes

- SU1500XL UPS System
- PowerAlert Software
- USB, DB9 and EPO cabling
- Owner's manual with warranty information



packs

- Some external battery configurations require the use of Tripp Lite's External Battery Configuration Software (see manual)
- Attractive all-black upright tower format
- Simultaneous communications via HID-compliant USB port, DB9 serial port, and SNMP/web card slot
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- DB9 serial network interface supports RS-232 and contact closure messaging
- Slot for optional SNMP/web card (part# SNMPWEBCARD)
- Included PowerAlert UPS Power Management Software and cabling provides monitoring of in-depth site power conditions, full UPS status and fault warnings, output load level and load bank power control
- Compatible with Tripp Lite's WatchDog Service Monitoring/Rebooting Software (part # WATCHDOGSW)
- Fault tolerant electronic bypass maintains utility output during a variety of UPS fault conditions
- Diagnostic LEDs
- Built-in RJ-11 EPO (Emergency Power Off) jack allows connection to site emergency power off systems
- \$250,000 Ultimate Lifetime Insurance coverage for connected equipment (USA and Canada Only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output kVA capacity (kVA)	1.5
Output Watt Capacity (watts)	1200
Output kW capacity	1.2
Output power factor	0.8
Crest Factor	3:1
Nominal Output Voltage(s) Supported	100V; 110V; 120V
Nominal Voltage details	120V default
Frequency compatibility	50 / 60 Hz
Frequency compatibility details	Output frequency matches input nominal on startup, defaults to 60 Hz on cold-start
Output voltage regulation (line mode)	+/- 2%
Output voltage regulation (Economy line mode)	+/- 10%
Output voltage regulation (Battery mode)	+/- 2%
Built-in UPS output receptacles	6 5-15R outlet(s)
Built-in controllable switched load banks	Two switchable three-outlet 5-15R load banks
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	Pure Sine wave



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Rated input current (at maximum load)	12A (120V), 14A (110V), 15.4A (100V)
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 120V AC
UPS input connection type	5-15P
Input circuit breaker	20A
UPS Input cord length (ft.)	10
UPS Input cord length (m)	3
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	4.5 min. (1200w)
Half load runtime (minutes)	14 min. (600w)
Expandable battery runtime	Extended runtime supported via optional external battery packs
External battery pack compatibility	BP48V24-2U (limit 1); BP48V60RT-3U (multi-pack compatible); BP48V27-2US (multi-pack compatible)
DC system voltage (VDC)	48
Battery recharge rate (included batteries)	Less than 6 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC48-SUTWR
Battery Access	Battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Online, double-conversion power conditioning
Overvoltage correction	2% output voltage regulation during overvoltages to 150
Undervoltage correction	2% output voltage regulation during undervoltages to 80
Severe undervoltage correction	2% output voltage regulation during undervoltages to 65 (under 70% load only)
LEDS ALARMS & SWITCHES	
LED Indicators	14 LEDs indicate line power, online mode, economy/bypass mode, on-battery, overload, battery low, replace battery and fault status information - includes 4-LED meter display for load and battery charge level
Alarms	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS AC suppression joule rating	570
UPS AC suppression response time	Instantaneous
UPS Dateline suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	10.2 x 9 x 19.5
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	26 x 22.9 x 49.5
UPS / Power Module weight (lbs)	49.3
UPS / Power Module weight (kg)	22.4
UPS Shipping dimensions (height x width x depth / inches)	15.2 x 13 x 24
UPS Shipping dimensions (height x width x depth / cm)	38.7 x 33 x 61
Shipping weight (lbs)	56
Shipping weight (kg)	25.4
Cooling method	Fans
UPS housing material	Steel
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	609.7
AC economy mode BTU / hr. (full load)	260.4
Battery mode BTU / hr. (full load)	609.7
AC mode efficiency rating (100% load)	87%
AC economy mode efficiency rating (100% load)	94%
Audible Noise	< 45 dB at front side 1m
COMMUNICATIONS	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Communications interface	USB (HID enabled); DB9 Serial; Contact closure; EPO (emergency power off); Slot for SNMP/Web interface
Network monitoring port description	Supports detailed monitoring of UPS and site power conditions; DB9 port supports RS232 and contact closure communications
PowerAlert software	Included
Communications cable	USB and DB9 cabling included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	No transfer time (0 ms.) in online, double-conversion mode
Low voltage transfer to battery power (setpoint)	80V (100% load), 65V (<70% load)
High voltage transfer to battery power (setpoint)	150
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Automatic inverter bypass; Hot swappable batteries
Green & high efficiency features	High efficiency economy mode operation; Individually controllable load banks; Schedulable daily hours of economy mode operation
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Model Number	Description	Qty.
SNMPWEBCARD	For remote monitoring and control via SNMP, Web, or Telnet.	1
ENVIROSENSE	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
SR SWITCH	Magnetic Door Switch Kit for front and rear doors; requires ENVIROSENSE	1
BP48V27-2US	BP48V27-2US - 2U External 48V Rack/Tower Battery pack for select Tripp Lite UPS Systems	1
BP48V24-2U	BP48V242U - External Battery Pack for UPS System	1
BP48V60RT-3U	External Battery Pack and Cable. 3U, Expandable, Blue 2-Point Connector	1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WEXT3-500-1500	3-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1
WEXT5-500-1500	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1
PDUB15	Dual source Power Distribution Unit / PDU with Manual Transfer Switch enables Hot-swappable UPS Replacement in Critical Network Applications	1
PDUMH15AT	Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching	1
PDUMH15	Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter	1
PDUMNH15	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
PDUMH15NET	Single-Phase Switched PDU, 15A 120V, 1U Horizontal Rackmount, NEMA 5-15R outlets, NEMA 5-15P input plug	1
RELAYIOCARD	Programmable Relay I/O Card	1
MODBUSCARD	For remote monitoring and control via MODBUS protocol	1
AS400CABLEKIT2	Power Management Tools - UPS Communication Cable Kit for System i / AS400 / iSeries Servers	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:

<http://www.tripplite.com/sku/SU1500XL>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SU1500XL](#)