



MOSFETs (Cont'd)



TO-206AF (TO-72)


Channel	Min. $V_{(BR)GSS}$ (V)	Max. $r_{DS(ON)}$ (Ω)	Max. $V_{GS(th)}$ (V)	Part Number
P	-40	250	-5	3N163
P	-30	300	-5	3N164



TO-220AB

Channel	Min. $V_{(BR)GSS}$ (V)	Max. $r_{DS(ON)}$ (Ω)	Max. $V_{GS(th)}$ (V)	Part Number
N	40	3	2.5	VN46AFD
N	60	3	2.5	VN66AFD

Channel	Min. $V_{(BR)GSS}$ (V)	Max. $r_{DS(ON)}$ (Ω)	Max. $V_{GS(th)}$ (V)	Part Number
N	80	4	2.5	VN88AFD
N	240	6	2.0	VN2406D



TO-226AA (TO-92)

Min. $V_{(BR)GSS}$ (V)	Max. $r_{DS(ON)}$ (Ω)	Max. $V_{GS(th)}$ (V)	Channel	Part Number
-240	10	-2.4	P	TP2410L
-240	10	-2.5	P	VP2410L
-200	20	-2.8	P	BSS92
-200	10	-2.4	P	TP2010L
-200	20	-2.4	P	TP2020L
-200	20	-2.5	P	VP2020L
-120	20	-2.4	P	TP1220L
-100	5	-4.5	P	VP1008L
-80	5	-4.5	P	VP0808L
-60	10	-3.5	P	VP0610L
-45	14	-3.5	P	BS250
-30	2.5	-4.5	P	VP0300L
20	4	2.0	N	TN0201L
30	1.2	2.5	N	VN0300L
40	4	2.0	N	TN0401L

Min. $V_{(BR)GSS}$ (V)	Max. $r_{DS(ON)}$ (Ω)	Max. $V_{GS(th)}$ (V)	Channel	Part Number
60	5	3.0	N	2N7000
60	5	3.0	N	BS170
60	3	2.0	N	TN0601L
60	5	2.5	N	VN0610L
60	5	2.5	N	VN0610LL
60	7.5	2.5	N	VN2222L
60	7.5	2.5	N	VN2222LL
120	6	2.0	N	TN1206L
120	6	2.0	N	VN1206L
120	10	2.0	N	VN1210L
200	28	3.0	N	BS107
200	12	-4.0	N	ND2012L
200	20	-2.5	N	ND2020L
200	10	1.8	N	TN2010L
200	10	1.8	N	VN2010L