

## Housing - HC-D 15-KML-48/O1M20 - 1604892

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON coupling housing D15, with single locking latch, height 48 mm, with support 1xM20

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 10            |
| GTIN             | 4017918882389 |

### Technical data

#### Dimensions

|        |         |
|--------|---------|
| Height | 48 mm   |
| Width  | 29.5 mm |
| Length | 63 mm   |

#### Ambient conditions

|                                  |                   |
|----------------------------------|-------------------|
| Degree of protection for housing | IP65              |
| Ambient temperature (operation)  | -40 °C ... 125 °C |

#### General

|                              |                                 |
|------------------------------|---------------------------------|
| Note                         | For contact inserts HC-D15, A10 |
| Design                       | D15                             |
| Housing type                 | Coupling housings               |
| Locking type                 | With single locking latch       |
| No. of cable exits           | 1                               |
| Cable exit                   | Straight                        |
| Screw connection             | None                            |
| Type of the screw connection | 1x M20                          |
| Housing material             | Aluminum die-cast               |
| Housing surface material     | Powder-coated, gray             |
| Material lock                | Steel, galvanized               |

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |

## Housing - HC-D 15-KML-48/O1M20 - 1604892

### classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440209 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000437 |
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11     | 31261502 |
| UNSPSC 12.01  | 31261502 |
| UNSPSC 13.2   | 31261502 |

### approvals

GOST /

#### Approval details

|                                                                                          |
|------------------------------------------------------------------------------------------|
|  GOST |
|------------------------------------------------------------------------------------------|

### accessories

#### Full screw connection

HC-K-KV-M20(8-13) - 1690626



## Housing - HC-D 15-KML-48/O1M20 - 1604892

### accessories

HC-M-KV-M20(9-13) - 1690561



---

HC-M-KV-M20(11-16) - 1645998



---

HC-M-KV-M20(1ASI) - 1584017




---

### Drawings

## Housing - HC-D 15-KML-48/O1M20 - 1604892

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>