

Io=200mA High accuracy ±1% CMOS LDO Regulator IC
Io=200mA ±1%高精度出力CMOS低飽和レギュレータIC



TK641XXAMF
(HSON1214-4)

DESCRIPTION

The TK641XXAMF is a CMOS LDO Regulator.
 The package is the very small and thin HSON1214-4.
 The IC is designed for portable applications with space requirements.
 The IC can supply 200mA output current.
 The IC does not require a noise-bypass capacitor.
 The output voltage is internally fixed from 1.5V to 4.2V.

TK641XXAMFはCMOS LDOレギュレータICです。
 パッケージは超小型低背のHSON1214-4です。
 高密度実装を要求される携帯機器に最適です。
 200mAの出力電流を安定に供給できます。
 ノイズパス容量を必要としません。
 出力電圧は内部固定で、1.5V~4.2Vで設定可能です。

FEATURES

- High accuracy (±1%)
- Package: HSON1214-4
- No noise bypass capacitor required
- High ripple rejection
- Fast transient response
- Low noise
- Thermal and over current protection
- High maximum load current
- On/Off control
- 高い出力電圧精度(±1%)
- パッケージ: HSON1214-4
- ノイズパス容量が不要
- 高いリップルリジェクション
- 高速応答特性
- 低いノイズ
- 垂下形過電流保護, 過熱保護
- 高い最大出力電流
- On/Offコントロール

ELECTRICAL CHARACTERISTICS

Type	V _{OUT} (tolerance)	I _{OUT} (I _{OUT.MAX})	On/off control	V _{DROP} @I _{OUT}	I _Q @I _O =0mA	Ripple rejection	V _{OP}	T _{OP}	P _D	f _{OP}
TK641XXAMF	1.5 to 4.2V (±1.0% or ±25mV)	200mA (210mA)	Active high	85mV@ 100mA	35μA	-72dB @f=1kHz	1.8 to 6.0V	-40 to +85°C	400mW	-

PIN DESCRIPTION

- HSON1214-4

